

SECURITY CLASSIFICATION: Customer Release NUMBER: 108-5307

DESIGN OBJECTIVES.

The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore, AMP (Japan), Ltd makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, AMP (Japan), Ltd. may change these requirements based on the results of additional testing and evaluation. Contact AMP Engineering for further details.

In case when "product specification" is referred to in this document, it should be read as "design objectives" for all times as applicable.

108-5307

2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device

1. Scope :

1.1 Contents :

This specification covers the requirements for product performance and test methods of AMP 2.0 mm Dia. Ignition Plug Contact for frame Sensor device of the part number specified below.

Part Number	Descriptions	Remarks
175135-□	Receptacle Contact	for #22 - #18 AWG

2. Materials :

2.1 Receptacle Contact : Pretinned Phosphor Bronze

3. Ratings :

3.1 Voltage Rating : 200 V AC max.

3.2 Current Rating : 5 A max.

3.3 Temperature Rating : -20/+150°C (Temperature rising due to loaded current is included.)

3.4 Applicable Wire Range :

Contact Part No.	Wire Size	
	Conductor mm ² (AWG)	Insulation Diameter (mm)
175135-□	0.3 - 0.89 (#22 - #18)	1.2 - 3.5

PRINT	DIST.	01	Design Objectives	Y.M	<i>[Signature]</i>	24 FEB 95	APP.	NAME	Design Objectives
		0	RFA-1472	<i>[Signature]</i>	<i>[Signature]</i>	24 FEB 95	<i>[Signature]</i>		
LTR	REVISION RECORD	DR	CHK	DATE					

AMP

AMP (Japan), Ltd.
Kawasaki, Japan

LOC	LOC	NO.		REV.
J	A	108-5307		01

SECURITY CLASSIFICATION: Customer Release NUMBER: 108-5307

4. Quality Assurance Provisions :

4.1 Test Conditions :

Unless otherwise specified, all the tests shall be performed under any combination of the following test conditions.

- Temperature : 15-35 °C
- Relative Humidity : 45-75 %
- Atmospheric Pressure : 650-800 mmHg

4.2 Test Specimens :

The test specimens to be employed for the testing shall be selected from the normal production, conforming to the applicable drawing (s), and prepared in accordance with AMP Application Specification, 114-5130, using the wires of the sizes specified in Para. 3.4. The samples shall be not reused, unless otherwise specified.

5. Performance Requirements and Test Methods :

Para.	Test Items	Requirements		Procedures	
5.1	Appearance	Product shall be free from the abnormalities such as scratch, cracks, deformation, blister, dirt and burrs that are detrimental to connector functions and merchandising value.		Visual inspection.	
5.2	Crimp Tensile Strength	Wire Size mm ² (AWG)	Tensile Strength kg (min)	Apply an axial pull-off load to contact crimped on applicable wire (about 100 mm in length), at a rate of 100 mm a minute. Measure the force required to break wire or separates wire from crimp without insulation barrel	
		0.3 (#22)	5		
		0.5 (#20)	7		
		0.75 (#18)	12		
5.3	Contact insertion Contact Separating Forces	Ins. Force	Sep. Force		Apply force to contact with the use of tensile tester at a rate of 100 mm a minute, with ignition plug fixed. Measure the forces required to insert or separate contact.
		(kg) (max.)	Initial (kg)	10th Cycle (kg)	
		5.0	1.0 to 5.0	0.8 to 5.0	

SHEET 2 OF 7	AMP		AMP (Japan), Ltd. Kawasaki, Japan	
			LOC J	LOC A
NAME 2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device				

SECURITY CLASSIFICATION: Customer Release NUMBER: 108-5307

Para.	Test Items	Requirements	Procedures
5.4	Temperature Rise	30 °C max.	Apply rated current to contact crimped on applicable range of wire, with it mated with plug. Take temperature reading on thermocouple attached to crimp, in stable condition reached. Temperature rise equals the above reading value minus room temperature.
5.5	Termination Resistance (Low Level)	100 m Ω max.	Subject contacts mated with plug to 50 mV open circuit at 100 mA maximum. Measure as indicated in Fig. 1. Calculate resistance values by subtracting resistance of wire (75 mm) and plug (55 mm) from the measured value.




Fig. 1

SHEET 3 OF 7	AMP		AMP (Japan), Ltd. Kawasaki, Japan	
	LOC J	LOC A	NO. 108-5307	REV. 01
NAME 2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device				

NUMBER: 108-5307
 SECURITY CLASSIFICATION: Customer Release

Para.	Test Items	Requirements	Procedures
5.6	Vibration Sinusoidal Low Frequency	Termination Resistance, (low level) : 150 mΩ max.	Subject contacts mated with plug to the following conditions as specified in MIL-STD-202, Method 201 with them fixed on vibration tester as indicated in Fig.2 : Frequency : 10-55-10 Hz traversed in 1 minute. Total excursion : 1.5 mm Duration : 2 hours in each of 3 mutually perpendicular axes (X,Y,and Z) Subject samples to termination resistance (low level) test after vibration test.
<p>Fig. 2</p>			
5.7	Humidity Steady State	Termination Resistance (low level) : 150 mΩ max.	Subject mated samples to the following conditions as specified in MIL-STD-202, Method 103 : Temperature : 40 °C Humidity : 90 to 95 % Duration : 96 hours Subject low level termination resistance test after the above test.

SHEET 4 OF 7	AMP		AMP (Japan), Ltd. Kawasaki, Japan	
	LOC J	LOC A	NO. 108-5307	REV. 01
NAME 2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device				

SECURITY CLASSIFICATION: Customer Release NUMBER: 108-5307	Para.	Test Items	Requirements	Procedures										
	5.8	Thermal Shock	Termination Resistance (low level) : 150 mΩ max.	Subject mated samples to 25 cycles of the following test conditions as specified in MIL-STD-202, Method 107 : <u>Step of</u> <table border="1"> <thead> <tr> <th>Temp Shift</th> <th>Exposure Condition</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>150 ± 3/0 °C, 30 minutes</td> </tr> <tr> <td>2</td> <td>Room Temp. 5 minutes</td> </tr> <tr> <td>3</td> <td>-20 ± 0/3 °C 30 minutes</td> </tr> <tr> <td>4</td> <td>Room Temp. 5 minnutes</td> </tr> </tbody> </table>	Temp Shift	Exposure Condition	1	150 ± 3/0 °C, 30 minutes	2	Room Temp. 5 minutes	3	-20 ± 0/3 °C 30 minutes	4	Room Temp. 5 minnutes
	Temp Shift	Exposure Condition												
1	150 ± 3/0 °C, 30 minutes													
2	Room Temp. 5 minutes													
3	-20 ± 0/3 °C 30 minutes													
4	Room Temp. 5 minnutes													
5.9	Salt Spray	Termination Resistance (low level) : 15 mΩ max.	Subject mated samples to the following conditions as specified in MIL-STD-202, Method 101, Condition B : Salt concentration : 5 % Temperature : 35 °C Duration : 48 hours Measure termination resistance after samples cleaned in tap water and dried in the room temperature for 1 hour.											
5.10	Temperature Life	Termination Resistance (low level) : 150 mΩ max.	Subject mated samples to the following conditions as specified in MIL-STD-202, Method 108 : Temperature : 150 °C Daration : 96 hours Measure termination resistance (low level) on samples after the above exposure test.											

SHEET	AMP			AMP (Japan), Ltd. Kawasaki, Japan
	5 OF 7	LOC J	LOC A	NO. 108-5307
NAME		2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device		
				REV. 01

NUMBER: 108-5307

SECURITY CLASSIFICATION:

Customer Release

6. Product tests and Sequences :

Products tests and sequences, shall be performed in accordance with the following table :

Classification			Test Sequence							
Test Item	Group	Para	I	II	III					IV
Appearance		5.1	1	1	1					
Crimp Tensile Strength		5.2	2							
Contact Insertion Force		5.3		2						
Contact Separating Force		5.3		3						
Temperature Rise		5.4								1
Temperature Resistance Low level		5.5			2	4	6	8	10	12
Vibration Low frequency		5.6			3					
Humidity		5.7				5				
Thermal Shock		5.8					7			
Salt Spray		5.9						9		
Temperature Life		5.10							11	

SHEET 6 OF 7	AMP		AMP (Japan), Ltd. Kawasaki, Japan	
	LOC J	LOC A	NO. 108-5307	REV. 01
NAME 2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device				

108-5307


NUMBER:

Customer Release

SECURITY CLASSIFICATION:

7. Mating Plug :

Mating plug to be used for product performance test shall have dimensions as indicated in Fig.3.



Unit : mm

- Note : 1. Material for plug shall be heat resistant alloy for high temperature. (YSS-YSTT)
 2. Unplated Plug shall be used.

Fig. 3

SHEET	AMP AMP (Japan), Ltd. Kawasaki, Japan			
	7 OF 7	LOC J	LOC A	NO. 108-5307
NAME 2.0 mm Dia. Ignition Plug Contact for Frame Sensor Device				