

PRODUCT SPECIFICATION 108-106087

15 NOV 21 Rev. E

Industrial Mini I/O Connector

1. Scope

1.1 Contents

This specification covers the requirements for product performance, test methods and quality assurance provisions of Industrial Mini I/O Connector.

Applicable product description and part numbers are as shown in Fig 1.

| P/N | Description |
|-------------|---|
| 1971885-1 | |
| 1-1971885-1 | |
| 2271656-1 | Industrial Vertical Mini I/O Connector SMT type I |
| 1-2271656-1 | |
| 4-2271656-1 | |
| 1971885-2 | |
| 1-1971885-2 | Industrial Vertical Mini I/O Connector SMT type II |
| 2271656-2 | industrial vertical with 1/O Confidential Swift type if |
| 1-2271656-2 | |
| 1971886-1 | Industrial Vertical Mini I/O Connector THR type I |
| 1971886-2 | Industrial Vertical Mini I/O Connector THR type II |

(Fig 1)

2. Applicable Documents:

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence.

In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1 TE Specifications:

A. 501-106087-1: Test Report: (SMT TYPE)B. 501-106087-2: Test Report: (DIP TYPE)



2.2 Commercial Standards and Specifications:

A. EIA364 series

3. Requirements:

3.1 Design and Construction:

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

3.2 Materials:

Receptacle:

A. Contact:

Material: Copper alloy

Finish: Nickel plating all over Contact area: Au plating Soldering area: Tin plating

B. Housing:

Material: Thermo plastic Flammability: UL94 V-0

C. Shell:

Material: Phosphor Bronze

Finish: Tin plating over Ni under-plating

3.3 Ratings:

A. Voltage Rating: 50 V a.c. / 60 V d.c.

B. Current Rating: 0.5A

C. Temperature Rating: −40° C to 85° C

3.4 Performance Requirements and Test Descriptions :

The product shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Fig.2.

All tests shall be performed in the room temperature, unless otherwise specified.



3.5 Test Requirements and Procedures Summary

| Para | Test Items | Requirements | Procedures | | | | | |
|-------|----------------------|--------------------------|--|--|--|--|--|--|
| 3.5.1 | Examination of | Meets requirements of | Visual inspection | | | | | |
| | Product | product drawing. | No physical damage. | | | | | |
| | | Electrical Requirer | nents | | | | | |
| 3.5.2 | Termination | 40 mΩMax. (Initial) | Subject mated contacts assembled in housing | | | | | |
| | Resistance | 50 mΩMax. (After Test) | to 20mV Max open circuit at 100mA. Fig.3. | | | | | |
| | (Low Level) | | EIA364-23 | | | | | |
| | | | | | | | | |
| 3.5.3 | Insulation | 500MΩMin. | 100V DC. 1minute hold. | | | | | |
| | Resistance | | Test between adjacent circuits of mated | | | | | |
| | | | connectors.EIA364-21 | | | | | |
| 3.5.4 | Dielectric | No creeping discharge or | DWV test condition (1 minute hold); | | | | | |
| | withstanding Voltage | flashover shall occur. | 1000V DC : Between contact to contact | | | | | |
| | | Leak current: 0.5mA Max. | 1500V DC : Between contact to shell | | | | | |
| | | | Test between adjacent circuits of mated | | | | | |
| | | | connectors. EIA364-20 | | | | | |
| 3.5.5 | Temperature Rising | 30° CMAX under loaded | Measure temperature rising by energized | | | | | |
| | | rating current. | current. | | | | | |
| | | Mechanical Require | ements | | | | | |
| 3.5.6 | Connector | 30 N Max. | Operation speed: 10mm/min. | | | | | |
| | Mating Force | | Measure force necessary to mate samples. | | | | | |
| | | | EIA364-13 | | | | | |
| | | | | | | | | |
| 3.5.7 | Connector | 30 N Max. | Set lock operation part of plug connector to | | | | | |
| | Un-mating Force | | open. Operation speed: 10mm/min. | | | | | |
| | | | Measure force necessary to unmate samples. | | | | | |
| | | | EIA364-13 | | | | | |
| 0.5.0 | Durahilitu | Tormination Desisters | Operation Cheed (200) water the com- | | | | | |
| 3.5.8 | Durability | Termination Resistance | Operation Speed :200cycles/hour | | | | | |
| | (Repeated | (Low Level). | No. of Cycles: 1500cycles.(SMT HDR) | | | | | |
| | Mate/Unmating) | | No. of Cycles: 1500cycles.(DIP HDR) | | | | | |
| 2.5.0 | Coble Bull Out | No domago or saldarina | EIA364-09 | | | | | |
| 3.5.9 | Cable Pull-Out | No damage on soldering | Apply axial load to cable on plug connector. | | | | | |
| | | place. | Fig.4 EIA364-38 | | | | | |
| | | No disconnection between | Retention force for KIT products shall be | | | | | |
| | | shield wire to shell. | determined by cable. | | | | | |
| | | | Retention force for CABLE ASSY products | | | | | |
| | | | shall be specified on CABLE ASSY drawing. | | | | | |



Fig.2(CONT.)

| Para | Test Items | Requirements | Procedures |
|--------|-------------------|-----------------------------|---|
| 3.5.10 | Lock Strength | Connector must not unmate. | Mate connector and make lock mechanism |
| | | No destruction on Lock | effective. |
| | | elements, no destruction on | Apply axial load to cable on plug connector. |
| | | Receptacle connector with | 98 N. 1 minute. Fig.4 |
| | | PC-Board and no harmful | |
| | | damage on other parts. | |
| 3.5.11 | Elasticity | Connector must not unmate. | Mate connector and make lock mechanism |
| | | No destruction on Lock | effective. |
| | | elements, no destruction on | Apply axial load to cable on plug connector |
| | | Receptacle connector with | 20N and bend cable to direction 45 degrees |
| | | PC-Board and no harmful | each on both side up to 20 cycles. |
| | | damage on other parts. | Fig.5 |
| 3.5.12 | Fixed Strength to | No destruction on | Mate connector. Apply load to edge of plug |
| | PC-Board | Receptacle connector with | connector. |
| | | PC-Board and no harmful | Load one direction on one sample. Fig 6 |
| | | damage on other parts. | 40 N. 1 minute for PN:*-227165-* |
| | | | 15N. 1 minute for PN:*-1971885-* |
| | | | Recommend panel protection for bigger |
| | | | strength application (Fig.7) |
| 3.5.13 | Vibration | No electrical discontinuity | Subject mated connectors to 10-55-10 Hz |
| | (Low Frequency) | greater than 1µsec shall | traversed in 1 minute at 1.52mm amplitude 2 |
| | | occur. | hours each of 3 mutually perpendicular planes. |
| | | Termination Resistance | EIA364-28 |
| | | (Low Level). | |
| 3.5.14 | Physical Shock | No electrical discontinuity | Accelerated Velocity : 30G |
| | | greater than 1µsec shall | Waveform : Half-sin wave |
| | | occur. | Duration: 11 millisecond |
| | | Termination Resistance | Number of drops: 3 drops each to normal and |
| | | (Low Level). | reversed directions of X, Y and Z axes, totally |
| | | | 18 drops. |
| | | | EIA364-27 |



PRODUCT SPECIFICATION 108-106087

15 NOV 21 Rev. F

| | | | 15 NOV 21 Rev. E |
|----------|--------------------|-------------------------------|--|
| 3.5.15-1 | Solder ability | Appearance of the specimen | Eutectic solder |
| | (DIP Products) | shall be inspected after the | Solder Temperature : 235±5° C |
| | | test with the assistance of a | Immersion Duration: 3±0.5 sec. |
| | | magnifier capable of giving a | Lead-Free solder (Sn-Ag-Cu) |
| | | magnifier of 10X. | Solder Temperature : 245±5° C |
| | | The soldered surface shall | Immersion Duration: 3±0.5 sec. |
| | | be covered with a smooth | MIL-STD-202 Method 208 |
| | | solder coating with no more | |
| | | than small amounts of | |
| | | scattering imperfections | |
| | | such as pin-holes or un-wet | |
| | | or de-wet areas. | |
| Para | Test Items | Requirements | Procedures |
| 3.5.15-2 | Solder ability | Appearance of the specimen | Conform to IEC60068-2-58 7.Solder reflow |
| | (SMT Products) | shall be inspected after the | method. |
| | | test with the assistance of a | Preheating: 150±10° C, 60~120sec |
| | | magnifier capable of giving a | Soldering: 235±5° C, 10±1 sec |
| | | magnifier of 10X. | Number of reflow : 2 |
| | | The soldered surface shall | |
| | | be covered with a smooth | |
| | | solder coating with no more | |
| | | than small amounts of | |
| | | scattering imperfections | |
| | | such as pin-holes or un-wet | |
| | | or de-wet areas. | |
| | | Environmental Requi | rements |
| 3.5.16 | Temperature Life | Termination resistance | Mated connector |
| | (Heat Aging) | (Low Level) | 85° C, 315 Hours |
| | | | EIA364-17 |
| 3.5.17 | Humidity | Insulation resistance | Mated connector |
| | (Steady State) | Dielectric Strength | 90-95%R.H. 40° C |
| | | Termination resistance | 240 hours |
| | | (Low Level) | EIA364-31 |
| 3.5.18 | Thermal Shock | Termination Resistance | Mated connector |
| | | (Low Level) | -55° C/ 30 min. +85° C/ 30 min. |
| | | | Making this a cycle, repeat 10 cycles. |
| | | | EIA364-32 |
| 3.5.19 | Humidity-Temperatu | Insulation resistance | Mated connector, 25∼65° C, |
| | re | Dielectric Strength | 80~100%R.H. 7 cycles |
| | Cycling | Termination resistance | Cold shock –10° C performed |
| | | (Low Level) | EIA364-31 |



PRODUCT SPECIFICATION 108-106087

15 NOV 21 Rev. E

| 3.5.20 | Salt Spray | Termination resistance(Low | Mated connector |
|--------|------------------------|-----------------------------------|---------------------------------------|
| | | Level) | Salt concentration: 5%, 35±2° C, |
| | | After it is left for 1 hour under | 48 hours |
| | | a steady | EIA364-26 |
| | | temperature/humidity, it is | (MIL-STD-202F Method 101 Condition B) |
| | | measured. | |
| 3.5.21 | Hydrogen sulfide | Termination resistance | Mated connector |
| | Gas (H ₂ S) | (Low Level) | H₂S Gas :3±1ppm, 40±2° C, 96 hours |
| 3.5.21 | | measured. Termination resistance | Mated connector |

Fig.2(CONT.)

| Para | Test Items | Requirements | Procedures |
|----------|----------------|-------------------------------|---|
| 3.5.22-1 | Resistance to | No physical damage shall | Test connector on PCB. |
| | Soldering Heat | occur. | Solder Temperature : 260±5° C |
| | (DIP Products) | | Immersion Duration : 10±0.5 sec. |
| | | | AMP Spec. 109-5204, Condition B |
| | | | MIL-STD-202, Condition 210 |
| | | | In case of manual soldering iron, apply it as |
| | | | 360±10° C for 3±0.5° C seconds without |
| | | | forcing pressure to affect the tine of contact. |
| 3.5.22-2 | Resistance to | Appearance of the specimen | Test connector on PC-Board. |
| | Soldering Heat | shall be inspected after the | Reflow |
| | (SMT Products) | test with the assistance of a | Average ramp rate: 3° C/ sec max |
| | | magnifier capable of giving a | Preheat temperature:150~200° C |
| | | magnification of 10X, No | Preheat time: 60~180sec |
| | | physical damage such as | Ramp to peak: 3° C/ sec max |
| | | cracks, chips or malting. | Time over liquid's (217° C):60~150 seconds |
| | | | Peak temperature: 260 +0/-5 ° C |
| | | | Time within 5° C of peak:20~40 sec |
| | | | Ramp - cool down: 6° C/ sec max |
| | | | Time 25° C to peak: 8 min max |
| | | | After reflow, then DIP (Legs of shell) |
| | | | Solder temperature 260° C±5° C |
| | | | Immersion duration 10±1sec. |
| | | | Number of reflow : 2 |
| | | | EIA-364-56 |

NOTE

Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in the Product Qualification and Re qualification Test Sequence shown in Figure 3.

Fig. 2 (END)



PRODUCT SPECIFICATION

1 108-106087 15 NOV 21 Rev. E

3.6 Product Qualification Test Sequence

| Test Examination | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 |
|-------------------------|-----|-----|---|-----|---|---|-----|-----|---|-----|-----|-----|-----|-----|-----|----|
| | | | | | | | | | | | | | | | | |
| Examination of | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 |
| Product | ı | · | | ı | ' | | ' | ı | ' | ı | ı | ı | ' | ' | ı | ľ |
| Termination | | | | | | | | | | | | | | | | |
| Resistance | | | | 2,6 | | | 2,4 | 2,5 | | 2,4 | 2,4 | 2,4 | 2,4 | 2,4 | 2,4 | |
| (Low Level) | | | | | | | | | | | | | | | | |
| Insulation Resistance | 2,5 | 2,5 | | | | | | | | | | | | | | |
| Dielectric withstanding | 0.0 | 0.0 | | | | | | | | | | | | | | |
| Voltage | 3,6 | 3,6 | | | | | | | | | | | | | | |
| Temperature Rising | | | 2 | | | | | | | | | | | | | |
| Conn. Mating Force | | | | 3 | | | | | | | | | | | | |
| Conn. Unmating | | | | | | | | | | | | | | | | |
| Force | | | | 4 | | | | | | | | | | | | |
| Durability | | | | | | | | | | | | | | | | |
| Repeated | | | | 5 | | | | | | | | | | | | |
| mate/Unmating | | | | | | | | | | | | | | | | |
| Cable Pull-Out | | | | | | | | | | | | | | | | |
| Lock Strength | | | | | 2 | | | | | | | | | | | |
| Elasticity | | | | | | 2 | | | | | | | | | | |
| Fixed strength to | | | | | | | | | | | | | | | | |
| PC-Board | | | | | | | 3 | | | | | | | | | |
| Vibration | | | | | | | | _ | | | | | | | | |
| (High Frequency) | | | | | | | | 3 | | | | | | | | |
| Physical Shock | | | | | | | | 4 | | | | | | | | |
| Solder ability | | | | | | | | | 2 | | | | | | | |
| Temperature Life | | | | | | | | | | | | | | | | |
| (Heat Aging) | | | | | | | | | | 3 | | | | | | |
| Humidity | | | | | | | | | | | | | | | | |
| (Steady State) | 4 | | | | | | | | | | 3 | | | | | |
| Thermal Shock | | | | | | | | | | | | 3 | | | | |
| Humidity-Temperature | | | | | | | | | | | | | _ | | | |
| Cycling | | 4 | | | | | | | | | | | 3 | | | |
| Salt Spray | | | | | | | | | | | | | | 3 | | |
| Hydrogen sulfide Gas | | | | | | | | | | | | | | | | |
| (SO ₂) | | | | | | | | | | | | | | | 3 | |
| Resistance to | | | | | | | | | | | | | | | | _ |
| Soldering Heat | | | | | | | | | | | | | | | | 2 |

⁽a) Numbers indicate sequence in which tests are performed.



4. QUALITY ASSURANCE PEOVISIONS

4.1 Qualification Testing

A. Specimen Selection

Plugs and jacks shall be prepared in accordance with applicable Instruction Sheet and shall be selected at random from current production. Each test group shall consist of a minimum of 5 specimens unless otherwise stated.

B. Test Sequence

Qualification inspection shall be verified by testing specimens as specified in figure 3.

4.2 Requalification testing

If changes significantly affecting form, fit or function are made to the product or manufacturing process or controlling industry specification, product assurance, shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality and reliability engineering.

4.3 Acceptance

Acceptance is based on verification that the product meets the requirements of Figure 2. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify the product. If product failure occurs, corrective action shall be taken and samples resubmitted for qualification. Testing to confirm corrective action is required before resubmitted.


4.4 Quality conformance Inspection

The applicable quality inspection plan shall specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification.



PRODUCT SPECIFICATION 108-106087

15 NOV 21 Rev. E



SMT Type




Fig.3

(Cable balk resistance of length X is deducted from measurement value.)

Termination Resistance Measurement Points






Fig.4

Cable Pull-Out、Lock Strength Measurement Method (Fig of DIP Type is omitted.)

Fig.5
Elasticity Measurement Method
(Fig of DIP Type is omitted)




Fig.6

(Fix P.C.Board. Load as shown figure、1 direction per 1 sample.)

Fixed strength to PC-Board Measurement Points

(Fig of DIP Type is omitted)






Fig.7
(Recommend panel protection for bigger strength application)
(Fig of DIP Type is omitted)