

- 1. Scope :
- 1.1 Contents

This specification covers the requirements for product performance, test methods and quality

assurance provisions of Spring Finger 2.05H.

2. Applicable Documents:

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1 AMP Specifications :

- A. 109-5000 : Test Specification, General Requirements for Test Methods
- B. 501-61067 : Test Report
- 2.2 Commercial Standards and Specifications

A. MIL STD. 202

1 of 6

This document is managed by our company, and it is changed if necessary. Please inquire to us about the latest revision. ©Copyright 2007 by Tyco Electronics AMP Korea. All Right Reserved.



- 3. Requirements :
- 3.1 Design and Construction :

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

- 3.2 Materials :
- A. Contact

Material : Copper alloy, Au plating on contact area Ni under plating all over.

3.3 Ratings :

- A. Temperature Rating: 40  $\,^\circ C$  to 85  $\,^\circ C$
- B. Voltage: 12 Volts AC
- C. Current: 0.5A

3.4 Performance Requirements and Test Descriptions :

The product shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Fig. 1. All tests shall be performed in the Room Temperature, unless otherwise specified.



## 3.5 Test Requirements and Procedures Summary

Para.	Test Items	Requirements	Procedures		
3.5.1	Examination of Product	No physical damage	Visual inspection		
			No physical damage		
		Electrical Requirements			
3.5.2	Contact Resistance	Initial, 50mΩ Max.	Mate pad with dry circuit(20mV Max.,		
	(Low Level)		10mA Max.) at 50% WP.		
			(Spring height: 1.725mm)		
			4-wire measurement is required.		
			Measuring condition shown as Fig.4		
		Mechanical Requirements			
3.5.3	Normal Force	Normal force at 1.725mm	Stroke the spring top to 1.725mm product		
		spring Height: 40gf Min	height.		
			Measuring condition shown as Fig.5		
3.5.4	Durability	Contact height should be under	Speed: 600cycle/hour, Total 10000cycle		
		20% from initial height after test	Stroke: 80% of Working position		
		No physical damage and shall	(Spring height 1.53mm)		
		meet requirements of			
		subsequent tests.			
	Solderability	Solderable area shall have a	Peak Temperature : 240℃±5℃,		
		minimum of 95% solder	Reflow Time(230℃ Min) : 45~60 seconds.		
3.5.5		coverage. For lead free solder			
		pot temperature shall be			
		240℃±5℃			
		Environmental Requirement	s		
3.5.6	Damp heat	Contact height should be under	120 hours at Temp. 85℃ ±2℃, R/H 85 ±		
		20% from initial height after test	5%		
		No physical damage and shall	It should be tested at 100% WP		
		meet requirement of	(Spring height 1.4mm)		
		subsequent test.			
3.5.7	Thermal Shock	Contact height should be under	Ta= - 40℃ for 2hour ;Tb= +85℃ for 2hour		
		20% from initial height after test	Total 15cycles.		
		No physical damage and shall	It should be tested at 100% WP		
		meet requirement of	(Spring height: 1.4mm)		
		subsequent test.			
3.5.8	Salt spray	No physical damage and shall	48 hours spray, At temp. 35±2 ℃		
		meet requirement of	R/H 90~95%, Salt NaCl mist 5%		
		subsequent test.	After test wash parts and return to room		
			ambient for 2 hours.		



3.5.9	Resistance to Soldering	No physical damage and shall	Reflow condition shown as Fig.3
	heat	meet requirement of	Peak Temerature: 245℃
		subsequent test.	

Fig 1. (END)

The meaning of text "Physical damage" in the table above is :

- No dimension change
- No pinhole corrosion of plating
- No general corrosion of plating
- No adhesion problem of plating
- No blistering of plating
- No flaking of plating
- No loosen parts
- No cracks on any parts



4. Product Qualification Test Sequence

		Test Group				
Para.	Test Examination	1	2	3	4	5
		Test Sequence (a)				
3.5.1	Examination of Product	1,10	1,3	1,7	1,7	1,5
3.5.2	Contact Height measurement	3,7		2,5	2,5	
3.5.3	Contact resistance	4,8		3,6	3,6	2,4
3.5.4	Normal force	5,9				
3.5.5	Durability	6				
3.5.6	Solderability		2			
3.5.7	Damp heat			4		
3.5.8	Thermal Shock				4	
3.5.9	Salt spray					3
3.5.10	Resistance to Soldering heat	2				

(a) Numbers indicate sequence in which the tests are performed.

Fig. 2



## Spring Finger 2.05H

108-61187

Rev.A2

