

# PRODUCT SPECIFICATION

## 1. SCOPE

This specification contains performance requirements and qualification test procedures and production testing for AMP\* Commercial BNC Dual Crimp Coaxial Plugs.

## 2. APPLICABLE DOCUMENTS

The following documents constitute a part of this specification to the extent specified herein. In the event of conflict between requirements of this specification and the referenced documents, this specification shall take precedence.

### 2.1. Military Documents

- A. MIL-C-17: Cable, Coaxial, Radio Frequency
- B. MIL-STD-1344: Test Methods for Electrical Connectors
- C. MIL-I-17214: Indicator, Permeability, Low-Mu
- D. MIL-C-39012: Connectors, Coaxial, Radio Frequency, General Specification for
- E. MIL-STD-45662: Calibration Systems Requirements

### 2.2. AMP Document

110-12022: Test Report

## 3. REQUIREMENTS

### 3.1. Definitions

For the purpose of this specification, the following definitions shall apply:

#### A. Connector Assembly

A connector assembly consists of a mated plug and jack terminated to their respective cable.

\*Trademark of AMP Incorporated.

Product Code: 3347

				DR D. Benfer 2-11-82		<b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608			
				CHK R. Fisher, Jr. 2-11-82					
				APP R. Laudig 2-11-82					
				NO		108-12044		REV D	LOC B
D	Revise per ECN AJ-5267	<i>FR</i>	12/10 90	PAGE 1 OF 10		TITLE AMP COMMERCIAL BNC COAXIAL PLUGS			
LTR	REVISION RECORD	APP	DATE						

## B. Connector

A connector may be either a plug or a jack, as rotating outer collar for locking purposes.

### (1) Plug

The plug contains the male inner contact and a rotating outer collar for locking purposes.

### (2) Jack

The jack contains the female inner contact and may be either cable or panel mount type.

## 3.2. Design and Construction

Plugs shall be of the captive contact design. Construction and physical dimensions shall be as specified on the applicable product drawing.

## 3.3. Materials

Materials utilized in the manufacture of this product shall be in accordance with the applicable product drawing.

## 3.4. Functional Characteristics

- A. Nominal impedance: 50 ohms
- B. Frequency range: 0 to 4 GHz
- C. Operating voltage @ sea level: 500 volts rms
- D. Operating temperature: -55°C to +85°C

## 4. QUALITY ASSURANCE PROVISIONS

### 4.1. General Provisions

The quality provisions specified herein shall be employed in the manufacturing and testing of this product to ensure that normal production units continue to meet the performance requirements of this specification.

### 4.2. Classification of Test

- A. Qualification Inspection, see Para 5.
- B. Quality Conformance Inspection, see Para 6.

### 4.3. Test Conditions

#### A. Measurements

Measurements shall be made with instruments that have been calibrated and are certified in accordance with MIL-STD-45662.

#### B. Laboratory Conditions

Unless otherwise specified herein, normal laboratory temperature, humidity, and atmospheric pressure shall be considered acceptable for test purposes.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

2

108-12044

REV

D

LOC

B

### C. Coaxial Cable

Coaxial cable used for testing shall be RG-58 C/U in accordance with MIL-C-17.

## 5. QUALIFICATION INSPECTION

### 5.1. Sample Selection

Test samples selected for qualification inspection shall be representative of current production and shall have met the requirements for Quality Conformance Inspection, Para 6.

### 5.2. Test Procedure

Qualification Inspection shall be conducted in accordance with Figure 1 with each test group consisting of 3 connector assemblies. Each test group shall be tested in the sequence specified.

### 5.3. Sample Preparation

After Quality Conformance Inspection, preparation of test samples shall be conducted in accordance with the appropriate Instruction Sheet.

#### A. Test Groups 1 and 3

Connectors shall be assembled to 12 inch lengths of cable with current equalizers applied to the opposite end on both the center conductor and braid. Also, 13 foot length of conductor shall have equalizers attached to the center conductor and braid at both ends. This cable shall be measured for resistance at 1 ampere DC and a milliohms per inch value determined for both center conductor and braid. These values shall be when determining contact resistance in Para 5.5.F.

#### B. Test Groups 2, 4, and 5

Connectors shall be assembled by the laboratory performing R.F. and VSWR measurements.

### 5.4. Acceptance

All test specimens shall meet the requirements specified in the Performance Section of this specification, Para 5.5.

### 5.5. Performance Requirements and Test Methods

Plugs shall be designed to meet the performance requirements specified herein. To verify compliance to this specification, production items shall be tested and shall meet the requirements of this specification. Tests shall be conducted in the order specified in Figure 1.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

3

108-12044

REV

D

LOC

B

# Qualification Inspection

Test or Examination	Test Group and Sequence				
	1	2	3	4	5
Examination of Product	1	1	1	1	1
Force of Engage/Disengage	2,7	2,8	2,22	2	2
Mating Characteristics	3	3,9	3	3	3
Permeability	4	4	4	4	4
Insulation Resistance	5	5	5,16	5	5
Contact Resistance			6,9*,11*,14*		
Dielectric Withstanding Voltage			7,13,17		
Voltage Standing Wave Ratio		6			
R.F. High Potential			19		
Coupling Mechanism Retention			21		
Cable Retention			20		
Corona Level			18		
Temperature Cycling			12		
Moisture Resistance			15		
Connector Durability		7			
Salt Spray Corrosion	6				
Vibration			8		
Physical Shock			10		
R.F. Leakage				6	
R.F. Insertion Loss					6

\*Center contact only

Figure 1

## A. Examination of Product

When test specimens are examined as specified, there shall be no evidence of physical damage or any other defect that could render the specimen unsuitable for test.

### Test Method

Each connector shall be thoroughly examined prior to test to assure proper design, construction, physical dimensions and workmanship.

## B. Force to Engage/Disengage

When tested as specified, the maximum torque required to completely couple or uncouple each connector from its standard mating connector shall not exceed 6.0 inch pounds.

### Test Method

Connectors shall be mated and unmated with their mating standard parts, during which time the torque values required to fully couple and uncouple the connectors shall be measured. The bayonet coupled connectors are fully engaged when the bayonet lugs of the jack have passed the detents in the coupling mechanism of the plug.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

4

108-12044

REV LOC

D

B

### C. Mating Characteristics

When tested as specified, the insertion force of the minimum jack outer contact gage shall not exceed 6 pounds. When inserted into a .324 inch minimum I.D. test ring, a minimum of 2 slotted spring members shall contact the ring within .031 inch of their tip ends.

#### Test Method

The connector plug shall be held rigidly in a suitable fixture. A test ring gage number 953884 (simulates a minimum size jack outer contact) attached to a force indicating device shall be aligned to within a .004 inch T.I.R. of any plane passing through the axis of the contact under test. While engaging the test ring to a depth of .300 inch from the top of the outer contact springs, the total force shall be measured. Also, a .324 inch minimum I.D. test ring shall be inserted and verified to contact a minimum of 2 slotted spring members within .031 inch of their tip ends.

### D. Permeability

When tested as specified, the magnetic properties of the connector shall be less than 2 mu.

#### Test Method

Each connector shall be measured with a permeability indicator conforming to MIL-I-17214.

### E. Insulation Resistance

When tested as specified at 500 vdc, the insulation resistance between the inner contact and the body of the connector shall be 5000 megohms or greater; except after Moisture Resistance it shall be 200 megohms or greater.

#### Test Method

Cabled connectors shall be tested in accordance with MIL-STD-1344, Method 3003. The measurement shall be taken between the inner contact and the outer shell of the assembly.

### F. Contact Resistance

When tested as specified, the contact resistance of mated contacts shall not exceed the following values:

Contact Resistance - Milliohms		
Contact	Initial	After Environment
Center Contact	2.0	3.0
Outer Contact	2.0	N/A
Braid to Body	.2	N/A

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

5

108-12044

REV

D

LOC

B

### Test Method

Contact resistance measurements shall be conducted in accordance with MIL-STD-1344, Method 3004, using a test current of 1 ampere D.C. The contact resistance shall be measured for the center contact, outer contact, and braid-to-body crimps as illustrated in Figure 2. For center contact and braid-to-body measurements, the distance between the probe points shall be measured and an equal distance of cable resistance subtracted from the measurement to obtain actual contact or crimp interface resistance.




Figure 2

### G. Dielectric Withstanding Voltage

When tested, as specified, at 1500 volts rms, there shall be no evidence of dielectric breakdown or flashover.

#### Test Method

Cabled connectors shall be tested in accordance with MIL-STD-1344, Method 3001, Condition I. A test potential of 1500 volts rms, 60 Hz, shall be instantaneously applied between the center contact and outer shell and held for a period of 1 minute.

### H. Voltage Standing Wave Ratio

When tested as specified, the VSWR of a connector shall not exceed 1.30 at frequencies to 4.0 GHz.

#### Test Method

Measurement of connector VSWR shall be conducted in accordance with the method stated in specification MIL-C-39012 or using an Automatic Network Analyzer (discrete frequency point), as applicable. Tests shall be conducted through a frequency range of 0.5 to 4.0 GHz.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE	NO
6	

108-12044

REV	LOC
D	B

### I. R.F. High Potential

When tested, as specified, at 1000 volts rms, 5 MHz, connector assemblies shall show no evidence of dielectric breakdown or flashover.

#### Test Method

Testing shall be conducted with the connectors mated and attached to approximately 2 inches of cable. An R.F. potential of 1000 volts rms, 5 MHz, shall be instantaneously applied between the center contact and the body of the connectors and held for a duration of 1 minute. The R.F. voltage source shall be frequency stabilized and have an approximate pure sine wave output with minimum harmonic content. Test equipment shall contain provisions for detection of disruptive discharge.

### J. Coupling Mechanism Retention

When tested as specified, at 60 pounds minimum, the coupling nut shall not be damaged or dislodged from the connector body.

#### Test Method

The body and coupling mechanism of the plug shall be secured to the lower and upper jaws, respectively, of a tensile testing machine. An axial force applied at a rate of 60 pounds per minute shall be held for 1 minute at a value of 60 pounds.

### K. Cable Retention

When tested as specified, using an axial force of 60 pounds, there shall be no evidence of mechanical failure, breaking, or loosening of parts, or electrical discontinuity.

#### Test Method

The connector shall be rigidly held in the jaws of a tensile machine with a suitable fixture. An axial force of 60 pounds shall be applied to the cable in a direction away from the connector in such a manner that the cable remains unbent and untwisted. The force shall be held for 30 seconds minimum, the removed, and the connector examined for mechanical failure, loosening or breaking of parts, and tested for electrical continuity using a simple low voltage lamp circuit. With the connector still in the fixed position, the cable shall be held at a point 10 times the cable diameter from the connector and bent to an angle of 90° from the axis of the connector, then reversed 180°. This procedure shall be repeated 4 times and the connector re-examined and tested for continuity as described above.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

7

108-12044

REV

D

LOC

B

L. Altitude Corona

When tested, as specified at a simulated altitude of 70,000 feet, mated connectors shall show no evidence of sustained corona discharge in excess of 5 picocoulombs with 375 volts rms, 60 Hz applied.

Test Method

Connector assemblies shall be subjected to a simulated altitude of 70,000 feet. The test circuit used shall be corona free to the extent that a discharge of 5 picocoulombs or less can be measured at the simulated altitude. Connector assemblies shall be tested as follows:

Samples shall be placed in a vacuum chamber and subjected to a simulated altitude of 70,000 feet for 10 minutes. (Note: Exposed cable ends shall be immersed in oil.) At the end of this period, and while still at 70,000 feet (simulated), a 60-Hz test voltage shall be increased until the detector, having a sensitivity of 5 picocoulombs, indicates a sustained corona discharge. The test voltage shall then be immediately reduced until the discharge stabilizes at 5 picocoulombs or less. This final voltage is the corona extinguishing level of the connector.

M. Thermal Shock

Upon completion of testing, as specified, at 85°C and -55°C, connectors shall show no evidence of physical damage.

Test Method

Unmated, cabled connectors shall be subjected to temperature cycling in accordance with MIL-STD-1344, Method 1003, Test Condition A.

N. Moisture Resistance

After the moisture resistance test as specified, connectors shall show no evidence of physical damage. Within 5 minutes after removal from humidity, samples shall be subjected to the Insulation Resistance test as specified in Para 5.5.E. and shall display a resistance of 200 megohms or greater.

Test Method

Mated connector assemblies shall be subjected to 240 hours of Moisture Resistance in accordance with MIL-STD-1344, Method 1002, Type II. Within 5 minutes after removal from the chamber, the connectors shall be tested for Insulation Resistance.

O. Connector Durability

After 500 cycles of mating and unmating as specified, connectors shall meet the requirements for all subsequent testing.

Test Method

Cabled connectors shall be completely mated and unmated a total of 500 times at a maximum rate of 12 cycles per minute.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

8

108-12044

REV LOC

D

B



#### P. Salt Spray

After being subjected to a 5% salt spray environment for 48 hours as specified, there shall be no base metal exposed on the interface or mating surface of the connectors.

##### Test Method

Mated connector assemblies shall be subjected to salt spray corrosion test in accordance with MIL-STD-1344, Method 1001, Test Condition B, using a 5% salt solution concentration. After 48 hours exposure to the salt fog environment, connectors shall be taken from the test chamber, washed in distilled water, brushed, and then air dried for a period of 24 hours at 40°C.

#### Q. Vibration

During the vibration test as specified at 10 to 2000 Hz for 12 hours, there shall be no electrical discontinuities exceeding 1 microsecond duration. Upon completion of testing, there shall be no evidence of physical damage.

##### Test Method

Mated connectors assembled to appropriate cables and mounted as illustrated in Figure 3 shall be subjected to vibration in accordance with MIL-STD-1344, Method 2005, Test Condition 3. During the test, center and outer contacts shall be wired in series and a D.C. current of 0.1 ampere shall be applied. Instrumentation shall be incorporated to detect electrical discontinuities as short as 1 microsecond.




Figure 3

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

9

108-12044

REV

D

LOC

B

## R. Physical Shock

During the shock test as specified (18 shock pulses at 100 G's), there shall be no electrical discontinuities exceeding 1 microsecond duration. Upon completion of testing, there shall be no evidence of physical damage.

### Test Method

Mated connectors shall be mounted as illustrated in Figure 3 and subjected to physical shock in accordance with MIL-STD-1344, Method 2004, Condition G. They shall withstand a total of 18 shock pulses at 100 G's.

## S. R.F. Leakage

When tested at a frequency between 2 and 3 GHz as specified, the total leakage, cable-to-cable, shall not exceed -55 dB minimum.

### Test Method

Mated connector pairs shall be tested for R.F. Leakage in accordance with specification MIL-C-39012 at a frequency between 2 and 3 GHz.

## T. Insertion Loss

When tested at 3 GHz as specified, the insertion loss of a connector shall not exceed .3 dB.

### Test Method

Mated connector pairs shall be tested for R.F. Insertion Loss in accordance with specification MIL-C-38012 at a frequency of 3 GHz.

## 6. QUALITY CONFORMANCE INSPECTION

### 6.1. Sample Selection

Unless otherwise specified, sampling procedures shall be in accordance with MIL-STD-105. Sampling and Acceptable Quality Levels shall be as specified in the applicable AMP Quality Specification. Dimensional requirements shall be in accordance with the applicable product drawing.

**AMP**

AMP INCORPORATED  
Harrisburg, Pa. 17105

PAGE NO

10

108-12044

REV

D

LOC

B