



The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore, TE Connectivity (TE) makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, TE may change these requirements based on the results of additional testing and evaluation. Contact TE Engineering for further details.

MTII JPT MCP SLD 36P Connector

SCOPE

1.1. Content

This specification covers the requirements for product performance, test methods and quality assurance provisions of MTII JPT MCP SLD 36P Connector.

1.2. Qualification

When tests are performed on the subject product line, procedures specified shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

1.3. Qualification Test Results

Successful qualification testing on the subject product line has not been completed. The Qualification Test Report number will be issued upon successful qualification testing.

2. APPLICABLE DOCUMENTS AND FORMS

The following documents and forms constitute a part of this specification to the extent specified herein. Unless otherwise indicated, the latest edition of the document applies.

2.1. TE Documents

- 1743632: Customer Drawing (MTII JPT MCP SLD 36P PLUG)
- 1743636: Customer Drawing (MTII JPT MCP SLD 36P CAP)
- 1743637: Customer Drawing (MTII JPT MCP SLD 36P PLUG COVER)
- 1743693: Customer Drawing (MTII JPT MCP SLD 36P CAP COVER)

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, construction, materials and physical dimensions specified on the applicable product drawing.

3.2. Ratings

Voltage	Temperature	Humidity
12V DC	25±5℃	60±20%

3.3. Test Requirements and Procedures Summary

Unless otherwise specified, all tests shall be performed at ambient environmental conditions.



TEST DESCRIPTION	REQUIREMENT	PROCEDURE
Appearance	No crack, damage, distortion are permitted	Using sense of sight and touch.
CONN engage and disengage force	Max 18 kgf and less	Measure force by inserting and disengaging the connector with terminal assembled at constant 50 mm/min speed. However, remove lock part when measuring disengage force.
Reverse insertion between housings	It shall not be incorrectly inserted by applying force of 20kgf.	Insert the housing with terminal by pushing it in reverse direction with applying 20kgf.
Reverse insertion between terminal and housing	5kgf or more	Crimp cable of maximum size on terminal and then, insert it into housing by the end of insulation.
Engage force between terminal and housing	1.5kgf or less	As shown in the following figure 4-1, measure the weight while inserting terminal into fixed housing at 50mm/min speed. Terminal Housing Figure 4-1>
Strength of HSG lock	Min 10kgf	Combine housing only, fix the one side of housing in completely locked condition, and extend the other side in axial direction and 30 angle direction at a constant speed of 50mm/min. Then measure weight when lock structure is disengaged or destroyed.
HSG lock releasing force	Max 6kgf	Apply force (F) to lock releasing part, and measure weight on the point of A=0. However, cut connector and then perform test at the section in order to secure visibility. A Lock releasing A Figure 5-2>
Terminal retention force	Min 6kgf	Fix the housing after inserting crimped terminals. Extend one line of cable in axial direction at a speed of 50mm/min at a position 50~100mm away from crimped part, and measure weight when terminal is disengaged from the housing.
Voltage Drop	060: Max 3mV/A 110: Max 3mV/A	Measure the circuit voltage drop (V) by sending voltage and current described in the table 5-1 with terminal combined on the connector. Then calculate a voltage drop (VD) in terminal by subtracting cable resistance (L) from the circuit voltage drop (V).

Rev.B **2** of 6



				1)HARNESS versus UNIT:VD =V(L3+L4)			
				Application Open voltage Short circuit current Division			
				Signal circuit 20 ± 5 mV 10 mA ECU, Sensor			
				Power circuit 13 V 1 A Other than the above			
				<table5-1></table5-1>			
Insulation resistance	Min 250 MΩ			Measure resistance between neighbor terminals (figure 5-6), and between terminal and housing surface (figure 5-7) with DC 500V insulation resistance gauge with connector combined.			
Leakage current		Max 1 μ A		Measure it by applying DC 14V between neighboring terminals			
High voltage test	No allowed insulation breakdown			Measured by applying test potential of 1000 V AC between the adjacent contact between the contact and housing.			
Twisting Test - Connector	Appearance	No crack, damage, distortion are permitted		Apply 8kgf force on the end part of combined connector 10 times each in the (front, rear, left, right) directions perpendicular to axial direction.			
Engage and Disengage Endurance Test	M	Лах 10mV/A		Make combine connectors engage and disengage at 100mm/min. Perform it 50 times. (Do not use locking device)			
	Appearance	No crack, damage, e distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and leave it in temperature chamber of -40°C for 120 hours. Make			
	Voltage Drop	Max 1		connector engaged and disengaged 5 times immediately, and drop it onto the concrete surface from 1m height 3 times in the direction of figure 6-1. (Voltage drop & Temperature rise test			
Cold temperature	Insulation	Sealed CONN'R :	Between terminals	perform at normal temperature) :			
test	Resistance	Min 100 MΩ	housing surface				
	Current	Max 1 μ A					
	Leakage	iviax	. /	<figure 6-1=""></figure>			
	Temperature Rise	Max 40°C					
Cold and hot	Appearance	No crack, damage, distortion are permitted		Engage and disengage Connector with terminal assembled 10 times with hands, this repeats 200 CYCLE by below test condition. (Sealed: 120°C, Non-Sealed: 80°C)			
temperature shock test	Voltage Drop	Max 10mV/A		Nomal temperature			

Rev.B **3** of 6



High	Appearance	No crack, damage, distortion are permitted		times with hands, and leave	table 6-1 for 300 hours. Then pick
temperature test	Voltage	Max 10mV/A		High temperature(*)	Connector using part
	Drop			80°C	Non-waterproof connector
	Appearance	No crack, damage, distortion are permitted		times with hands, and leave	ure and 65% relative humidity for
Temperature Humidity Test	Voltage Drop	Max 10mV/A		(°C) 60± 2 °C, 90± 5% FiH 90± 10% 45± 2°C,	96 ± 5% RH 25± 2°C 65± 10% RH -10± 2°C
	Insulation Resistance	Min 100 ^{MΩ}	housing surface	1 CY	CLE
	Current Leakage	Max	x 1 μA	< Figure 6-3 : Tes	st pattern >
Dust Test	Voltage Drop	Max 10mV/A		times with hands, and diffuse 1.5kg Portland ceme for 10 seconds per 15	nector with terminal assembled 10 ent(JIS R5210) with fan (or others) 50mm distance from wall in the and height, with connector
-		No crack	, damage,		engaged and disengaged 10 times k
	Appearance	distortion are permitted		for 40 minutes and then spra	ined state at 120 °C ambient tempera ay water of normal temperature for 2
Waterproof Test	Insulation Resistance	Min 100 ^{MΩ}	housing surface	* JIS D0203 S2 condition: a the waterproof pipe with water	JIS D0203. Repeat 48 cycles of this. attach specimen at 400mm distance for the spray hole or water discharge hole.
	Current Leakage	Max 1 μ A		and rotate waterproof pipe 2	23 times per minute around the axis.
Oil and liquid test	Appearance	No crack, damage, distortion are permitted		times with hands, and performance connector combined. A. Immerge connector in control oil of 50± 2°C ENG oil (SAE) B. Immerge connector in control oil of same connector in control of same	mbined state for 2 hours in mixed

Rev.B **4** of 6



	Voltage Drop	Max 1	0mV/A	liquid (pure product) at rout. D. Immerge connector i washer liquid (pure produck it out. E. Immerge connector in	n combined state for 1 hour in brake normal temperature, and then pick it in combined state for 1 hour in 100% duct) at normal temperature, and then in combined state for 1 hour in 50% at normal temperature, and then pick it	
Ozone Test	Appearance No crack, damage, distortion are permitted		Engage and disengage Connector with terminal assembled 10 times with hands, and samples keep at 40°C and 50±5pphm Ozone for 100hour. Then pick connector out of chamber and dry it for 2hours or more.			
Voltage Drop		Max 10mV/A				
Sulfur (SO2)	Appearance	No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and expose it in combined state to sulfur gas of 40±3°C, density 10ppm, humidity 90~95%, for 24 hours. Then pick connector out of chamber and dry it for 2 hours or more.		
gas test	Voltage Drop	Max 10mV/A				
	Appearance	distort	, damage, ion are nitted	Engage and disengage connector with terminal assembled 10 times with hands, and pout it in 35℃ temperature regulation chamber, spray 5% salty water for 24 hours according to JIS		
	Voltage Drop	Max 10mV/A		Z2371, and, maintain room temperature without spray for 1 hour, Then repeat this four times. Then pick connector out of chamber and dry it at room temperature for 2 hours or more.		
Salt water test	Insulation Resistance Current	Min 100 MΩ	Between terminals housing surface			
	Leakage Appearance	No crack, distort	, damage, ion are nitted	times with hands, and le	connector with terminal assembled 10 eave it in combined state in the f 120°C or 80°C (follows table 7) for 48	
		0.3SQ	Min 6kgf		llowing vibration test. Then measure ording to the method of clause 4.16 for	
		0.75SQ	Min 11kgf	4 hours for X, Y, Z each Division	Condition	
Complex environment endurance	Crimp Tensile Strength	0.5SQ	Min 9kgf	Ambient temperature/humidity	80°C, 90~95% Basic current (Connector electrodes	
test		2.5SQ	Min 25kgf	Applied current Current application	in series.) 120 CYCLE (45 minutes-ON, 15	
		2.5SQ	Min 25kgf	cycle Vibration acceleration	minutes-OFF) 4.4g	
		4.0SQ	Min 37.5kgf	Frequency Vibration time	20Hz ~ 200Hz (sweep time: 3 minutes or less)	
	Voltage Drop	Max 1	0mV/A	Vibration time Connector attaching method	40 hours for X, Y, Z each Test mode A, B, C	

Rev.B **5** of 6



Temperature Rise	e Max 40°C
Instant shor circuit	t Max 10 <i>µ</i> s

3.4. Applied Part No List

TE Part no	Description
1743632	MTII JPT MCP SLD 36P PLUG
1743636	MTII JPT MCP SLD 36P CAP
1743637	MTII JPT MCP SLD 36P PLUG COVER
1743693	MTII JPT MCP SLD 36P CAP COVER

Rev	Description	Date
Α	Released	25.Mar'20
В	Update terminal retention force spec following HKMC spec (ES91500-00 rev 33) min 10kgf → min 6kgf	26.Jan'23

Rev.B **6** of 6