



### NOTE

All numerical values are in metric units [with U.S. customary units in brackets]. Dimensions are in millimeters [and inches]. Unless otherwise specified, dimensions have a tolerance of  $\pm 0.13$  [ $\pm 0.005$ ] and angles have a tolerance of  $\pm 2^\circ$ . Figures and illustrations are for identification only and are not drawn to scale.

## 1. INTRODUCTION

This specification covers the requirements for application of Grace Inertial Connector (GIC) 5.8 connector system includes plug housing, cap housing, receptacle terminal, tab terminal and TPA used in the wire-to-wire interconnections.

The GIC 5.8 connector system is available in 3 positions for a 16 to 14 AWG wire range.

When corresponding with TE Connectivity Personnel, use the terminology provided in this specification to facilitate your inquiries for information. Basic terms and features of this product are provided in Figure 1.




Figure 1

## 2. REFERENCE MATERIAL

### 2.1. Revision Summary

Revision to this application specification include:

- Initial release

### 2.2. Customer Assistance

Reference Product Base Part numbers are stated in Figure 2. Use of these numbers will identify the product line and help you to obtain product and tooling information when visiting [www.te.com](http://www.te.com) or calling the number at the bottom of page 1.

GIC 5.8 connector	
Product Type	PN
Cap Housing	2365949-1
Plug Housing	2365950-1
Rec contact	2365991-1
Tab contact	2365990-1
TPA	2365951-1

Figure 2

### 2.3. Drawings

Customer drawings for product part numbers are available from [www.te.com](http://www.te.com). Information contained in the customer drawing takes priority.

### 2.4. Specifications

Product Specification 108-106515 and Qualification Report 501-106515 provide product performance and test results.

### 2.5. Instructional Material

Instruction sheets (408-series) provide product assembly instructions or tooling setup and operation procedures and customer manuals (409-series) provide machine setup and operating procedures. Instructional material that pertain to this product are:

- [408-8040](#) Heavy Duty Miniature Quick-Change Applicators with Mechanical Feed System
- [408-9640](#) Crimp Quality Monitor (CQM) Applicators for Side-Feed and End-Feed Applications
- [408-10389](#) Ocean Side-Feed Applicators

## 3. REQUIREMENTS

### 3.1. Safety

Do not stack product shipping containers so high that the containers buckle or deform.

### 3.2. Storage

#### A. Ultraviolet Light

Prolonged exposure to ultraviolet light may deteriorate the chemical composition used in the product material.

#### B. Shelf Life

The product should remain in the shipping containers until ready for use to prevent deformation to components. The product should be used on a first in, first out basis to avoid storage contamination that could adversely affect performance.

### C. Reels

When using reeled contacts, store coil wound reels horizontally. When storing partial reeled contacts, the end of the strip should be secured to the flange using a wire tie or similar method.

### D. Chemical Exposure

Do not store product near any chemical listed below as they may cause stress corrosion cracking in the material.

Alkalies	Ammonia	Citrates	Phosphates	Citrates	Sulfur Compounds
Amines	Carbonates	Nitrites	Sulfur Nitrites		Tartrates


## 3.3. Wire Selection and Preparation

The contacts accept stranded wire sizes 16-14 AWG [1.25-2.0 mm<sup>2</sup>] with an insulation diameter range given in Figure 3. The wire must be stripped to the dimension given in Figure 3.



### CAUTION

Care shall be taken during the stripping operation to ensure the conductor is not nicked, scraped, or cut.



CONTACT			WIRE	
TYPE	BASE PART NUMBER	WIRE SIZE (AWG) [mm <sup>2</sup> ]	INSULATION DIAMETER	STRIP LENGTH
Receptacle contact	2365991	16-14 [1.25-2.0]	3.0 - 3.6	4.55-5.31
Tab contact	2365990	16-14 [1.25-2.0]	3.0 - 3.6	4.75-5.51

Figure 3

## 3.4. Crimp Requirements

Contacts must be terminated according to the instructions packaged with the tooling.

### A. Bellmouth

The bellmouth shall be evident and be within the dimensions given in Figure 4.

### B. Cutoff Tab and Burr

The cutoff tab is the remaining portion of the carrier strip after the contact is cut from the strip. The cutoff tab and burr shall not exceed the dimension given in Figure 4.

### C. Wire Barrel Flash

Wire barrel flash is the formation that may appear on both sides of the wire barrel as the result of the crimping process. The wire barrel flash shall not exceed the dimension given in Figure 4.

### D. Wire Barrel Crimp

The crimp applied to the wire barrel portion of the contact is the most compressed area and is most critical in ensuring optimum electrical and mechanical performance of the crimped contact. The crimp must be centered on the closed wire barrel. The crimp must result in an “F” crimp where the wire barrel forms a closed seam with no evidence of loose wire strands or wire strands visible in the seam. The crimp height and width must be within the dimensions given in Figure 4.

#### **E. Insulation Barrel Crimp**

The crimp applied to the insulation barrel of the contact must result in an “O” crimp. The crimp height and width must be within the dimensions provided in Figure 4.

#### **F. Effective Crimp Length**

Effective crimp length shall be defined as that portion of the wire barrel, excluding the rear bell-mouth, fully formed by the crimping tool. Refer to Figure 4.

#### **G. Wire Location**

All conductors must be held firmly inside the wire barrel. No strands can be folded back over the wire insulation. The wire insulation must be inside the insulation barrel but must not enter the wire barrel. The wire insulation and conductors must be visible in the transition area between the wire barrel and insulation barrel. See Figure 4.

#### **H. Wire Brush**

The conductors may extend beyond the wire barrel within the dimensions given in Figure 4.

#### **I. Wire Barrel Seam**

The wire barrel seam must be closed with no evidence of loose wire strands visible in the seam.






#### **K. Twist and Roll**

There should be no twist or roll of the wire barrel or mating portion of the crimped contact that would cause overstress or impair usage. See Figure 4 for allowable limits.


**NOTE**

The effective crimp length depends on the crimping dies used and should not be measured for inspection purposes.

**Note:** Receptacle contact shown, requirements are also applied to tab contact


**Section X-X**

**Avoid Twist and Roll**

**Detail A**

**Section Y-Y**


WIRE SIZE		Receptacle CONTACT								
mm²	AWG	WIRE BARREL CRIMP		INSULATION BARREL			WIRE BRUSH	BELLMOUTH		Length
		HEIGHT ±0.05	WIDTH REF	CRIMP WIDTH	CRIMP HEIGHT	LEGS TOUCH	APPLICATOR	FRONT	REAR	
1.25	16	1.28	2.29 <i>F Crimp</i>	4.10 REF	3.30 REF	0.25 min	0.1 – 1.0	0.30 MAX	0.10-0.90	17.3- 18.0mm
2	14	1.52		<i>O Crimp</i>	3.60 REF					
WIRE SIZE		Tab CONTACT								
mm²	AWG	WIRE BARREL CRIMP		INSULATION BARREL			WIRE BRUSH	BELLMOUTH		Length
		HEIGHT ±0.05	WIDTH REF	CRIMP WIDTH	CRIMP HEIGHT	LEGS TOUCH	APPLICATOR	FRONT	REAR	
1.25	16	1.32	2.54 <i>F Crimp</i>	4.20 REF	3.30 REF	0.3 min	0.1 – 1.0	0.30 MAX	0.10-0.90	25.3- 26.0mm
2	14	1.54		<i>O Crimp</i>	3.60 REF					

Figure 4

## L. Straightness

The force applied during crimping may cause some bending between the crimped wire barrel and the mating portion of the contact. Such deformation is acceptable within the following limits:

The side-to-side bending of the contact may not exceed the limits provided in Figure 5.

The crimped contact, including cutoff tab and burr, shall not be bent above or below the datum line more than the amount given in Figure 4.




Figure 5

## 3.5. Inserting Contact into Housing

Grasp the wire directly behind the contact insulation barre and push the contact straight into the cavity until it bottoms (there should be an audible click). Pull back lightly on the wire to be sure the contact is locked in place. See Figure 6.




Figure 6

### 3.6. Installing TPA

Grasp the TPA and push it straight into the housing until it bottoms (there should be an audible click). Pull back lightly to be sure the TPA is locked in place. See Figure 7.




Figure 7

### 3.7. Mating Connectors

Ensure that the mating connectors have identical number of circuits and a pin contact mating with a socket contact. Align the mating faces of the connectors and push them together until the locking latch fully engages the locking tab (there should be an audible click). Pull back to ensure proper engagement and to prevent any deformation of the locking mechanism. See Figure 8.




Figure 8

### 3.8. Unmating Connectors

To disengage mating connectors, depress latch of plug housing with thumbnail, and pull the connectors apart. See Figure 9.



#### NOTE

*DO NOT pull the connectors by the wires.*




Figure 9

### 3.9. Replacement and Repair

Do not use defective or damaged product. These products cannot be repaired. For replacement information, call the number at the bottom of page 1.



#### 4. TOOLING

Applicators contain the tooling for feeding and crimping strip-form terminals. Automatic machines provide the power to operate the applicator. See Figure 10 for representative images.

Tooling information for product part numbers is available from [www.te.com](http://www.te.com) or by calling the Product Information Center at the number at the bottom of page 1.

Applicators for product part numbers are available from the [Applicator Search Portal](#) on [www.te.com](http://www.te.com) or by calling the Product Information Center at the bottom of page 1.



Ocean Applicator



Semi Automatic Machine

Figure 10

## 5. VISUAL AID

The illustration below shows a typical application of this product. This illustration should be used by production personnel to ensure a correctly applied product. Applications which do not appear correct should be inspected using the information in the preceding pages of this specification and in the instructional material shipped with the product or tooling.




Figure 11 (continued): Visual Aid