M. Spooren V

DR.

LTR

REV. RECORD (REV. 09-91)

DATE

₽29 jan 92

1 of 5

В

AMP

AMP-HOLLAND B.V. 's-Hertogenbosch, The Netherlands.

NO. 108-19078

SHEET REV.

3. REQUIREMENTS:

3.1. <u>Design and Construction:</u>

Tabs shall be of the design and construction and physical dimensions specified on applicable product drawing.

PRODUCT SPECIFICATION

3.2. Materials:

Base Material:

Phos. Bronze

Plating:

Tin-Lead over Nickel

3.3. Ratings:

A. Current:

40 amperes, 8 positions; 30 amperes, 6 positions.

B. Operating temperature

-55°C to 85°C including heating effects of the tab.

3.4. Performance and Test Description:

The product is designed to meet the electrical, mechanical and environmental performance requirements specified in 3.5. as tested per test sequence in 3.6. All tests are performed at ambient environmental conditions per IEC specification 512-1 unless otherwise specified.

3.5. Test Requirements and Procedures Summary.

Para	Test Description	Requirements	Procedure			
3.5.1.	Examination of Product	Meets requirements of product drawing and application specification.	Visual, dimensional and functional per applicable quality inspection plan.			
	ELECTRICAL					
3.5.2.	Contact Resistance	Max. rise 5 m Ω after tests	Measure between body of terminal and connecting printed circuit pad. Max voltage 20 mV Max. current 100 mA IEC 512-2 test 2a			
3.5.3.	Temperature rise vs current	Max. 30°C temperature rise at rated current.	Apply rated current. Measure temperature after stabilization. See fig. 2 IEC 512-3 test 5a.			
3.5.4.	Current cycling	8 ° '	Subject tabs to 250 cycles at 125 % of rated current for 15 minutes "on", 15 min. "off".			

PRODUCT SPECIFICATION

3.5. <u>Test Requirements and Procedures Summary (cont'd).</u>

Para	Test Description	Requirements	Procedure			
	MECHANICAL					
3.5.5.	Insertion Force ACTION PINS	1500 N maximum for 8 position 1125 N maximum for 6 position	Measure force necessary to mount Power Linking Terminal onto test board illustrated in Fig. 1 using proper insertion tooling.			
3.5.6.	Extraction Force ACTION PINS	240 N min. for 8 position 180 N min. for 6 position.	Measure force necessary to remove Power Linking Terminal from printed circuit board.			
× ×	ENVIRONMENTAL					
3.5.7.	Thermal Shock		Subject p.c.b. mounted terminals to 5 cycles of 30 min. at -55°C and 30 min. at +85°C IEC 512-6 test 11d.			
3.5.8.	Dry Heat		Subject p.c.b. mounted terminals to 85°C for 56 days IEC 512-6 test 11i.			

3.6. Test Sequence for Qualification.

Test Group	Test	Paragraph
1	Contact Resistance Temperature rise / current Current cycling Contact resistance	3.5.2. 3.5.3. 3.5.4. 3.5.2.
Insertion force Extraction force (half lot) Thermal Shock Dry Heat Extraction force (half lot)		3.5.5. 3.5.6. 3.5.7. 3.5.8. 3.5.6.

COPYRIGHT 19
BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.

LOC.

SIZE A4

AMP

AMP-HOLLAND B.V. s-Hertogenbosch, The Netherlands.

NO.

108-19078

SHEET 3 OF 5 REV.

PRODUCT SPECIFICATION

4. QUALITY ASSURANCE PROVISIONS.

4.1. Qualification Testing.

Sample selection. A.

Terminals shall be selected at random from current production. Group 1 shall be inserted in p.c. boards in accordance with figure 1, having copper pads of sufficient size for the relevant test current. Tabs linked with Faston (Bronze, tinplated) receptacles and wire 4 mm². length

25 cm min.

10 Terminals with 8 Action Pins and 10 terminals with 6 Action Pins.

Group 2 shall consist of 10 terminals with 8 Action Pins and 10 terminals with 6 Action Pins and testboards in accordance with figure 1. (Insertion during test).

B. Test Sequence.

Qualification inspection shall be verified by testing samples as specified in Paragraph 3.6.

4.2. Requalification Testing.

If changes significantly affecting form, fit or function are made to the product or to the manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality and reliability engineering.

4.3. Acceptance.

Acceptance is based on verification that the products meet the requirements of paragraph 3.5. Failures attributed to equipment, test set-up or operator deficiencies shall not disqualify the product. When product failure occurs, corrective action shall be taken and samples resubmitted for qualification.

Testing to confirm corrective action is required before resubmittal.

4.4. Quality Conformance Inspection.

The applicable AMP quality inspection plan will specify the samples acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with applicable product drawing and this specification.

"E"

"B"

"D"

AMP

AMP-HOLLAND B.V. s-Hertogenbosch, The Netherlands.

NO. 108-19078

SHEET REV. 5 OF 5 B


Plated thru hole see Figure 3

Board material G-10, G-11 or FR-4, FR-5 (3,2 mm Thick. min)

Tab Contact	"B"	"C"	"D"	"E"
6 A.P.	2,54	5,08		7,62
8 A.P.	2,54	5,08	7,62	7,62

Rec'd	Drilled	Plating Thickness		Hole Diameter	
Drill Size	Hole Dia	Copper	Tin/Lead	After Plating	After Reflow
1,60 mm	± 0,025	0,025 0,075	0,004 0,010	1,39 1,54	1,36 1,54

Figure 1
Printed Circuit Test Board



R6-77 (REV.09-91)