



REVISIONS				
P.	LTN	DESCRIPTION	DATE	APVD
A		NEW DRAWING	29SEP2008	GP GM
A1		WARPAGE NOTE CHANGED TO REFER DATUM A	06JUL2015	SS PT




MATERIAL: Cu-ALLOY  
 Basiswerkstoff: Cu-Legierung

TENSILE STRENGTH:  
 Zugfestigkeit:  
 Rm > 600 N/mm<sup>2</sup>

ELECTRICAL CONDUCTIVITY  
 Elektrische Leitfähigkeit:  
 30 Sm/mm<sup>2</sup>

**TAB 1.2x0.63**




**TAB 2.8x0.80**



MATERIAL: Cu-ALLOY  
 Basiswerkstoff: Cu-Legierung

TENSILE STRENGTH:  
 Zugfestigkeit:  
 Rm > 350 N/mm<sup>2</sup>

ELECTRICAL CONDUCTIVITY  
 Elektrische Leitfähigkeit:  
 45 Sm/mm<sup>2</sup>




WARPAGE 1.2mm ALLOWED (DATUM A)  
 Einfall 1.2mm zulaessig (DATUM A)



NOTES:  
 Bemerkungen:

- ALL RADII R0.5 <sub>0.1</sub> EXCEPT AS NOTED  
 unbemessene Radien R0.5 <sub>0.1</sub>
- 1.5 - 3.0 μm Sn OVER / ueber  
 1.3 - 2.2 μm Ni
- 2.0 - 4.0 μm Ag OVER / ueber  
 1.3 - 2.2 μm Ni  
 ANTI TARNISH LUBRICATION WITH THIOLEN  
 Anlaufschutz Thiolen
- 0.8 - 2.0 μm Au OVER / ueber  
 1.3 - 2.2 μm Ni
- TO BE USED TOGETHER WITH REC.HSG 0-1563123-1 WITH SEC.LOCK 0-1563124-1  
 Verwendet mit Buchsengehäuse 0-1563123-1 mit 2ter Kontaktsicherung 0-1563124-1



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN G.PUCKEL 16JAN2008	TE Connectivity														
DIMENSIONS: mm		CHK K.ROTH 16JAN2008															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E.MUMMER 17JAN2008	NAME 10POS MIXED INLINE CONNECTOR INTERFACE SPECIFICATION 8 x MCON1.2 AND 2 x AMP MCP2.8														
<table border="1"> <tr><td>0 PLC</td><td>±0.10</td></tr> <tr><td>1 PLC</td><td>±0.10</td></tr> <tr><td>2 PLC</td><td>±0.05</td></tr> <tr><td>3 PLC</td><td>±0.05</td></tr> <tr><td>4 PLC</td><td>±0.05</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td>±</td></tr> </table>		0 PLC	±0.10	1 PLC	±0.10	2 PLC	±0.05	3 PLC	±0.05	4 PLC	±0.05	ANGLES	±	FINISH	±	APPLICATION SPEC	RESTRICTED TO
0 PLC	±0.10																
1 PLC	±0.10																
2 PLC	±0.05																
3 PLC	±0.05																
4 PLC	±0.05																
ANGLES	±																
FINISH	±																
MATERIAL		WEIGHT	SIZE A1														
		CUSTOMER DRAWING	SCALE 5:1														
			SHEET 1 OF 1														
			REV A1														