


154 POSITIONS HEADER AND RECEPTACLE CONNECTORS FOR ENGINE MANAGEMENT



A6	Cross out test no. 9.2 and 9.3	S.H.	02/02/2024	V.N.	02/02/2024
A 5	5 Revised		16/05/2016	M.G.	16/05/2016
A 4	Revised	M.G.	22/10/2013	M.G.	22/10/2013
A3	Updated 9.10 (Page 10)	M.P.	10/09/2009	M.G.	10/09/2009
A2	Updated P/N's table (Page 4)	M.P.	23/06/2006	O.C.	23/06/2006
A 1	Active ET00-0122-04	M.P.	11/06/2004	O.C.	11/06/2004
rev letter	rev. record	DR	Date	CHK	Date
DR.	DATE	DATE			

This specification is a controlled

document.

This information is confidential and is disclosed to you on condition that no further disclosure is made by you to other than AMP personnel without written authorization from AMP Italia.

Page 1 of 12



INDEX

- 0.1 CONTENTS
- 0.2 APPLICABLE DOCUMENTS
- 0.3 TE SPECIFICATIONS
- 0.4 STANDARD AND SPECIFICATIONS
- 0.5 DESIGN AND CONSTRUCTION
- 0.6 RATINGS
- 0.7 QUALITY ASSURANCE PROVISION
- 0.8 TEST REQUIREMENTS AND PROCEDURES

1.0 PRODUCT EXAMINATION

- 1.1 VISUAL ASPECT
- 1.2 DIMENSIONS AND TOLERANCES
- 1.3 MARKING
- 1.4 MATERIAL AND COVERING

2.0 ELECTRICAL REQUIREMENTS

- 2.1 INSULATION RESISTANCE
- 2.2 DIELECTRIC STRENGHT
- 2.3 VOLTAGE DROP
- 2.4 INITIAL CONTACT RESISTANCE
- 2.5 HIGH TEMPERATURE RESISTANCE WITH CURRENT LOAD
- 2.6 CURRENT OVERLOAD

3.0 MECHANICAL REQUIREMENTS FOR HEADER COUNTERPART

3.1 PIN AND TAB RETENTION FORCE FROM HEADER

4.0 MECHANICAL REQUIREMENTS FOR TERMINALS

- 4.1 SINGLE CONTACT ENGAGING AND SEPARATING FORCE
- 4.2 CONTACT INSERTION FORCE INTO HOUSING
- 4.3 PULL OUT FORCE OF TERMINAL FROM HOUSING
- 4.4 CRIMP TENSILE STRENGHT

5.0 MECHANICAL REQUIREMENTS FOR CONNECTORS

- 5.1 CONNECTORS MATING FORCE
- 5.2 FRONT SEAL RETENTION FORCE
- 5.3 CONNECTORS RETENTION FORCE
- 5.4 MECHANICAL RETENTION OF THE CONNECTORS
- 5.5 POLARIZATION EFFECTIVENESS

Rev. A6 Page 2 of 12



6.0 MECHANICAL REQUIREMENTS FOR SECONDARY LOCK

- 6.1 OPERATING FORCE OF SECONDARY LOCK.
 - 6.1.1 WITH ALL CONTACTS CORRECTLY INSERTED
 - 6.1.2 WITH ONE OR MORE CONTACTS NOT COMPLETELY INSERTED
- 6.2 CONNECTOR MATING FORCE WITH SECONDARY LOCK NOT COMPLETELY CLOSED

7.0 MECHANICAL REQUIREMENTS FOR SLIDES AND LEVERS

- 7.1 SLIDE RETENTION FORCE IN OPEN OR PRE-ASSEMBLED POSITION
- 7.2 LEVER RESISTANCE TO TRASVERSAL LOAD
- 7.3 LEVER LOCKING RESISTANCE FORCE (WITH C.P.A. ACTUATED)

8.0 MECHANICAL REQUIREMENTS FOR C.P.A. DEVICE

- 8.1 C.P.A. ACTUATING FORCE
- 8.1.1WITH LEVER COMPLETELY CLOSED
 - 8.1.1 WITH LEVER NOT COMPLETELY CLOSED
- 8.2 C.P.A. RETENTION FORCE
 - 8.2.1 IN OPEN POSITION
 - 8.2.2 IN CLOSED POSITION

9.0 ENVIROMENTAL REQUIREMENTS

- 9.1 ACCELERATING AGEING
- 9.2 WATERPROOFNESS TEST OF CONNECTION WITH PERIMETRAL GASKET (IPx.4)
- 9.3 WATERPROOFNESS TEST ON HEADER COUNTERPART (IPx5).
- 9.4 HIGH PRESSURE WASHING TEST (IPx9K)
- 9.5 LOW TEMPERATURE RESISTANCE TEST
- 9.6 SALT SPRAY CORROSION TEST
- 9.7 KESTERNICH CORROSION
- 9.8 RESISTANCE TO CHEMICAL AGENTS
- 9.9 RESISTANCE TO ALTERNATING CYCLES OF TEMPERATURE, CURRENT AND HUMIDITY
- 9.10 RANDOM VIBRATIONS IN TEMPERATURE

Rev. A6 Page 3 of 12 LOC I



0.1 CONTENTS

This specification covers the requirements for product performance, test methods and quality assurance provision for the 154 positions header and receptacle connector system for engine management, composed by the parts listed in the following table:

Description	Part number
154 positions Header	284617-1
Socket housing, 60w	284742-1
Socket housing, 94w	284743-1
MQS Clean Body contact, WSR 0.35-0.5 mm ²	968220-1
MQS Clean Body contact, WSR 0.75 mm ²	968221-1
1.5 mm Clean Body contact, WSR 0.5 mm ²	1452158-1
1.5 mm Clean Body contact, WSR 0.75-1.5 mm ²	1241608-1
AMP MCP2.8K, SWS, WSR 0.5-1 mm ²	1241394-1
AMP MCP2.8K, SWS, WSR > 1-2.5 mm ²	1241396-1
Single wire seal for AMP MCP2.8K	963292-1,963293-1,963294-1 (For the assignment of the individual seals to the various wire cross-sections, see the drawing of the individual seal)

0.2 APPLICABLE DOCUMENTS

Product drawings have to be considered part of this specification. In case of conflicts between specification and referenced documents, this specification shall take precedence.

0.3 TE CONNECTIVITYSPECIFICATIONS

A. 109-1 Test Specification, General Requirements for Test Methods

B. 108-18030 Product Specification, Micro-Quadlock-System

C. 108-18717/108-18513-0 Product Specification, AMP MCP 2.8

0.4 STANDARD AND SPECIFICATIONS

A. Low Voltage Stranded Cables for Automobiles according to FIAT normation table Nr. 91107/05 and 91107/17.

B. FIAT General Specification for Connectors 9.91320/02 Ed. 7.

0.5 DESIGN AND CONSTRUCTION

Product shall comply with design, construction and physical dimensions specified in the applicable product drawing.

Rev. A6 Page 4 of 12 LOC I



0.6 RATINGS

- **A.** TEMPERATURE RATING: -40°C TO +125 °C (including the temperature increasing due to working current flow).
- **B**: MAXIMUM OPERATING VOLTAGE: 24 V dc. For application at higher voltage please contact TE Connectivity
- C. MQS Clean Body CURRENT RATING:

7,5 A max. with 0.75 mm² wire 6,0 A max. with 0.50 mm² wire 3,5 A max. with 0.35 mm² wire

D. 1.5 mm MQS Clean Body CURRENT RATING:

14,0 A max. with 1.50 mm² wire 11,0 A max. with 1.00 mm² wire 9,0 A max. with 0.75 mm² wire 6,0 A max. with 0.50 mm² wire

E. AMP MCP2.8K CURRENT RATING:

20,0 A max. with 2.50 mm² wire 14,0 A max. with 1.50 mm² wire 11,0 A max. with 1.00 mm² wire 6,0 A max. with 0.50 mm² wire

Current rating per wire section a.m. are according to Fiat spec. 91107/05, 91107/17

0.7 QUALITY ASSURANCE PROVISION

A. SAMPLES PREPARATION

The test samples to be used for the test shall be prepared by random selection from the current production and the contact shall be crimped in accordance with the Application Specifications: 114-18021, 114-18286, 114-18387/114-18148.

No sample shall be reused, unless otherwise specified.

B. TEST CONDITION:

All the tests shall be performed under any combination of the following test condition, unless otherwise specified:

Room temperature: 23±5°CRelative humidity: 45÷70%

Atmospheric pressure: 860÷1060 mbar

Rev. A6 Page 5 of 12 LOC I



0.8 TEST REQUIREMENTS AND PROCEDURES

#	Test	Procedures	Requirements									
PRODUCT EXAMINATION												
1.1	Visual aspect	Visual Inspection	Compliance with relevant drawings									
1.2	Dimensions and tolerances		Following relevant drawings									
1.3	Marking	Visual Inspection	Supplier's indications must be clear and legible									
1.4	Materials and coverings		Following relevant drawings									
		ELECTRICAL REQUIREM	ENTS									
2.1	Insulation resistance	Applied voltage 500 V dc between one contact and the others short circuited.	≥10MΩ									
2.2	Dielectric strength	>1000V ac for 1 minute Test between adjacent circuits of mated connectors	Neither creeping discharge nor flash over shall occur									
		Between a point of the wire at 1 cm from the connector edge and a point	On new contacts and after ten in/outs									
2.3	Voltage Drop	very close to the header edge, at the nominal current for each wire size.	Class of terminal types									
		(Termination resistance is obtained	0.63 1.5 2.8									
		after subtraction of the resistance of wire used for termination)	≤5mV/A ≤4mV/A ≤4mV/A									
	Contact	On terminal without housing mated.	Class of terminal types									
2.4	Resistance	Placed the measure points in the transition zones	0.63 1.5 2.8									
			$\leq 4 \text{m}\Omega$ $\leq 3 \text{m}\Omega$ $\leq 3 \text{m}\Omega$									
2.5	High temperature resistance with current load.	On 6 adjacent ways contemporary. 5 temperature cycles composed of: - 5 hours in oven at 80 ±2°C without air ventilation, with rated current according to wire size. (see point 0.6) - 2 hours in freezing cell at -30°C, without current. (thermocouple placed on transition zone of each contact)	 Over temperature in transit area: ≤45°C (at the end of the first test cycle) Voltage drop within the original limit specified No damage Over temperature in transit area: ≤50°C (at the end of 5 test cycles) 									
2.6	Current overload	On one pair of mated contacts without housing: Test current 1.5 time nominal current (See par. 0.6) - Duration 500 cycles composed of: 45 min current ON 15 min current OFF (Thermocouple placed between contact body and wire barrel)	 Over temperature in transit area: ≤70°C Voltage drop: a max 50% decay is allowed from the original prescribed limit 									

Rev. A6 Page 6 of 12 LOC I



#	Test	Procedures		Requiremer	nts							
MECHANICAL REQUIREMENTS FOR HEADER												
	Pin and tab	Apply an axial force on pin and tab in	Clas	ss of terminal	types							
3.1	retention force in	order to remove them from the header.	0.63	1.5	2.8							
	header	Operation speed: 25 mm/min	≥25N	≥40N	≥50N							
	MECHAN	ICAL REQUIREMENTS FOR FI	EMALE TERN	MINALS								
			Clas	types								
	Cinale contact		0.63	1.5	2.8							
4.1	Single contact mating and un-	Operation speed: 50 mm/min (with relevant counterpart pin and	On. 1 st	mating and ι	ın-mating							
4.1	mating force	tabs)	≤5N	≤5N	≤15N							
	mating force		C	n 10 th un-ma	ting							
			≥2N	≥2.5N	l ≥4N							
	Contact insertion	Insert contacts into the cavities with	Clas	ss of terminal	types							
4.2	force into housing	operating speed of 25 mm/min. The housing has to be mounted on a	0.63	1.5	2.8							
	(crimp contacts)	self aligning platform.	≤15N	≤20N								
				ss of terminal								
	Pull-out force of		0.63	1.5	2.8							
4.3	contacts from housing. (crimp contacts)	Pulling wires axially with an operating	Wit	k only								
7.0		speed of 50 mm/min	≥30N	≥60N								
			with prim	ondary lock								
			≥60N	≥100N								
		Apply a pulling force to the terminal correctly crimped on wire for 1 minute.		s of wire sizes								
4.4	Crimp tensile		0.5 0.75		1.5 2.5							
	MEOL	Operating speed: 25÷50 mm/min	≥70N ≥90N		155N ≥235N							
	IVIECT	IANICAL REQUIREMENTS FOR										
	Cannastar mating		• ≤ 70 N at 1st mating / un-mating									
5.1	Connector mating and un-mating	With correspondent header counterpart all assembled moving the lever with an	for connectors equipped with force reduction device (lever, slide, etc.).									
0.1	force	operating speed of 50 mm/min	 Max. 50% decay is admitted after thermal cycles. 									
5 0	Front seal	Pull front gasket with proper fixture at										
5.2	retention force	speed of 25 to 100 mm/min		> 15 N								
		With relevant Header counterpart										
5.3	Connector	assembled, apply a pulling force axially to the female connector mating	> 120 N									
0.0	retention force	direction, with an operating speed of	> 120 14									
		60±10 mm/min Connector fully loaded mated with the	a Naunaa	unling of con-	acetor not							
		corresponding header counterpart (wire	No unco even par	upling of con	nector, not							
	Mechanical	bundle fixed to the shell by a tie) Operating speed: 100 mm/min.			ment from							
5.4	retention of the	Operating speed. 100 mm/mm.	 No extraction, detachment from connection, opening of electric 									
	connector	7.pp., a.: a.: a.: pa.: 01. 10aa 0. 120 11.		contact.								
		the cables bundle in all directions of the semi-sphere over the wire exit plane.	No damage on the coupling									
			system	J = 11 2 30	i. 3							
		A										
	Polarization	Assembled connectors must withstand without mating the counterpart with the	No coupling of connector or closing									
5.5	effectiveness	incorrect polarization.	of electrical contact for a force <									
			100 N									
	I .		1									

Rev. A6 Page 7 of 12 LOC I



#	Test	Procedures	Requirements								
	MECHAI	NICAL REQUIREMENTS FOR S	ECONDARY L	.OCK							
	Closing force of		Class	s of terminal t	ypes						
6.1 6.1.1	secondary lock with all terminals	Apply increasing load parallel to the operating direction and measure force	0.63	0.63 1.5							
0	correctly inserted	to actuate.	≤ 30N	≤ 40N	≤ 40N						
	Closing force of secondary lock		Class	s of terminal t	ypes						
6.1 6.1.2	with one or more contacts not	Apply increasing load parallel to the operating direction and measure force to actuate.	0.63	2.8							
	correctly inserted		≥ 80 N	≥ 120 N	≥ 120 N						
6.2	Connector mating force with secondary lock not completely closed	Apply increasing load parallel to the operating direction and measure force to actuate.	Apply increasing load parallel to the operating direction and measure force ≥ 100								
		IICAL REQUIREMENTS FOR S	LIDES AND LI	EVER							
7.1	SLIDE retention force in pre- assembled position	Pull slide axially to its operating direction with increasing force	≥ 50 N								
7.2	LEVER resistance to transversal load	Apply 100 N transversal load to the lever positioned open and at the middle of its operating angular displacement. Apply 60 N transversal load to the lever in all other positions of its operating angular displacement.	 No lever stepping and/or damages; permanent deformations are allowed if they do not affect the lever operation 								
7.3	LEVER locking resistance force (without C.P.A. device)	Apply a load to the lever with connection completely closed (without C.P.A. device) in order to open it	≥ 70 N								
	,	HANICAL REQUIREMENTS FOR	R C.P.A DEVIC	E							
8.1 8.1.1	C.P.A. device actuating force (with lever correctly closed)	C.P.A. device actuating force (with lever with lever completely closed, apply a load to C.P.A. device in order to close it (direction of load should be parallel to the C.P.A. with female connector lever completely closed, apply a load to C.P.A. device in order to close it (direction of load should be parallel to the C.P.A.									
8.1 8.1.2	C.P.A. device actuating force (with lever not correctly closed)	With female connector lever NOT completely closed, apply a load to C.P.A. device due to close it (direction of load should be parallel to the C.P.A. displacement direction.)	≥ 80 N								
8.2 8.2.1	C.P.A. device retention force (in open position)	With connector equipped with cover and C.P.A., apply a pulling force to the C.P.A. in order to remove it from the cover	ped with cover ling force to the								
8.2 8.2.2	C.P.A. retention force (in closed position)	With connector equipped with cover and C.P.A. apply a load to the C.P.A. device in order to move it in its prelocking position	≤ 20 N								

Rev. A6 Page 8 of 12 LOC I



#	Test	Procedures	Requirements							
		ENVIROMENTAL REQUIRE	MENTS							
9.1	Accelerating aging	On mated connector submitted to the following cumulative tests: A- 5 cycles composed of: 2 hrs at 125°C ±2°C 2 hrs at -30°C ±2°C B- 5 cycles composed of 2 hrs at 125°C ±2°C 2 hrs at 40°C ±2°C and 90-95% r.h. 2 hrs at -30°C ±2°C C-200 hrs at 125°C	 No deformation, scraping or breaking; color variations are allowed on. plastic material Insulation resistance and discharge voltage within the limits specified. Voltage drop max 50% decay is allowed from the original limit. Initial contact resistance and resistance of short-circuit device: a max 50% decay is allowed from the original limit. After 10 mating and un-mating: characteristics and mechanical tests within the original limits specified with 50% max variation allowed 							
9.2	Waterproof test of connection with peripheral gasket. (IP x.4)	Test according to IEC 529 par. 14.2.4 Duration: 4 hours Samples mated with relevant counterpart. This test must be carried out after cumulative aging test (par. 9.1) This test must be carried out also en Header mating side without female counterparts.	 Insulation resistance and discharge voltage within the prescribed limits No water infiltration inside the connector No water infiltration through the pin and tab cavities (For test on Header only) 							
9.3	Waterproof test	Test according to IEC 529 par. 14.2.5 Duration: 3 min.								
	(on relevant	The header counterpart must be	No control in City and a subsequent the subsequent							
	header counterpart	submitted to water jet on female counterpart mating side; the other side	No water infiltration through the pin and tab cavities							
	only).	must be close and sealed. This test must be carried out after	and gavillos							
	(IP x.5)	cumulative aging test (par. 9.1)								
9.4	High pressure washing test (on connection fully loaded and closed). (IP x.9K)	Test according to <u>DIN 40050</u> index 9K Duration: 30 sec for each nozzle. Samples: mated with relevant counterpart. Submit the connection completely loaded with terminals, fixed with tie, to the cumulative action of the four nozzle. This test must be carried out after cumulative ageing test (par. 9.1)	No water infiltration inside the connector							
9.5	Low temperature resistance test	Keep mated samples to -40°C for 2 hrs, move to 0°C in a time of 3 min. max and let stabilize, then un-mate and re-mate the connectors one time	No breaking between connection parts							
9.6	Salt spray corrosion test	150 hrs of exposure to salt mist at 35°C ±2°C, 5% of NaCl, pH 6.5÷7.2 class 2 (mated connector)	Voltage drop ≤ specified limits for new contact increased of 100%							
9.7	Kesternich corrosion test	4 cycles composed of: 8 hrs of exposure to an atmosphere with 0.66 % of SO2 at +40°C ±2°C (method acc. To DIN 50118) 16 hrs in free air (mated connectors)	Voltage drop ≤ specified limits for new contact increased of 100%							


Rev. A6 Page 9 of 12 LOC I



#	Test	Procedures	Requirements
9.8	Chemical agents' resistance test	Test complete, mated connectors with 3 min. of immersion in the following fluids (not cumulative test, use different samples for each fluid): - Gasoline at 23°C ± 5°C - Cleaning agent at 23°C ± 5°C - Break fluid at 50°C ± 5°C - Anti-freeze mixture at 23°C ± 5°C - ASTM1 oil/engine oil at 100°C ± 3°C - Unleaded engine fuel at 23°C ± 5°C - Transmission fluid at 100° C ± 3°C	 No damages, deformations, cracks, breakage on the parts. Contact retention in housing, connector mating / un-mating forces according to the specified limits.
9.9	Resistance to alternating cycles of temperature, current and humidity	Submit mated samples to the following cumulative cycles: • 4 hrs at +80°C with current flow on 6 adjacent contacts at the maximum current for the wire size 45 min ON and 15 min. OFF. • 4 hrs at 40°C with 95% U.R. without current. • 4 hrs at -40°C without current	 No damages, deformations, cracks, breakage on the parts. Insulation resistance, dielectric strength, voltage drop, Initial contact resistance, within the limits specified.
9.10	Random vibration in temperature	Temperature sequence during vibration as follows: -6h at +85°C -4h at +40°C -2h at -25°C PSD curve as per picture 1 Duration: 180 hours / 1 axis only	 No electric continuity missing (R>100Ω in >1µs time) during test. Voltage drop: a max. 50% decay is allowed from the original limit Mechanical characteristics within the prescribed limits with 50% variation allowed

Rev. A6 Page 10 of 12 LOC I





Rev. A6 Page 11 of 12 LOC I



TABLE I PRODUCT QUALIFICATION TEST SEQUENCE TEST GROUPS

ITEM	DESCRIPTION	Α	В	С	D	Е	F	G	Н	I	J	K	L	М	N	0	Р	Q	R
1.1	Visual aspect	1	1,9	1,3	1,5	1,5	1,6	1,10		1,9	1,5	1,9	1,8	1,5	1,5	1,5	1,5	1,6	
1.2	Dimensions and tolerances	2																	
1.3	Marking	3																	
1.4	Materials and coverings	4																	
2.1	Insulation resistance		4							8		5	2,6					4	4
2.2	Dielectric strength		5							7		6	3,7					5	5
2.3	Voltage drop		3,8		2,4	2,4				2,5	2,4	4		2,4	2,4				
2.4	Contact resistance		2,7							3,6		3					2,4		
2.5	High temperature resistance with current load				3														
2.6	Current over-load					3												П	
3.1	Pins and tabs retention force in header						2											П	
4.1	Single contact engaging and separating		6						2									П	
4.2	Contact insertion force into housing						3											П	
4.3	Pull out force of terminal from housing						4									4		П	
4.4	Crimp tensile			2														П	
5.1	Connectors mating force							2				7				3		Ħ	
5.2	Front seal retention force						5											11	
5.3	Connector retention force								3									11	
5.4	Mechanical retention of the connector							3										I	
5.5	Polarization effectiveness							4										I	
6.1.1	Operating force of secondary lock with all contacts correctly inserted							5										V	
6.1.2	Operating force of secondary lock with one contact not correctly inserted							6											
6.2	Connector mating force with secondary lock not completely closed							7				8							
7.1	Slide retention force in open or pre- assembled position							8											
7.2	Lever resistance to transversal load							9											
7.3	Lever locking resistance force (with C.P.A. device actuated)								4										
8.1.1	C.P.A. actuating force with lever completely closed								5										
8.1.2	C.P.A. actuating force with lever NOT completely closed								6									\parallel	
8.2.1	C.P.A. retention force in open position								7									Ш	
8.2.2	C.P.A. retention force (closed position								8									Ш	
9.1	Accelerating aging											2	4					2	2
9.2	Waterproof test of connection with peripheral gasket (IPx.4)												5					Ш	
9.3	Waterproof test on header counterpart																	3	
9.4	(lpx.5)																	Н	3
9.4	High pressure washing test (9k) Low temperature resistance test										3							Н	+ 3
9.6	Salt spray corrosion test										J			3				Н	+
9.6	Kesternich corrosion													3	3				+
9.7	Resistance to chemical agents														J	2			+-
	Resistance to chemical agents Resistance to alternating cycles of																		
9.9	temperature, current and humidity Random vibrations in temperature									4							3		
9.10	nandom vibrations in temperature																ა		

Rev. A6 Page 12 of 12 LOC I