

**Series 50 Power Connector****DESIGN OBJECTIVES**

The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore Tyco Electronics makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, Tyco Electronics may change these requirements based on the results of additional testing and evaluation. Contact Tyco Electronics Engineering for further details.

**1. SCOPE**

## 1.1. Content

This specification covers performance, tests and quality requirements for the Tyco Electronics Series 50 Power Connector. This power product is a two position hermaphroditic connector system capable of handling up to 50 amperes using 6 AWG wire. Contacts are available in stamped and formed and cold headed to accommodate 6 to 12 AWG wire.

## 1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 1 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

**2. APPLICABLE DOCUMENTS**

The following documents form a part of this specification to the extent specified herein. Unless otherwise specified, the latest edition of the document applies. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

## 2.1. Tyco Electronics Documents

- 109-197: AMP Test Specifications vs EIA and IEC Test Methods
- 114-13071: Application Specification
- 501- : Qualification Test Report

## 2.2. Industry Standard

EIA-364: Electrical Connector/Socket Test Procedures Including Environmental Classifications

**3. REQUIREMENTS**

## 3.1. Design and Construction

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

## 3.2. Materials

Materials used in the construction of this product shall be as specified on the applicable product drawing.

**DESIGN OBJECTIVES 10Apr03**

3.3. Ratings

- Voltage: 600 volts AC
- Current: 50 amperes
- Temperature: -20 to 105°C

3.4. Performance and Test Description

Product is designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1. Unless otherwise specified, all tests shall be performed at ambient environmental conditions per EIA-364.

3.5. Test Requirements and Procedures Summary

Test Description	Requirement	Procedure
Initial examination of product.	Meets requirements of product drawing.	EIA-364-18. Visual and dimensional (C of C) inspection per product drawing.
Final examination of product.	Meets visual requirements.	EIA-364-18. Visual inspection.
<b>ELECTRICAL</b>		
Low level contact resistance.	200 milliohms maximum initial with a 31.75 mm [1.25 in] length of 6 AWG wire.	EIA-364-23. Subject specimens to 100 milliamperes maximum and 20 millivolts maximum open circuit voltage. See Figure 3.
Temperature rise vs current.	30°C maximum temperature rise at specified current.	EIA-364-70, Method 1. Stabilize at a single current level until 3 readings at 5 minute intervals are within 1°C. See Figure 4.
<b>MECHANICAL</b>		
Vibration, sinusoidal.	No discontinuities of 1 microsecond or longer duration. See Note.	EIA-364-28, Test Condition I. Subject mated specimens to 10-55-10 Hz traversed in 1 minute with 1.5 mm [.06 in] maximum total excursion. 2 hours in each of 3 mutually perpendicular planes. See Figure 5.
Mechanical shock.	No discontinuities of 1 microsecond or longer duration. See Note.	EIA-364-27, Method A. Subject mated specimens to 50 G's half-sine shock pulses of 11 milliseconds duration. 3 shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks. See Figure 5.

Figure 1 (cont)

**DESIGN OBJECTIVES 10Apr03**

Test Description	Requirement	Procedure
Durability.	See Note.	EIA-364-9. Mate and unmate specimens for 10000 cycles at a maximum rate of 400 cycles per hour. See Figure 2.
Mating force.	71.17 N [16 lbf] maximum.	EIA-364-13. Measure force necessary to mate specimens at a maximum rate of 12.7 mm [.5 in] per minute.
Unmating force.	31.14 N [7 lbf] minimum.	EIA-364-13. Measure force necessary to unmate specimens at a maximum rate of 12.7 mm [.5 in] per minute.
Contact insertion force.		EIA-364-5. Measure force necessary to insert individual contacts into the housing at a maximum rate of 12.7 mm [.5 in] per minute.
Contact retention.		EIA-364-29. Measure force necessary to remove individual contacts from the housing at a maximum rate of 12.7 mm [.5 in] per minute.
ENVIRONMENTAL		
Humidity-temperature cycling.	See Note.	EIA-364-31, Method III. Subject specimens to 10 cycles (10 days) between 25 and 65°C at 80 to 100% RH.
Temperature life.	See Note.	EIA-364-17, Method A, Test Condition 4, Test Time Condition C. Subject mated specimens to 105°C for 500 hours.

**DESIGN OBJECTIVES 10Apr03**

**NOTE**

*Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in the Product Qualification and Requalification Test Sequence shown in Figure 2.*

Figure 1 (end)

3.6. Product Qualification and Requalification Test Sequence

Test or Examination	Test Group (a)		
	1	2	3
	Test Sequence (b)		
Initial examination of product	1	1	1
Low level contact resistance		2,5,8,10,13,16,18,21,23,26	2,8,12
Temperature rise vs current		3,27	
Vibration, sinusoidal		19(c)	
Mechanical shock		24	
Durability		4(e),7(d),9(e),12(d),15(d),17(e),20(d),22(e),25(d)	5(f),9(g)
Mating force	3		3,6,10
Unmating force	4		4,7,11
Contact insertion force	2		
Contact retention	5		
Humidity-temperature cycling		14	
Temperature life		6(h),11(h)	
Final examination of product	6	28	13

- NOTE**
- (a) See paragraph 4.1.A.
  - (b) Numbers indicate sequence in which tests are performed.
  - (c) Discontinuities shall not be measured. Energize at 18°C level for 100% loadings per Quality Specification 102-950.
  - (d) 1 cycle.
  - (e) 1000 cycles.
  - (f) 4000 cycles.
  - (g) 6000 cycles.
  - (h) 50% of the total cycle time.

Figure 2

4. QUALITY ASSURANCE PROVISIONS

4.1. Qualification Testing

A. Specimen Selection

Specimens shall be prepared in accordance with applicable Instruction Sheets and shall be selected at random from current production. All test groups shall each consist of a minimum of 5 specimens.

B. Test Sequence

Qualification inspection shall be verified by testing specimens as specified in Figure 2.

**DESIGN OBJECTIVES 10Apr03**

**4.2. Requalification Testing**

If changes significantly affecting form, fit or function are made to the product or manufacturing process, product assurance shall coordinate requalification testing, consisting of all or part of the original testing sequence as determined by development/product, quality and reliability engineering.

**4.3. Acceptance**

Acceptance is based on verification that the product meets the requirements of Figure 1. Failures attributed to equipment, test setup or operator deficiencies shall not disqualify the product. If product failure occurs, corrective action shall be taken and specimens resubmitted for qualification. Testing to confirm corrective action is required before resubmittal.

**4.4. Quality Conformance Inspection**

The applicable quality inspection plan shall specify the sampling acceptable quality level to be used. Dimensional and functional requirements shall be in accordance with the applicable product drawing and this specification.

**TBD**

Figure 3  
Low Level Contact Resistance Measurement Points

**DESIGN OBJECTIVES 10Apr03**




Figure 4A  
Current Carrying Capability

Percent Connector Loading	Wire Size AWG			
Single Contact				
50				
100				

**NOTE**

To determine acceptable current carrying capacity for percentage connector loading and wire gage indicated, use the Multiplication Factor (F) from the above chart and multiply it times the Base rated Current for a single circuit at the maximum ambient operating temperature shown in Figure 4A.

Figure 4B  
Current Rating

**DESIGN OBJECTIVES 10Apr03**

**TBD**

Figure 5  
Vibration & Mechanical Shock Mounting Fixture

**DESIGN OBJECTIVES 10Apr03**