


For application requirements, please refer to application specification 114-133061 and product specification 108-133061. Find more information at www.te.com/CoolSplice.


PART NUMBER	BUTTON A		BUTTON B		SEALING LEVEL
	WIRE RANGE	COLOR	WIRE RANGE	COLOR	
2213600-1	14 - 12 AWG	YELLOW	16 - 14 AWG	BLUE	SEALED IPX5, IPX7 & IPX8 •
	2.5 - 4.0 mm ²		1.5 - 2.5 mm ²		
2213600-2	14 - 12 AWG	YELLOW	18 - 16 AWG	RED	
	2.5 - 4.0 mm ²		0.75 - 1.5 mm ²		
2213600-3	16 - 14 AWG	BLUE	18 - 16 AWG	RED	
	1.5 - 2.5 mm ²		0.75 - 1.5 mm ²		
2213600-4	14 - 12 AWG	YELLOW	16 - 14 AWG	BLUE	NON-SEALED IP20
	2.5 - 4.0 mm ²		1.5 - 2.5 mm ²		
2213600-5	14 - 12 AWG	YELLOW	18 - 16 AWG	RED	
	2.5 - 4.0 mm ²		0.75 - 1.5 mm ²		
2213600-6	16 - 14 AWG	BLUE	18 - 16 AWG	RED	
	1.5 - 2.5 mm ²		0.75 - 1.5 mm ²		

COOLSPICE CONNECTOR LARGE WIRE 2213600-*




WIRE TERMINATION STEP


STEP 1: INSERT THE WIRE



STEP 2: PUSH DOWN THE BUTTON WITH A STANDARD PAIR OF PLIERS



STEP 3: REPEAT 1&2 AND READY TO GO!



SLIDE SIDE-BY-SIDE FOR STACKING




• IPx8 allows water resistance for 2 hours and 1 meter under water.

For application requirements, please refer to application specification 114-133061 and product specification 108-133061. Find more information at www.te.com/CoolSplice.


PART NUMBER	BUTTON A		BUTTON B		SEALING LEVEL
	WIRE RANGE	COLOR	WIRE RANGE	COLOR	
2213800-1	18 AWG	GREEN	18 AWG	GREEN	NON-SEALED IP20
	0.75 mm ²		0.75 mm ²		
2213800-2	18 AWG	BLUE	18 AWG	BLUE	SEALED IPX5, IPX7 & IPX8●
	0.75 mm ²		0.75 mm ²		
2213800-3	22 - 20 AWG	GREEN	22 - 20 AWG	GREEN	NON-SEALED IP20
	0.34 - 0.52 mm ²		0.34 - 0.52 mm ²		
2213800-4	22 - 20 AWG	BLUE	22 - 20 AWG	BLUE	SEALED IPX5, IPX7 & IPX8●
	0.34 - 0.52 mm ²		0.34 - 0.52 mm ²		

COOLSPICE CONNECTOR 2213800-*




WIRE TERMINATION STEP

STEP 1: INSERT THE WIRE



STEP 2: PUSH DOWN THE BUTTON WITH A STANDARD PAIR OF PLIERS



STEP3: REPEAT 1&2 AND READY TO GO!



● IPX8 allows water resistance for 2 hours and 1 meter under water.