
AMP INCORPORATED HARRISBURG, PA 17105

AMP* SIZE 1 COAXIAL CONNECTORS FOR ARINC CONNECTOR APPLICATIONS IS 2348-2

RELEASED 6-25-92

TOOLING 1 800 722-1111 AMP FAX 1 800 522-6752



4.74

[.187]

4.74

11.09

[.437]

12.7

[.500]

Fig. 1

73-111A

IS 2336

IS 2331

1. INTRODUCTION

SOCKET

SOCKET

225831-5

225831-6

This Instruction Sheet (IS) covers AMP Size 1 coaxial connectors (pin and socket assemblies) listed in Figure 1. which can be used in any ARINC 404 (IS 7482), ĀRINC 600 (IS 6762), or MIL-C-81659 connector containing an insert for Size 1 coaxial connectors. For information on the

FILECA

F1703-63

RG-393

7.92

[.312]

12.7

[.500]

use of tooling, see the AMP Instruction Sheet supplied with the tooling, as listed in Figure 1.

NOTE

220045-2

220015-1

All dimensions are in metric units [with inch equivalents in brackets].

220045-2

220015-1

^[.187] ● M22520/2-01 TOOL AND K350 POSITIONER CAN BE ORDERED FROM: DANIELS MANUFACTURING COMPANY, **BLOOMFIELD HILLS, MI 48013**

2. ASSEMBLING CONNECTORS

A. Semirigid Cable

- 1. Strip the cable to the dimensions shown in Figure 1.
- 2. Crimp the center contact to the cable conductor using the tool listed in Figure 1.
- 3. Seat the crimped center contact in the body, then crimp the back shell with the tool listed in Figure 1.

B. Flexible Cable

- 1. Slide the ferrule onto the cable. Strip the cable to the dimensions shown in Figure 1.
- 2. Crimp the center contact to the cable conductor using the tool listed in Figure 1.
- 3. Slide the seal ring onto the back shell until it bottoms on the shoulder of the body.

- 4. Flare the shield slightly so it will go OVER the back shell and not into it.
- 5. Insert the crimped contact into the body until the dielectric bottoms on the back shell.
- 6. Make sure the braid is spread evenly over the back shell, then slide the ferrule forward until it butts against the body.
- 7. Crimp the ferrule using the hand tool listed in Figure 1.

3. CUSTOMER SERVICE

To order AMP products, please contact your customer service representative through normal channels, or call 1800 525–5142 or send a facsimile of your purchase order to 1717 986–7605. You may also mail your order to:

CUSTOMER SERVICE (38–35) AMP INCORPORATED P.O. BOX 3608 HARRISBURG, PA 17105–3608