

TO BE SOLD ONLY WITH INSTALLATION

INSTRUCTIONS

Shrink Temperature

149°C [300°F] (Min)

Pressure Type Wire Connector Combinations Pre-Insulated Heat Sealable **Polyolefin Terminals and Splices**

408-4022 02 DEC 13 Rev E

CU

| STRANDED WIRE | | TOOL | |
|---------------|--------------------|------------------|--|
| SIZE RANGE | STRIP LENGTH | PART NUMBER | |
| 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 | |
| 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 | |
| 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 | |
| 8 AWG | 9.52 mm [3/8 in.] | 55894-1 | |

© 2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company

TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752

TO BE SOLD ONLY

WITH INSTALLATION INSTRUCTIONS

Shrink Temperature

149°C [300°F] (Min)

Pressure Type Wire Connector Combinations Pre-Insulated Heat Sealable **Dolyolofin Terminals and Splices**

408-4022 02 DEC 13 Rev E

| | Polyolei | ili terilililais aliu opi | iices Gu |
|-----|------------|---------------------------|------------------|
| STR | | IDED WIRE | TOOL |
| | SIZE RANGE | STRIP LENGTH | PART NUMBER |
| | 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 |
| | 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 |
| | 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 |
| | 8 AWG | 9.52 mm [3/8 in.] | 55894-1 |

© 2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company

TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION

1-800-522-6752



TO BE SOLD ONLY

WITH INSTALLATION

INSTRUCTIONS

Shrink Temperature

149°C [300°F] (Min)

Pressure Type Wire Connector Combinations Pre-Insulated Heat Sealable

408-4022 02 DEC 13 Rev E

CU

Polyolefin Terminals and Splices

| STRANDED WIRE | | TOOL | |
|---------------|------------|--------------------|------------------|
| | SIZE RANGE | STRIP LENGTH | PART NUMBER |
| | 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 |
| | 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 |
| | 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 |
| | 8 AWG | 9.52 mm [3/8 in.] | 55894-1 |

©2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company

TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752

Pressure Type Wire Connector Combinations Pre-Insulated Heat Sealable **Polyolefin Terminals and Splices**

408-4022 02 DEC 13 Rev E

CU

TO BE SOLD ONLY WITH INSTALLATION INSTRUCTIONS

Shrink Temperature 149°C [300°F] (Min)

| STRANDED WIRE | | TOOL | |
|---------------|--------------------|------------------|--|
| SIZE RANGE | STRIP LENGTH | PART NUMBER | |
| 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 | |
| 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 | |
| 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 | |
| 8 AWG | 9.52 mm [3/8 in.] | 55894-1 | |

©2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company

TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752



Pressure Type Wire Connector Combinations Pre-Insulated Heat Sealable **Polyolefin Terminals and Splices**

408-4022 02 DEC 13 Rev E

CU

| _ | | _ |
|------|---------|---|
| - 7 | | _ |
| | | = |
| | | - |
| conn | ectivit | y |

Pressure Type Wire Connector Combinations Pre-Insulated Heat Sealable Polyolefin Terminals and Splices

408-4022 02 DEC 13 Rev E

| TO BE SOLD ONLY |
|--------------------|
| WITH INSTALLATION |
| INSTRUCTIONS |
| |
| |
| Shrink Temperature |

149°C [300°F] (Min)

| • | STRANDED WIRE | | TOOL | |
|---|---------------|--------------------|------------------|--|
| | SIZE RANGE | STRIP LENGTH | PART NUMBER | |
| | 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 | |
| | 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 | |
| | 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 | |
| | 8 AWG | 9.52 mm [3/8 in.] | 55894-1 | |

©2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company All Rights Reserved
TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752

TO BE SOLD ONLY WITH INSTALLATION

Shrink Temperature 149°C [300°F] (Min)

INSTRUCTIONS

| i oryoton | 00 | | |
|---------------|--------------------|------------------|--|
| STRANDED WIRE | | TOOL | |
| SIZE RANGE | STRIP LENGTH | PART NUMBER | |
| 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 | |
| 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 | |
| 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 | |
| 8 AWG | 9.52 mm [3/8 in.] | 55894-1 | |

©2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company All Rights Reserved TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752



TO BE SOLD ONLY

WITH INSTALLATION

INSTRUCTIONS

Shrink Temperature

149°C [300°F] (Min)

Pressure Type Wire Co Pre Pol

408-4022 νE

| , | | |
|--------------------------------|-----------|-------|
| lyolefin Terminals and Splices | ; (| CU |
| e-Insulated Heat Sealable | | |
| nnector Combinations | 02 DEC 13 | Rev E |

| STRANDED WIRE | | TOOL |
|---------------|--------------------|------------------|
| SIZE RANGE | STRIP LENGTH | PART NUMBER |
| 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 |
| 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 |
| 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 |
| 8 AWG | 9.52 mm [3/8 in.] | 55894-1 |

©2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company

All Rights Reserved
TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752



TO BE SOLD ONLY

Pressure Type Wire **Connector Combinations** Pre-Insulated Heat Sealable **Polyolefin Terminals and Splices**

408-4022 02 DEC 13 Rev E CU

WITH INSTALLATION INSTRUCTIONS Shrink Temperature 149°C [300°F] (Min)

| STRANDED WIRE | | TOOL |
|---------------|--------------------|------------------|
| SIZE RANGE | STRIP LENGTH | PART NUMBER |
| 22-18 AWG | 7.94 mm [5/16 in.] | 55893-1 |
| 16-14 AWG | 7.94 mm [5/16 in.] | 55893-1, 55894-1 |
| 12-10 AWG | 9.52 mm [3/8 in.] | 55893-1, 55894-1 |
| 8 AWG | 9.52 mm [3/8 in.] | 55894-1 |

©2013 Tyco Electronics Corporation, a TE Connectivity Ltd. company

All Rights Reserved
TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product, and/or company names may be trademarks of their respective owners.

TOOLING ASSISTANCE CENTER 1-800-722-1111 PRODUCT INFORMATION 1-800-522-6752