

OS-50 Straight Cable Connectors Solder Clamp Attachment 1063291-1, 1083944-1, 1063296-1, 1313687-1, and 1063298-1

Instruction Sheet 408–4616 21 MAR 00 Rev A

EC 0990-0362-00 CONNECTOR CABLE TOOLS REO'D FIXTURE BASE: 2098-5206-54 CLAMP INSERT: 2098-5208-54 INTERFACE LOCATING TOOL: 2598-5110-02 METAL FILE, SOLDER (60/40), FLUX, CLEANING ALCOHOL, RAZOR BLADE TYPE TYPE DS-50 STRAIGHT CABLE CONNECTORS SOLDER CLAMP ATTACHMENT .085 S/R COAXIAL CABLE 05 ■ NOTE: THIS AP CAN BE USED FOR FLANGE MOUNT AND BULKHEAD FEEDTHRU CONNECTORS ALSO. CONNECTOR SLEEVE ASSEMBLY CLA NUT HOUSING ASSEMBLY ASSEMBLY OPERATIONS ±.020 100 1.0 PREPARATION OF COAXIAL CABLE:
1.1 CUT CABLE TO DESIRED LENGTH.
1.2 TRIM END OF CABLE TO DIMENSION
SHOWN TO EXPOSE CABLE DIELECTRIC.
1.3 REMOVE BURRS AND CLEAN WITH ALCOHOL. CABLE DIELECTRIC CABLE OUTER CONDUCTOR 2.0 SOLDERING OF SLEEVE TO CABLE:
2.1 PLACE THE CLAMP NUT ON CABLE WITH EXTERIOR
THREAD FACING TOWARD THE CUT END OF CABLE OUTER CONDUCTOR THREAD FACING TOWARD THE CUT END OF THE CABLE.

2.2 PLACE THE SLEEVE ON THE CABLE WITH THE LARGER DIAMETER OF THE SLEEVE CLOSEST TO THE CABLE END.
PUSH SLEEVE UNTIL FIRMLY SEATED AGAINST THE CABLE.

2.3 PLACE LOOSE ASSEMBLY IN FIXTURE BASE AS SI FEVE 2.3 PLACE LOOSE ASSEMBLY IN FIXTURE BASE AS SHOWN.
2.3.1 NEST EXPOSED DIELECTRIC INTO INTERFACE LOCATING TOOL, BOTTOMING SLEEVE AGAINST LOCATOR TOOL AS SHOWN.
2.3.2 TIGHTEN CLAMP SCREW TO SECURE CABLE.
2.3.3 ENSURE LOCATOR TOOL IS FIRMLY SEATED AGAINST THE SLEEVE
2.4 MAINTAIN POSITION OF SLEEVE AGAINST LOCATOR TOOL AND APPLY A SMALL AMOUNT OF FLUX AROUND THE CABLE/SLEEVE JUNCTION. APPLY ONLY ENOUGH SOLDER TO FIRMLY ATTACH THE SLEEVE TO THE CABLE.
2.5 VERIEY THAT NO VOIDS EXSIST AT EITHER END OF SLEEVE. • NUT INTERFACE LOCATING TOOL INSERT SOLDER HERE FIXTURE BASE T-4567 3.0 TRIMMING CABLE DIELECTRIC
3.1 PLACE CUTTING BLADE FLUSH WITH SLEEVE
FACE AND CUT THROUGH THE DIELECTRIC
WHILE ROTATING THE CABLE. A CUTTING OR
SLICING MOTION WILL WORK EASIER THAN A
SAWING MOTION

3.2 FINISH CUTTING DIELECTRIC WITH CUTTING
BLADE TAKING CARE NOT TO SCORE THE CENTER
CONDUCTOR OF CABLE BARE INNER CONDUCTOR
BY PRYING THE DIELECTRIC FROM THE CABLE. SLEEVE CABLE OUTER CONDUCTOR CUT HERE FLUSH CABLE DIELECTRIC CLAMP 5.0 TRIM END OF CLAMP ASSEMBLY. 5.1 CUT EXPOSED CENTER CONDUCTOR TO DIMENSION SHOWN. SLEEVE DIMENSION SHOWN.

2. FILE BLUNT END OF INNER CONDUCTOR
TO A 60°-75° CONE AS SHOWN, MAINTAINING
055 ±003 DIMENSION.

5.3 CLEAN WITH ALCOHOL. £003 .055 .75 5.0 SECURE HOUSING ASSEMBLY TO CABLE ASSEMBLY.
5.1 INSERT THE CABLE SUB-ASSY INTO THE HOUSING
SO THAT THE CABLE CENTER CONDUCTOR IS
ACCEPTED BY THE CONTACT IN THE CONNECTOR.
5.2 HOLDING THE CABLE STEADY. SLIDE NUT
FORWARD AS SHOWN.
5.3 ENGAGE THREADS OF NUT TO HOUSING ASSEMBLY
AND TORQUE TO 25 in-ibs. SLEEVE HOUSING ASSEMBL

JACK -HOUSING