Product Specification

108-5477

COMMERCIAL MATE-N-LOK PIN CONTACT HIGH PRESSURE TYPE

1. Scope:

1.1 Contents

This specification covers the requirements for product performance, test methods and quality assurance provisions of high pressure type pin contact for COMMERCIAL MATE-N-LOK CONNECTOR. Mating performance is only specified with applicable socket contact.

Applicable product description and part numbers are as shown in Appendix 1.

Applicable Documents:

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1 AMP Specifications:

Λ.109-5000

Test Specification, General Requirements for Test Methods

B. 114-5214

Application Specification

C. 501-5158

Test Report:

2.2 Commercial Standards and Specifications:

Test methods for electronic and electrical component parts. A. MIL-STD-202

					DR. 26 Jul '95 I. HASEGAWA CHK. 26 Jul '95	SHEET 1 OF			AMP (Japan), Ltd. Kawasaki, Japan	
					I Hasgrauer	6	foc	Loc	NO. 108-5477	REV.
PRINT DIST.	A	FJ00-2833-95	1 '	75 1/4 DATE	APP. 26. JUL. 15	L CO	COMMERCIAL MATE-N-LOK PIN CONTACT HIGH PRESSURE TYPE			

Requirements: 3.

Design and Construction: 3.1

> Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

Materials: 3.2

A. Contact: Pre-Tin Brass

Ratings: 3.3

> Voltage Rating: A.

250 V (AC, DC)

Current Rating: В.

	mm ²	0.5	0.75	1.25	2.0
Wire Size	AWG	#20	#18	#16	#14
Current Ra	ting (A)	5	6	8	10

Temperature Rating: C.

-55 °C to 105 °C

(Upper limit of temperature include temperature rising by current.)

 ${\bf Performance} \ {\bf Requirements} \ {\bf and} \ {\bf Test} \ {\bf Descriptions}:$ 3.4

> The product shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Fig. 2. All tests shall be performed in the room temperature, unless otherwise specified.

> > AMP (Japan), Ltd. SHEET Kawasaki, Japan 2 OF 6 NO. LOC 108-5477 .COMMERCIAL MATE-N-LOK PIN

CONTACT HIGH PRESSURE TYPE

3.5 Test Requirements and Procedures Summary:

Para.	Test Items	Requirements		Procedures						
3.5.1	Confirmation of Product	Product shall be conform the requirements of appl product drawing and Application Specification	icable	cable functionally inspected per applicable quality inspection plan.						
		Electrical Require	ments							
3.5.2	Termination Resistance (Low Level)	5 m Ω Max. (Initial) 10 m Ω Max. (Final)		Measuring method is specified in 4.1.						
3.5.3	Crimp Tensile Strength	Wire Size Crimp Term mm² (AWG) N 0.5 #20 88.2 0.75 #18 127.4 1.25 #16 127.4 2.0 #14 147	(kgf) (9) (13) (13)	Apply an axial pull-off load to crimped wire of contact secured on the tester, (wire length 150 mm) Operation Speed: 100 mm/min. Measure force at wire broken or come out from contact.						
3.5.4	Contact Mating Force	49 N (5 kgf) Max.		Operation Speed: 100 mm/min. Measure the force required to mate connectors.						
Force		4.9 N (0.5 kgf) Min.		Operation Speed: 100 mm/min. Measure the force required to unmate connectors.						
		Be satisfied 3.5.2, 3.5.4,	3.5.5	Operation Speed: 100 mm/min. No. of Cycles: 50 cycles.						
Environmental Requirements										
3.5.7	Thermal Shock	Be satisfied 3.5.2, 3.5.4,	3.5.5	Mated contact -55°C/30 min., 85°C/30 min. Making this a cycle, repeat 25 cycles. MIL-STD-202, Method 107D-A1 Mated contact, 25~65°C 90~95% R.H. 10 cycles Cold-shock -10°C performed MIL-STD-202, Method 106D						
3.5.8	Humidity-Temperature Cycling	Be satisfied 3.5.2, 3.5.4,	3.5.5							
3.5.9	Temperature Life	Be satisfied 3.5.2, 3.5.4, 3.5.5	SHEET	AMP (Japan), Lt Kawasaki, Japa						
Mated contact 85°C. 250 F MIL-STD-202, Method 10			3 OF 6	DMMERCIAL MATE-N-LOK PIN						

3.6 Product Qualification test Sequence

	· Test Group							
Test of Examination	1	2	3	4	5			
		Test Sequence (a)						
Confirmation of Product	1	1	1	1	1			
Termination Resistance (Low Level)	2, 6		2, 4	2, 4	2, 4			
Contact Mating Force	3		5	5	5			
Contact Unmating Force	4		6	6	6			
Crimp Tensile Strength		2			·			
Durability (Repeated Mate/Unmating)	5		-					
Thermal Shock			3					
Humidity-Temperature Cycling				3				
Temperature Life (Heat Aging)					3			

(a) Numbers indicate sequence in which tests are performed.

SHEET	Æ	7 L	/F		AMP (Japan), Ltd. Kawasaki, Japan		
4 OF 6	LOC J	10C A	NO.	108-5477	REV.		
NAME							

NAME

COMMERCIAL MATE-N-LOK PIN CONTACT HIGH PRESSURE TYPE

108-5477

MUMBER:

Customer Release

SECURITY CLASSIFICATION: The applicable product descriptions and part numbers are as shown in Appendix 1.

The applicable product

Produc Part No.	Description				
0-917636-1	COMMERCIAL MATE-N-LOK PIN CONTACT HIGH PRESSURE TYPE (REEL)				

Applicable Socket Contact

Produc Part No.	Description
0-170120-□	COMMERCIAL MATE-N-LOK SOCKET CONTACT (REEL)
0-170121-□	OMMERCIAL MATE-N-LOK SOCKET CONTACT (PIECE)
0-60949-	AUTOMOTIVE MATE-N-LOK SOCKET CONTACT (REEL)

Appendix 1

SHEET		/L	ЛF		AMP (Japan), Ltd. Kawasaki, Japan		
5 OF 6	ιοc	LOC	NO.	108-5477	AEV.		

NAME

COMMERCIAL MATE-N-LOK PIN CONTACT HIGH PRESSURE TYPE

4. Appendix Figure

4.1 Measuring method for termination resistance (Low Level)

Subject mated pin and socket contact crimped on applicable wire to 20 mV Max. open circuit at $10\,\text{m}\Lambda$ Max. closed circuit.

To reduce 150 mm of wire resistance from measuring resistance value as shown Fig. 2.





Fig. 2



COMMERCIAL MATE-N-LOK PIN CONTACT HIGH PRESSURE TYPE