0.8mm FS (Fine-Stack) B To B CONNECTOR

1. SCOPE

This specification covers the requirements for product performance, test methods and quality assurance provisions of 0.8mm Fine-Stack Board to Board connector.

2. APPLICABLE DOCUMENTS

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

- A. EIA-364: Test method for electronic and electrical component parts.
- B. MIL-STD-1344A: Test method for electronic and electrical component parts.
- C. MIL-STD-202: Test methods for electronic and electrical component parts.
- D. Test Report: 501-57566

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, Construction and physical dimensions specified in the applicable product drawing.

3.2. Materials

- A: Housing: Thermoplastic, UL 94V-0, natural color.
- B: Contact: Copper Alloy, 100μ " minimum Tin or Tin-Lead over 50μ " minimum nickel plating over entire contact.
- C: Peg: Copper Alloy, 100μ " minimum Tin or Tin-Lead over 50μ " minimum nickel plating over entire contact.

3.3. Ratings

- A: Voltage rating: 50 VAC.
- B: Current rating: 0.5 A max.
- C: Operating temperature range: -25°C to 85°C.
- D: Storage temperature range: -10°C to 40°C.

| DWN | DATE | APVD | DATE |
|----------|--------------|--------|--------------|
| Angus Wu | 19-July-2004 | Ted Ke | 19-July-2004 |
| | | | FZ00-0159-04 |





3.4. Performance and Test Description

The product shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Figure 1. Unless otherwise specified, all tests shall be performed at ambient environmental conditions per EIA-364.

3.5. Test Requirements and Procedures

| Test Description | Requirements | Procedure | | | | |
|------------------------------------|---|--|--|--|--|--|
| Examination of Product | Meets requirements of product drawing | Visual, dimensional and functional per applicable quality inspection plan. | | | | |
| | ELECTRICAL | | | | | |
| Contact Resistance (Low level) | Initial: 40 m Ω max. Finial: 60 m Ω max. | Mate connector, measure by open circuit voltage 20mV max, closed circuit 10mA max. EIA-364-23A | | | | |
| Insulation Resistance | Initial: 500 M Ω min. Finial: 100 M Ω min. | Apply 500V DC between adjacent pins or pin and ground EIA-364-21A | | | | |
| Dielectric Withstanding Voltage | No breakdown. | Apply 500V AC (rms.) for 1 minute between adjacent pins or pin and ground EIA-364-20A | | | | |
| | MECHANICAL | | | | | |
| Connector mating force | Pos. X 150g (1.47N) max. | Apply axial pullout force at the speed rate of 25±3mm/min. EIA-364-29A | | | | |
| Connector unmating force | Pos. X 20g (0.196N) min. | Apply axial pullout force at the speed rate of 25±3mm/min. EIA-364-29A | | | | |
| Contact retention force | Pos. X 100g (0.98N) min. | Apply axial pullout force at the speed rate of 25±3mm/min. | | | | |
| Durability | Contact resistance after environmental tests: 60 mΩ max. No damage | Repeat mate/unmated connector for 20 cycles. Operation speed: 25±3mm/min. | | | | |
| Vibration | Appearance: No physical damage Shall occur. Discontinuity: No current discontinuity of 1 μ Sec. | Frequency: 10~55~10Hz/1 minute. Amplitude: 1.5mm. Direction: Each of X, Y, Z 3 axes direction. Test time: 2 hours in each axis MIL-STD-1344A METHOD 2005.1 CONDITION | | | | |

Figure 1 (cont)

Rev. O 2 of 3

| Test Description | Requirements | Procedure | | | | | |
|---------------------------------|--|---|--|--|--|--|--|
| ENVIRONMENTAL | | | | | | | |
| Humidity/Temperature Cycling | Contact resistance: After environmental tests: $60 \text{ m}\Omega$ max. | Connector to 9 cycles. The test specimens shall be exposed to STEP 7a during only 5 out of 9 cycles. A 10 th cycles consisting of only step 1 through 6 is then per formed. After which the test | | | | | |
| | Insulation resistance: After environmental tests: $100 \text{ M}\Omega$ min. | | | | | | |
| | Appearance: No damage. | at ambient room conditioned at ambient room conditions for 24 hours. MIL-STD-202 METHOD 106 | | | | | |
| Resistance to Soldering Heat | No physical damage shall occur. | Subject connector to solder bath at 250±5°C for 5±1 seconds. MIL STD-202 METHOD 210 | | | | | |
| | <u>Lead-Free type</u> No physical damage shall occur. | Lead-Free type Subject connector to solder bath at 260±5°C for 5±1 seconds. MIL STD-202 METHOD 210 | | | | | |
| Solderability | Plating surface of solder- Dipping section shall be Covered with smooth Solder. | Subject connector lead to solder bath (63% Sn & 37% Pb) at 235 ±5°C for 5±0.5 seconds. MIL STD-202 METHOD 208 | | | | | |

Note: Shall meet visual requirement, show no physical damages.

Figure 1 (end)

3.6. Product Qualification and Test Sequence

| | Test Group | | | | | | | |
|---------------------------------|-------------------|------|------|------|------|------|------|------|
| Test or Examination | Α | В | С | D | E | F | G | Н |
| | Test Sequence (a) | | | | | | | |
| Examination of Product | 1, 5 | 1, 4 | 1, 3 | 1, 5 | 1, 3 | 1, 8 | 1, 3 | 1, 3 |
| Contact resistance | 2 | | | 2, 4 | | 2, 6 | | |
| Insulation resistance | 3 | | | | | 3, 7 | | |
| Dielectric withstanding voltage | 4 | | | | | 4 | | |
| Connector mating force | | 2 | | | | | | |
| Connector unmating force | | 3 | | | | | | |
| Contact retention force | | | 2 | | | | | |
| Durability | | | | 3 | | | | |
| Vibration | | | | | 2 | | | |
| Humidity/Temperature cycling | | | | | | 5 | | |
| Resistance to Soldering Heat | | | | | | | 2 | |
| Solderability | | | | | | | | 2 |

Note: (a) Numbers indicate sequence in which tests are performed.

Figure 2

Rev. O 3 of 3