1.Scope:

1.1 Contents

This specification covers the requirements for product performance, test methods and quality assurance provisions of Clean Body 025/040 Sealed 132pos.Connector.

Applicable product description and part numbers are as shown in Appendix 1.

2. Applicable Documents:

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

2.1 AMP Specifications:

- A. 109-5000 : Test Specification, General Requirements for Test Methods
- B. 114-5278 : Application Specification

Crimping CLEAN BODY 025/040 Receptacle Contact.

C. 501-5587 : Qualification Test Report

2.2 Commercial Standards and Specifications.

- A. JASO D605 : Multi-pole Connector for Automobiles
- B. JASO D7101 : Test Methods for Plastic Molded Parts
- C. JIS C3406 : Low Voltage Wires and Cables for Automobiles
- D. JIS D0203 : Method of Moisture, Rain and Spray Test for Automobile Parts
- E. JIS D0204 : Method of High and Low Temperature Test for Automobile Parts
- F. JIS D1601 : Vibration Testing Method for Automobile Parts
- G. JIS R5210 : Portland Cement

108-5911

3.Requirements:

3.1 Design and Construction:

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

3.2 Material:

A. Contact:

a. Receptacle Contact: Pre-tinned Cu Alloy, Brass, Pre-tinned Brass.

b. Tab Contact : Pre-tinned Cu Alloy

- B. Housing : PBT resin
- C. Seal Ring; Wire Seal Rubber: Silicone Rubber
- 3.3 Ratings:
 - A. Temperature Rating : -40°C to 120°C
- 3.4 Performance Requirements and Test Descriptions:

The product shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Fig.1. All tests shall be performed in the room temperature, unless otherwise specified.

Para.	Test Items	Requirements	Procedures						
3.5.1	Confirmation of Product	Product shall be conforming to the requirements of applicable product drawing and Application Specification. No. 114-5278	ally inspected per applicable quality						
Electrical Requirements									
3.5.2	Termination Re- sistance (Specified Current)	10mV/A Max. (Initial) 20mV/A Max. (Final)	Measure initial termination resistance of contact test circuit in mated con- nectors. Fig.3 AMP Spec.109-5311-2						
3.5.3	Termination Resistance (Low Level)	10m Ω Max. (Initial) 20m Ω Max. (Final)	Subject mated contacts assembled in housing to closed circuit current of 10mA Max. at open circuit voltage of 20mV Max. Fig.3 AMP Spec.109-5311-1						
3.5.4	Dielectric Strength	No creeping discharge nor flashover shall occur.	1kV AC for 1 minute. Cutoff current : 1 mA Test between adjacent contacts and between contacts and housing of mated connectors. Fig.4 AMP Spec. 109-5301						
3.5.5	Insulation Resistance	100MΩ Min.	Impressed voltage 500V DC. Test between adjacent contacts and between contacts and housing of mated connectors. Fig.4 AMP Spec. 109-5302						
3.5.6	Temperature Rising	30℃ Max. under loaded specified current.	Measure temperature rising of mated connectors with all contacts se- ries-wired, by energized current. Test Current: 3A (025: 0.5mm ² wire) Test Current: 5A (040: 0.85mm ² wire) AMP Spec. 109-5310						
3.5.7	Current Cycling	$\begin{array}{l} \mbox{Termination Resistance (Low Level)} \\ 20m\Omega \ \mbox{Max. (Final)} \\ \mbox{No ignition is allowed during the} \\ \mbox{test.} \end{array}$	45minutes"ON",15minutes"OFF", 1000cycles. Test Current: 3.5A (025: 0.5mm ² wire) Test Current:6.5A(040: 0.85mm ² wire) AMP Spec.109-5308						

Fig.1(To be continued)

108-5911

Para.	Test Items	Requirem	Requirements ents	Procedures						
3.5.8	Vibration	No electrical discontin than 1msec. shall occi Termination Resistanc (Specified Current) 20mV//	ur.	Vibration Frequency: 20~400Hz/6min. Accelerated Velocity : 43.1m/s ² Vibration Direction : X.Y.Z Duration: 3 hours each for "X" "Y", and "Z" Fig.5 AMP Spec.109-5202						
3.5.9	Connector Mating Force	70N Max.		Operation Speed : 100mm/min. Measure the force required to mate connectors. AMP Spec.109-5206						
3.5.10	Connector Unmating Force	70N Max.		Operation Speed : 100mm/min. Measure the force required to un- mate connectors without locking latch set in effect. AMP Spec.109-5206						
3.5.11	Housing Locking Strength	98N Min.		Measure housing locking strength. Operation Speed:100mm/min. AMP Spec. 109-5210						
3.5.12	Contact Insertion Force	14.7N Max. per contac	ot	Measure the force required to in- sert contacts into housing. Operation Speed:100/mm/min AMP Spec. 109-5211						
3.5.13	Contact Retention Force	48N Min.		Apply axial load to contact without secondary lock set in effect. Operation Speed: 100mm/min. AMP Spec. 109-5212						
3.5.14	Contact Retention Force (Secondary lock)	98N Min.		Apply axial load to contact with secondary lock set in effect. Operation Speed: 100mm/min. AMP Spec. 109-5212						
3.5.15	Crimp Tensile Strength	Wire Size mm ² 0.3 0.5 0.75 1.25	Crimp Ten- sile(min.) N 49 88 117 176	Apply an axial pull-off load to crimped wire of contact secured on the tester. Operation Speed: 100mm/min. AMP Spec. 109-5205						

Fig.1(To be continued)

Para.	Test Items	Requirements	Procedures
3.5.16	Resistance	Termination Resistance	Repeated mating / unmating by hand,
	to "Kojiri"	(Specified Current)	
		20mV/A Max. (Final)	AMP Spec.109-5215
3.5.17	Watertight	98kPa Min. (Initial)	Blow compressed air into mated pair
	Sealing	49kPa Min. (Final)	of connectors through a small hole.
	-		For this test, wire ends are sealed.
			Put the connectors into water and
			must withstand the air pressure of
			9.8kPa for 30 seconds.
			Increase the air pressure at a rate of
			9.8kPa each time until air leakage
			takes place.
3.5.18	Handling	No abnormalities allowed in man-	Manually operated
	Ergonomics	ual mating/unmating handling.	
	T I I C' '	Environmental Requireme	
3.5.19	Thermal Shock	Termination Resistance (Low Level)	Mated connector
		20m Ω Max. (Final)	-40°C/30min.,120°C/30min.
		Watertight Sealing	Making this a cycle,
		49kPa Min. (Final)	repeat 1000cycles.
			AMP Spec. 109-5103
3.5.20	Humidity, Steady	Insulation resistance (Final)	Mated connector,
	State	100M Ω Min.	90∼95%R.H.,60℃
		Termination resistance (Low Level)	96hours
		20m Ω Max. (Final)	AMP Spec. 109-5105
		Current Leakage : 1mA Max.	
3.5.21	Industrial Gas	Termination resistance (Low Level)	SO ₂ Gas : 10ppm, 90~95%R.H.
	(SO_2)	20m Ω Max. (Final)	40°C, 24hours (AMP Spec.109-5107)
3.5.22	Temperature Life	Termination resistance (Low Level)	120°C±2°C,120hours
	(Heat Aging)	20m Ω Max. (Final)	AMP Spec. 109-5104
		Watertight Sealing	
		49kPa Min. (Final)	
3.5.23	Resistance to	Termination resistance (Low Level)	-40°C±5°C,120hours
	Cold	20m Ω Max. (Final)	AMP Spec. 109-5108
		Watertight Sealing	· · /
		49kPa Min. (Final)	
3.5.24	Dust	Termination Resistance	Subject JIS R 5210 cement blow
	Bombardment		1.5kg per 10 seconds in 15 minutes
		(Specified Current)	intervals for 60 minutes.
		20mV/A Max. (Final)	After completion of duration, repeat
			mating / unmating for 3 cycles.
			AMP Spec. 109-5110
3.5.25	Water Splash	Termination Resistance	Expose mated connectors under
			$120^{\circ}C \pm 3^{\circ}C$ for 40 minutes, splash
		(Specified Current)	Water for 20 minutes.
		20mV/A Max. (Final)	48 cycles, Test Voltage : 12V
		Current Leakage : 100 μ A Max.	AMP Spec. 109-5109
			Condition: JIS D 0203, S2

Fig.1 (End)

CLEAN BODY 025/040 Sealed 132pos Connector

108-5911

3.6 Product Qualification Test Sequence

	Test Items		Test Group												
Para.			2	3	4	5	6	7	8	9	10	11	12	13	
		Test Sequence													
3.5.1	Confirmation of Product	1	1	1	1	1, 5	1	1	1	1	1	1	1	1	
3.5.2	Termination Resistance (Specified Current)		3,5	3,5			2,6	2,4					2,4	2,4	
3.5.3	Termination Resistance (Low Level)					2,4			2,5	2,5	2,4	2,5, 8			
3.5.4	Dielectric Strength						4								
3.5.5	Insulation Resistance						3			7					
3.5.6	Temperature Rising						5								
3.5.7	Current Cycling					3									
3.5.8	Vibration							3							
3.5.9	Connector Mating Force			2											
3.5.10	Connector Unmating Force			4											
3.5.11	Housing Locking Strength				5										
3.5.12	Contact Insertion Force				2										
3.5.13	Contact Retention Force				3										
3.5.14	Contact Retention Force (Secondary lock)				4										
3.5.15	Crimp Tensile Strength	2													
3.5.16	Resistance to "Kojiri"		4												
3.5.17	Watertight Sealing								3,6	3,6		4,7			
3.5.18	Handling Ergonomics		2												
3.5.19	Thermal Shock								4						
3.5.20	Humidity (Steady State)									4					
3.5.21	Industrial Gas (SO ₂)										3				
3.5.22	Temperature Life (Heat Aging)											3			
3.5.23	Resistance to Cold											6			
3.5.24	Dust Bombardment												3		
3.5.25	Water Splash													3	

Numbers indicate sequence in which tests are performed.

Fig.2





From the measured readings, deduct the resistance of the wire used for termination. When testing for rated current measurement, apply 12 V DC,1A to the circuit.

For obtaining uniformity of the current density on probing points Y-Y', apply soldering on the probing points prior testing.

Fig.3 Measurement of Termination Resistance



Fig. 4



108-5911



Fig.5

The applicable product descriptions and part numbers are as shown in Appendix. 1 Appendix 1

Part Numbers	Description
1717138-4	44Pos Plug Assembly (C)
1717138–5	44Pos Plug Assembly (B)
1717138-6	44Pos Plug Assembly (A)
1612108-4	Cavity Plug
1746089-1	Wire Cover V Type
1717139–1	132Pos Cap Assembly
1827108-1	44Pos Wire Cover (A)
1827109-1	44Pos Wire Cover (B)
1674419-2	44Pos Wire Cover (C)
1903287-1	44Pos Wire Cover Type-IV