

Product Specification

The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore, TE Connectivity (TE) makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, TE may change these requirements based on the results of additional testing and evaluation. Contact TE Engineering for further details.

040III MLC 44P

1. SCOPE

1.1. Content

This specification covers the requirements for product performance, test methods and quality assurance provisions of 040III MLC 44P

1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 1 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

1.3. Qualification Test Results

Successful qualification testing on the subject product line has not been completed. The Qualification Test Report number will be issued upon successful qualification testing.

2. APPLICABLE DOCUMENTS AND FORMS

The following documents and forms constitute a part of this specification to the extent specified herein. Unless otherwise indicated, the latest edition of the document applies.

2.1. TE Documents

- 936460 : Customer Drawing (44POS. CAP ASSEMBLY(WIRE TO BOARD) .040III MULTI LOCK CONNECTOR)
- 936473: Customer Drawing (20POS PLUG HOUSING ASS'Y 040 III MLC CONN)
- 936475 : Customer Drawing (24POS PLUG HOUSING ASS'Y 040 III MLC CONN)

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, construction, materials and physical dimensions specified on the applicable product drawing.

3.2. Ratings

Voltage	Temperature	Humidity
12V DC	25±5℃	65±20%

PRODUCT INFORMATION 1-800-522-6752



3.3. Test Requirements and Procedures Summary

Unless otherwise specified, all tests shall be performed at ambient environmental conditions.

TEST DESCRIPTION	REQUIREMENT		PROCEDURE		
Appearance	No crack, damage, distortion are permitted		Using sense of sight and touch.		
CONN engage and	936473(20P) 15kgf or less		Measure force by inserting and disengaging the connector with terminal assembled at constant 50 mm/min speed. However,		
disengage force	936475(24P) 18kgf or less	remove lock part when measuring disengage force.		
Reverse insertion between housings	It shall not be incorrectly inserted by applying force of 20kgf.		1) Insert terminal to housing 2) Fix housing of female connector to moving part of measuring instrument in reverse insertion direction. (Reverse insertion: 180 degree rotation on the locking part) 3) Set a measuring instrument to stop at force of 20kgf and insert that. At this moment, monitor resistance of one terminal matched to identify current carrying between terminals. 4) Check the insertion by housing modification of male connector after connector insertion.		
Strength of HSG lock	Min 8kgf or more		Combine housing only, fix the one side of housing in completely locked condition, and extend the other side in axial direction and 30 angle direction at a constant speed of 50mm/min. Then measure weight when lock structure is disengaged or destroyed.		
HSG lock releasing force	Max 6kgf		Apply force (F) to lock releasing part, and measure weight on the point of A=0. However, cut connector and then perform test at the section in order to secure visibility. A		
Terminal engage and	Engage	0.2~0.8kgf	As shown in figure 4-3, engage and disengage male terminal or steel gauge into or from female terminal at 50 mm/min speed.		
disengage force (kgf)	Disengage	0.15~0.8kgf	Steel Female		
Voltage Drop	Max 5mV/A		Measure the circuit voltage drop (V) by sending voltage and current described in the table 5-1 with terminal combined on the connector. Then calculate a voltage drop (VD) in terminal by subtracting cable resistance (L) from the circuit voltage drop (V).		

Rev.A 2 of 6



			1)HARNESS versus UNIT:VD =V(L3+L4)				
			Application	Open voltage	Short circuit current	Division	
			Signal circuit	20 ± 5 mV	10 mA	ECU, Sensor	
			Power circuit	13 Y	1 A	Other than the above	
			<table5-1></table5-1>				
Insulation resistance	Min 100 ^{MΩ}		Measure resistan and between tern DC 500V insulation combined.	on resistance oc 500/ Insulation resistance gauge	ısing surface (figure 5-7) with onnector OC 500V Insulation resistance gauge	
Leakage current	10 ⊭ ^A or less		(figure 5-6).		20 DC	500V sulation sistance gauge	
High voltage test	No allowed insulation breakdown				ential of 1000 n the contact a	V AC between the and housing.	
Terminal bending strength	Terminals should not be torn. When bent material stretched to its original state, it should not be torn or cracked.		Terminal is ready fixed. After applying bent portion and second of the s	ng force on 1 scans. The ne nd then is me	5 seconds, ex ew sample was easured in the aw material, a	pand at least 10 s fixed to rotate same way.	
Connector coupling sounds	Connector coupling sound : 65dB(A) or more		the connector. Me combine the conn	easure the pe ector. Sound	eak sound that Is unit: dB(A)	•	
Twisting Test - Connector	Appearance	No crack, damage, distortion are permitted	Apply 8kgf force on the end part of combined connector 10 times each in the (front, rear, left, right) directions perpendicular to axial direction.				
Engage and Disengage Endurance Test	Max 10mV/A		Make combine co 100mm/min. Perfo (Do not use lockin	orm it 50 time		ngage at	
Overcurrent cycle test	Appearance No crack, damage distortion are permitted		Engage and diser times with hands, for the connector	and apply th	e following cu	rent 1000 cycles	

Rev.A **3** of 6



		1		tom:				
	Voltage Drop	Max 10mV/A	Condition	temperature		ied current	2 times of basic curre	ent
			Α	Current applicat condition A		pplication time	1 minute - ON, 9 minutes	10.0000
			Condition	Current applicat	ion App	ied current	5 times of basic curr	ent
			В	condition B	Current a	application time	10 seconds - ON, 590 seco	nds - OFF
	Temp rise	Max 40°C	Condition A					
			Condition					
		No orași	b					
	Appearance	No crack, damage,					r with terminal asse	embled 10
		distortion are permitted		times with hands, and leave it in temperature chamber of -40°C for 120 hours. Make				
	Voltage Drop	Max	10mV/A	connector engaged and disengaged 5 times immediately, and drop it onto the concrete surface from 1m height 3 times in the direction of figure 6-1. (Voltage drop & Temperature rise test				
Cold			Between	perform at normal temperature):				
temperature	Insulation	Min 100	terminals					
test	Resistance	MΩ	housing					
			surface					
	Current	Surace		1 1] \		
	Leakage	Max 1 #A					<figure 6-1<="" td=""><td>></td></figure>	>
	Temperature Rise	Max 40 C						
	Appearance	No crack, damage, distortion are permitted					or with terminal asso 0 CYCLE by below	
				condition. (-	o o roll by bolow	1001
Cold and hot				Cortation: (
temperature					(*)			
shock test	Voltage	oltage Drop Max 10mV/A		temper		T1 T2	T1 T2 T1 ≤ 5 m T2 = 1 ho	
	Drop				-		1 CYCLE	
	Appearance	No crack, damage, distortion are permitted		Engage and	d disengag	e connecto	r with terminal asse	mbled 10
							combined state at the	
High				temperature chamber of the table 6-1 for 300 hours. Then pick it out and leave it until it returns to normal temperature.				
temperature test	Voltage	Max 10mV/A		High Ter	mperature	Conn	ector Using Part	
	Drop			80	o°C		n - Waterproof Connector	
		No crack, damage,					r with terminal asse	mbled 10
Temperature · Humidity Test	Appearance		tion are	times with h			1.050/ 1.11	
		per	mitted				nd 65% relative hun	nidity for
	Voltage Drop	Max 10mV/A		25 hours. And perform 5 cycles of the method specified in figure 6-3. Then pick connector out of chamber and dry				
	Insulation Resistance	Min 100 MΩ	Between	it for 2 hours or more.				
			terminals					
			housing					
			surface					
	Current Leakage							

Rev.A **4** of 6



		Ma	x 1 μ ^A					
				(b) 80± 2 b, 90± 5%RH 90± 10%RH 25± 20 45± 20, 90± 5%RH 25± 20 45± 20, 90± 5%RH 25± 20 45± 20, 90± 5%RH 1 CYCLE < Figure 6-3: Test pattern >				
Dust Test	Appearance distor			Engage and disengage connector with terminal assembled 1 times with hands, and diffuse 1.5kg Portland cement(JIS R5210) with fan (or others) for 10 seconds per 15 minutes while maintaining 150mm distance from wall in the closed				
	Voltage Drop	Max	10mV/A	container of 900~1200mm length, width and height, with connector combined. After 1 hour, measure it.				
	Appearance No crack, damage, distortion are permitted		tion are	Engage and disengage connector with terminal assembled 10 times with hands, and perform test each sample with connector combined.				
Oil and liquid test	Voltage Drop		10mV/A	A. Immerge connector in combined state for 2 hours in mixed oil of 50± 2°C ENG oil (SAE10W) or equivalent oil and B. Immerge connector in combined state for 1 hour in car gasoline (JIS K2202) at normal temperature, and then pick it out. C. Immerge connector in combined state for 1 hour in brake liquid (pure product) at normal temperature, and then pick it out. D. Immerge connector in combined state for 1 hour in 100% washer liquid (pure product) at normal temperature, and then pick it out. E. Immerge connector in combined state for 1 hour in 50% LLC (Long life coolant) at normal temperature, and then pick it out.				
Ozone Test	Appearance	No crack, damage, distortion are permitted		Engage and disengage Connector with terminal assembled 10 times with hands, and samples keep at 40°C and 50±5pphm				
Voltage Drop		Max 10mV/A		Ozone for 100hour. Then pick connector out of chamber and dry it for 2hours or more.				
Sulfur (SO2)	Appearance	No crack, damage, distortion are permitted Max 10mV/A		Engage and disengage connector with terminal assembled 10 times with hands, and expose it in combined state to sulfur gas of 40±3°C, density 10ppm, humidity 90~95%, for 24 hours.				
gas test	Voltage Drop			Then pick connector out of chamber and dry it for 2 hours or more.				
Appearance		No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and leave it in combined state in the temperature chamber of 120°C or 80°C (follows table 7) for 48				
Complex environment	Crimp Tensile	0.3SQ	Min 6kgf	hours. And then perform the following vibration test. Then measure				
endurance test	Strength Voltage Drop	0.5SQ Min 9kgf Max 10mV/A		instant short circuit according to the method of clause 4.16 for 4 hours for X, Y, Z each. 1) Sin Wave Test Division Condition				

Rev.A **5** of 6



umi Refer to figure 4-8, 90~95%
Basic current (Connector electrodes in series.)
120 CYCLE (45 minutes-ON, 15
cle minutes-OFF)
4.4G
20Hz ~ 200Hz (sweep time: 3 minutes or less)
e 40 hours for X, Y, Z each
nod Test mode A, B, C
1

3.4. Applied Part No List

TE Part no	Description		
0-936460-1	44POS. CAP ASSEMBLY(WIRE TO BOARD) .040III MULTI LOCK CONNECTOR)		
0-936473-1/2/5/6/7/8	20POS PLUG HOUSING ASS'Y 040 III MLC CONN		
0-936475-1/2/5/6/7/8	24POS PLUG HOUSING ASS'Y 040 III MLC CONN		

Rev.A **6** of 6