

The product described in this document has not been fully tested to ensure conformance to the requirements outlined below. Therefore, TE Connectivity (TE) makes no representation or warranty, express or implied, that the product will comply with these requirements. Further, TE may change these requirements based on the results of additional testing and evaluation. Contact TE Engineering for further details.

090 SLD Series

1. SCOPE

1.1. Content

This specification covers the requirements for product performance, test methods and quality assurance provisions of 090 SLD Series.

1.2. Qualification

When tests are performed on the subject product line, procedures specified in Figure 1 shall be used. All inspections shall be performed using the applicable inspection plan and product drawing.

1.3. Qualification Test Results

Successful qualification testing on the subject product line has not been completed. The Qualification Test Report number will be issued upon successful qualification testing.

2. APPLICABLE DOCUMENTS AND FORMS

The following documents and forms constitute a part of this specification to the extent specified herein. Unless otherwise indicated, the latest edition of the document applies.

2.1. TE Documents

- 936248: Customer Drawing (090 SEALED 2P PLUG ASS'Y)
- 936291 : Customer Drawing (090 SEALED 2P CAP ASS'Y)
- 936311: Customer Drawing (COVER HSG FOR .090 SEALED 2P PLUG CONN'R)
- 936251: Customer Drawing (090 SLD 3P PLUG ASSY)
- 936292 : Customer Drawing (090 SEALED 3P CAP ASS'Y)
- 936312 : Customer Drawing (COVER HSG FOR .090 SEALED 3P PLUG CONN'R)
- 936578: Customer Drawing (SEALED CHIP RESISTOR CONNECTOR FOR CAN)
- 936584: Customer Drawing (090 SEALED 2P PLUG ASS'Y FOR CHIP RESISTOR)

3. REQUIREMENTS

3.1. Design and Construction

Product shall be of the design, construction, materials and physical dimensions specified on the applicable product drawing.

3.2. Ratings

Voltage	Temperature	Humidity
12V DC	2 5±5℃	65±20%

PRODUCT INFORMATION 1-800-522-6752



3.3. Test Requirements and Procedures Summary

Unless otherwise specified, all tests shall be performed at ambient environmental conditions.

TEST DESCRIPTION	REQUIREMENT	PROCEDURE		
Appearance	No crack, damage, distortion are permitted	Using sense of sight and touch.		
CONN engage and disengage force	10kgf or less	Measure force by inserting and disengaging the connector with terminal assembled at constant 50 mm/min speed. However, remove lock part when measuring disengage force.		
Reverse insertion between housings	It shall not be incorrectly inserted by applying force of 20kgf.	1) Insert terminal to housing 2) Fix housing of female connector to moving part of measuring instrument in reverse insertion direction. (Reverse insertion: 180 degree rotation on the locking part) 3) Set a measuring instrument to stop at force of 20kgf and insert that. At this moment, monitor resistance of one terminal matched to identify current carrying between terminals. 4) Check the insertion by housing modification of male connector after connector insertion.		
Reverse insertion between terminal and housing	5kgf or more	Crimp cable of maximum size on terminal and then insert it into housing by end of insulation barrel in the reserve direction.		
Engage force between terminal and housing	Max 1.5kgf or less	As shown in the following figure 4-1, measure the weight while inserting terminal into fixed housing at 50mm/min speed. Terminal Figure 4-1>		
CONN Clip panel engage and retention force	Engage: Max 12kgf or less Retention: Min 15kgf or more	 Insert clip into the fixed plate that can be furnished with clip at 50mm/min and measure the force at that time. Pull clip at 50mm.min and measure the force when destroyed or disengaged 		
Strength of HSG lock	Min 10kgf or more	Combine housing only, fix the one side of housing in completely locked condition, and extend the other side in axial direction and 30 angle direction at a constant speed of 50mm/min. Then measure weight when lock structure is disengaged or destroyed.		
HSG lock releasing force	Max 6kgf	Apply force (F) to lock releasing part, and measure weight on the point of A=0. However, cut connector and then perform		

Rev.A 2 of 7



			test at the section in order to secure visibility.			
			A	F		eleasing ure 5-2>
Terminal retention force	N	Min 10kgf	Fix the housing line of cable in a position 50~100 weight when ter	xial direction a mm away from	t a speed of 5 crimped part	and measure
Terminal	Engage	070~090 : 0.3~1.0kgf	As shown in figure or steel gauge in speed.			ge male terminal t 50 mm/min
engage and disengage force (kgf)	Disengage 070~090: 0.15~1.0kgf			Stee	I Fe	emale
Crimp strength (kgf)		Min 9kgf or more Min 13kgf or more	Fix the crimped terminal, and draw the cable at a position 50~100 mm away from crimped part in axial direction at 100 mm/min speed. Then measure the weight when cable is cut or disengaged from the crimped part			
Voltage Drop	090~37	75 : Max 3mV/A	Measure the circ current describe 5-1 with termina Then calculate a by subtracting c drop (V).	d in the table I combined on I voltage drop (the connector (VD) in termina (L) from the o	: al circuit voltage
			Application	Open voltage	Short circuit current	Division
			Signal circuit	20 ± 5 mV	10 mA	ECU, Sensor
			Power circuit	13 V	1 A	Other than the above
				<tab< td=""><td>le5-1></td><td></td></tab<>	le5-1>	
Insulation resistance	Λ	⁄lin 250 ^{MΩ}	Measure resista and between te DC 500V insula combined.	minal and hou tion resistance	sing surface (OC 500V Insulation resistance gauge
Leakage current	1	⊭A or less	Measure it by ap	oplying DC 14V	/ between neiç	ghboring terminal

Rev.A **3** of 7



				COO DO DC 500V Insulation resistance gauge Figure 5-6: Between neighboring terminals>		
Temperature rise	Max 30 ℃			Apply basic current (I = Io *K) of clause to the connector with electrodes in series in the room free from wind (normal temperature). And measure a temperature of crimped part after reaching saturation temperature. Then calculate a temperature of crimped part by subtracting ambient temperature from the temperature.		
	After endurance			Put the combined connector in water as shown in the figure 5-9 and supply 10Kpa(0.1kg/cm²) to connector for 30 seconds. Then increase it by 10Kpa(0.1kg/cm²) until 200Kpa(2kg/cm²) is reached and maximum value shall be specified in the test report for reference. (Use a wire of which the pressure does not leak at the end) Compressed		
Sealing test	Sealing test 1kgf/ cm ²			90° 150° 180°		
Twisting Test - Connector	Appearance	No crack, damage, Appearance distortion are permitted		Apply 8kgf force on the end part of combined connector 10 times each in the (front, rear, left, right) directions perpendicular to axial direction.		
Engage and Disengage Endurance Test	Max 10mV/A			Make combine connectors engage and disengage at 100mm/min. Perform it 50 times. (Do not use locking device)		
Appearance		No crack, damage distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and apply the following current 1000 cycles for the connector with electrodes in series at 60 °C of ambient temperature.		
Overcurrent cycle test	Voltage Drop	Max 10mV/ A	Condition A Condition B	Current application condition A Applied current 2 times of basic current Current application time 1 minute - ON, 9 minutes - OFF Current application Applied current 5 times of basic current		
,				condition B Current application time 10 seconds - ON, 590 seconds - OFF		
	Temp rise		Condition A			

Rev.A 4 of 7



		Max 40°C	Condition b				
	Appearance	No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and leave it in temperature chamber of -40°C for 120 hours. Make			
Cold temperature test	Insulation Resistance	Min 100 ™Ω	Between terminals housing surface	connector engaged and disengaged 5 times immediately, and drop it onto the concrete surface from 1m height 3 times in the direction of figure 6-1. (Voltage drop & Temperature rise test perform at normal temperature):			
	Current Leakage	Max 100 μA		Figure 6-1>			
Cold and hot	Appearance	No crack, damage, distortion are permitted		Engage and disengage Connector with terminal assembled 10 times with hands, this repeats 200 CYCLE by below test condition. (Non-Sealed: 80°C) Cycle Tile Tile Tile Tile Tile Tile Tile Ti			
temperature shock test	Voltage Drop	Max 10mV/A					
	Sealing	Max 0.5kgf/ cm ²					
High	Appearance	No crack, damage, distortion are permitted					
temperature test	Voltage Drop	Max	10mV/A	High Temperature Connector Using Part			
	Sealing	Max 0.5kgf/ cm ²		80°C Non - Waterproof Connector			
	Appearance	disto	k, damage, rtion are mitted	Engage and disengage connector with terminal assembled 10 times with hands, and leave it at 25°C ambient temperature and 65% relative humidity for			
	Voltage Drop	Max	10mV/A	25 hours. And perform 5 cycles of the method specified in figure 6-3. Then pick			
	Insulation Resistance	Min 100 ™Ω	Between terminals	connector out of chamber and dry it for 2 hours or more.			
Temperature Humidity Test			housing surface	(°C) 60± 2 °C, 90± 5%RH 90± 10%RH			
	Current Leakage	Max	100 <i>μ</i> Α	45± 2°C, 96± 5°S,RH 25± 2°C 85± 10%,RH 2hr 4hr 2hr 1chr 2hr 1hr 2hr 1,hr 1 CYCLE < Figure 6-3: Test pattern >			
Dust Test	Appearance	No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and diffuse 1.5kg Portland cement(JIS R5210) with fan (or others) for 10 seconds per 15 minutes			

Rev.A **5** of 7



	Voltage Drop	Max 10mV/A		while maintaining 150mm distance from wall in the closed container of 900~1200mm length, width and height, with connector			
	Sealing	Max 0.5	5kgf/ cm ²	combined. After 1 hour, measure it.			
Waterproof Test			a, damage, tion are mitted	Make combined connectors engaged and disengaged 10 time hands, and leave it in combined state at 120 °C ambient temper for 40 minutes and then spray water of normal temperature for			
	Insulation Resistance	Min 100	Between terminals housing	minutes according to S2 of JIS D0203. Repeat 48 cycles of this * JIS D0203 S2 condition: attach specimen at 400mm distance from the waterproof pipe with water spray hole or water discharge hole, and rotate waterproof pipe 23 times per			
			surface	minute around the axis.			
	Current Leakage	Max 100 μA					
Oil and liquid test	Appearance	No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and perform test each sample with connector combined. A. Immerge connector in combined state for 2 hours in mixed			
	Voltage Drop	Max 1	0mV/A	oil of 50± 2°C ENG oil (SAE10W) or equivalent oil and B. Immerge connector in combined state for1 hour in car gasoline (JIS K2202) at normal temperature, and then pick it			
	Sealing	ealing Min 0.5kgf/cm ²		out. C. Immerge connector in combined state for 1 hour in brake liquid (pure product) at normal temperature, and then pick it out. D. Immerge connector in combined state for 1 hour in 100% washer liquid (pure product) at normal temperature, and the pick it out. E. Immerge connector in combined state for 1 hour in 50% LLC (Long life coolant) at normal temperature, and then pick out.			
	Appearance	No crack, damage, e distortion are permitted		Engage and disengage Connector with terminal assembled 10 times with hands, and samples keep at 40°C and 50±5pphm Ozone for 100hour. Then pick connector out of chamber and dry it for 2hours or more			
Ozone Test	est Voltage Drop Max 10mv/A		I0mv/A				
Sealing		Min 0.5kgf/cm ²					
Salt Water Test		No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled times with hands, and put it in 35°C temperature regulation chamber, spray 5% salty water for 24 hours according to			
	Voltage Drop	Max 1	I0Mv/A	Z2371, and, maintain room temperature without spray for 1 hour, Then repeat this four times. Then pick connector out of			
	Insulation Resistance			chamber and dry it at room temperature for 2 hours or more.			
	Current Leakage	Max 100 <i>µ</i> A					
Sulfur (SO2) gas test	Appearance	No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and expose it in combined state to sulfur gas			

Rev.A **6** of 7



	Voltage Drop	Max 10mv/A		of 40±3°C, density 10ppm, humidity 90~95%, for 24 hours. Then pick connector out of chamber and dry it for 2 hours or more.				
	Appearance No crack, damage, distortion are permitted		Engage and disengage connector with terminal assembled 10 times with hands, and leave it in combined state in the temperature chamber of 120°C or 80°C (follows table 7) for 48					
	Crimp	0.5SQ	Min 9kgf		hours.			
	Tensile Strength 0.85SQ Min 13k		Min 13kgf	ii	And then perform the following vibration test. Then measure instant short circuit according to the method of clause 4.16 for 4 hours for X, Y, Z each.			
Complex environment Temp					1) Sin Wave Test			
	Voltage Drop	Max	Max 10mV/A		Division	Condition		
				-	Ambient temperature/humi dity	Refer to figure 4-8, 90~95%		
	Temperature Rise	Max 40°C			Applied current	Basic current (Connector electrodes in series.)		
	Instant short circuit	Max 10 <i>⊭</i> s			Current application cycle	120 CYCLE (45 minutes-ON, 15 minutes-OFF)		
					Vibration acceleration	4.4G		
					Frequency	20Hz ~ 200Hz (sweep time: 3 minutes or less)		
					Vibration time	40 hours for X, Y, Z each		
					Connector attaching method	Test mode A, B, C		

3.4. Applied Part No List

TE Part no	Description
0-936248-2	090 SEALED 2P PLUG ASS'Y
0-936291-2/8	090 SEALED 2P CAP ASS'Y
0-936311-1	COVER HSG FOR .090 SEALED 2P PLUG CONN'R
0-936251-2/3	090 SEALED 3P PLUG ASS'Y
0-936292-2	090 SEALED 3P CAP ASS'Y
0-936312-1	COVER HSG FOR .090 SEALED 3P PLUG CONN'R
0-936578-2	090 SLD CHIP RESISTOR CONN-CAN
0-936584-2	090 SLD 2P PLUG ASSY FOR CAN

Rev.A **7** of 7