PRODUCT SPECIFICATION

1. SCOPE

1.1. Content

This specification covers the performance requirements for the AMP-LEAF* connector assembly, with .000015 gold plated contacts and housings molded with either phenolic or thermoplastic material.

1.2. Qualification

When testing or inspecting the subject product, this document shall always be supported by the applicable product drawing and by 109-9000, Packaging Components Division Connector Test Methods. In case of conflict the order of document precedence is as follows:

- A. Product Drawing
- B. This Product Specification
- C. 109-9000: Packaging Components Division Connector Test Methods

2. APPLICABLE DOCUMENTS

- 2.1. Applicable portions of the following documents form a part of the manufacturing control of this product.
 - A. MIL-G-45204: Gold Plating, Electrodeposited
 - B. MIL-STD-105: Sampling Procedures and Tables for Inspection by Attributes
- 2.2. The following documents describe handling and use of this product.
 - A. 109-9000: Packaging Components Division Connector Test Methods
 - B. MIL-STD-202: Test Methods for Electronic and Electrical Component Parts
 - C. MIL-STD-275: Printed Wiring for Electronic Equipment
- 3. PERFORMANCE REQUIREMENTS
- 3.1. Ratings
 - A. Current: 5 amperes max per contact
 - B. Temperature: ~55° to 105°C


* Trademark of AMP Incorporated.

⊕ I Æ⊃					CHK That	9-27-15	AMP INCORPORATE Harrisburg, Pa.					
					Dn/Bu	he 8/27/75	LOC B	Α	801° ⁰	-9014	REV F	
DIST	ਜ	Revised & retyped	AI.	8-27 -75	SHEET 1 OF <u>5</u>		TOR, AMP-LEAF, PHENOLIC HERMOPLASTIC HOUSING					
14	LTR		APP	DATE		OK ITI	SKMO.	τLΛ	PIIC U	DUITIO		

4	
0	
9	
ω	
Ö	
ON	

3.2. Test Requirements a	nd Procedures Summary	
Test Description	Requirement	Procedure
Examination of Product	Meet requirements of drawing.	Dimensional and visual.
Termination Resistance,	.006 ohm max, with wire	50 mv max open circuit,
Low Level	AWG 20 or larger.	100 ma max short circuit.
Termination Resistance,	.006 ohm max, with wire	5 amp.
Rated Current	AWG 20 or larger.	
Insulation Resistance	5,000 megohms min initial, 1,000 megohms min final.	500 vdc.
Dielectric Withstanding	Altitude Test Voltage,	Unmated connectors, test
Voltage	rms	between adjacent contacts,
	sea level 1800	and contacts to mounting
	50,000 ft 675	hardware.
	2 ma max leakage.	
Contact Engaging Force	16 oz max per contact pair.	Max thickness gage .070.
Contact Separating Force	2 oz min per contact pair.	Size 3 times with max thick-
		ness gage .070. Check with
		min thickness gage .054.
Connector Mating Force	16 oz max average per	Max thickness gage .070.
	contact pair.	
Durability	No mechanical damage;	100 matings and unmatings
	meet limits of contact sep-	using max gage .070, for
,	aration force and termina-	.000015 gold plate.
	tion resistance.	
Thermal Shock	No evidence of physical	-55° to 105°C, 5 cycles.
	damage; mate and unmate	
	with max thickness gage.	
Vibration	No interruption of continuity	10-55 Hz; .06 in total excur-
	greater than 1 microsecond.	sion; mated with printed
	No physical damage.	circuit board.
Physical Shock	No interruption of continuity	100 G's, 6 msec, sawtooth;
<u>-</u>	greater than 1 microsecond.	mated with printed circuit
	No physical damage.	board.
Humidity, Steady State	Meet insulation resistance	Unmated, 90-95% RH,
	and dielectric withstanding	40° ± 2°C, 96 hr.
	voltage.	
Contact Retention	Contacts shall not dislodge	Axial load of 10 lb applied
(Crimped Contacts)	from its normal locking	to contacts lead, AWG 20 or
	position.	larger.

Figure 1 (cont)



SHEET 2_OF<u>5</u>

NAME

CONNECTOR, AMP-LEAF, PHENOLIC OR THERMOPLASTIC HOUSING

	Test Description	Requirement				Procedure			
108-9014	Crimp Resistance	Size, AWG 26 24 22 20	Cur- rent, amp 1.0 3.0 5.0 7.5	Resist milliohr Initial 2.5 2.0 1.2 0.7 0.5	*	Measure potential drop across crimped contact between wire as it enters the wire barrel and the end of the wire barrel nearest the contact transition.			
ON	Current Cycling	1	Crimp resistance shall not exceed "final" value.			125% rated current for 30 min, 15 min no current, total of 50 cycles.			
	Crimp Tensile	Wire AW 20 22 22 22 22	/G 6 4 2	Tensi Stren 1b m 5 8 12 20	gth, in	Axial tensile load as shown. Wire shall not separate from contact.			

Figure 1 (end)

18

30





Figure 2
Termination Resistance Test Circuit



5	į	-
-	-	-
	_	3
_		
Ç	,	ð
()	
C	ľ	7
2	_	•
_	_	_
0		
		4106-801 °

3.3. Connector Tests and Sequence					
Test	MIL-STD-202	109-9000 Requirement	Test Sequence (a)		
1030	Method	Paragraph	1	2	3
Examination of Product		5.1.	Х	Х	Х
Connector Mating Force		5.8.		X	
Termination Resistance, Low Level (b)		5.2.	Х	X	
Termination Resistance, Rated Current (b)	307	5.3.	X	X	
Insulation Resistance	302, cond B	5.4.	X	X	
Dielectric Withstanding Voltage	301	5.5.	X	X	
Contact Engaging Force		5.6.		X	
Contact Separation Force		5.7.		X	
Thermal Shock (c)	107, cond A	5.11.	X		
Durability		5.10.	X	X	
Contact Separation Force					
Vibration (d)	201	5.12.		X	
Physical Shock (d)	213, cond I	5.13.		X	
Humidity, Steady State	103, cond B	5.14.	X		
Insulation Resistance, Final					
Dielectric Withstanding Voltage	<u> </u>			<u> </u>	
Termination Resistance, Low Level (b)		5.2.	X	X	
Termination Resistance, Rated Current (b)		5.3.	X	X	
Contact Retention		5.16.	X	X	
Crimp Resistance		5.17.			Х
Current Cycling		5.18.			X
Crimp Resistance		5.17.	_	<u> </u>	X

- (a) Test Sequence 1 and 2 are for connectors with contacts and hardware. Test Sequence 3 is for contacts.
- (b) See Figure 2.


Crimp Tensile

- (c) Upper temperature limit 105°C.
- (d) See Figure 4.

Figure 3


3.4. Selection of Test Samples

- A. Test samples shall consist of 6 connectors of the greatest number of positions of each connector type offered, 3 each Test Sequence 1 and Test Sequence 2. Two additional specimens shall be selected from the least number of positions offered and tested to Test Sequence 2.
- B. Thirty contacts of each style and desired wire size shall be tested to Test Sequence 3.



OR THERMOPLASTIC HOUSING

3.5. Acceptance Quality Level
MIL-STD-105, Inspection Level II, Normal
Inspection, AQL 1.5%.



Notes:

- 1. Dimensions are in inches.
- 2. Unless otherwise specified, tolerance is ±.005.
- 3. The test card shall extend 4.00 \pm .02 from the receptacle after insertion.
- 4. Number of contacts shall be the same as on the corresponding printed wiring connector.
- Printed circuit test board shall be 2 oz copper and gold over nickel plated per MIL-STD-275.
- 6. This dimension shall be the minimum connector card slot length minus .008.
- 7. Conductor configuration optional beyond card slot depth.
- 8. Printed wiring shall be identical on both sides.

Figure 4
Printed Circuit Test Board

