

**Class 1**



**CI 1-80/500**

**Product Specification Vehicle Charge  
Inlet Type CCS1 Larger AC – 95mm2**

**TABLE OF CONTENTS**

1. Scope.....	2
1.1. Introduction .....	2
2. APPLICABLE DOCUMENTS .....	3
2.1. TE Connectivity Documents .....	3
2.2. Other Documents.....	4
3. REQUIREMENTS.....	5
3.1. Design and Construction .....	5
3.2. Material .....	5
3.3. Product Ratings .....	5
3.4. Performance requirements and Test descriptions.....	7
3.5. Test Requirements and procedures summary: .....	8
4. Temperature Rise curves: .....	11
4.1. 500A T-Rise curve .....	11

## 1. SCOPE

### 1.1. Introduction

The TE CCS1 charging inlet was designed to power electric and hybrid vehicles that comply with standard IEC 62196-3.

The maximum rated current for AC is 80A at the maximum voltage of 250V.

The maximum rated current for DC is 335A continuously with 1000V.

The maximum rated current for DC is 350A continuously with cooled connector and 1000V.

The maximum rated current for DC is 500A for 12min with cooled connector and 1000V.

The content of this specification covers the technical characteristics, performance and test requirements for the EV CHARGE INLET Combined Charging System Type 1 further mentioned as CCS1.

When tests are performed the following specifications and standards shall be used. All inspections shall be performed using the applicable inspection plan and customer drawing.

## 2. APPLICABLE DOCUMENTS

The following mentioned documents are part of this specification. Unless otherwise specified, the latest edition of the documents applies. In the event of conflict between the requirements of this specification and the information contained in the referenced documents, this specification shall take precedence.

### 2.1. TE Connectivity Documents

#### General Requirements

Requirement	Description
109-1 Rev. J	General Requirements for Testing

Table 1

#### Drawings

Optinal LED indicators, for more information see customer drawings.




Figure 1

Drawing	Description
CD-2402048	Charge Inlet, Assy, CCS1 Kit

Table 2

**Specifications**

Specification	Description
114-94814	Application Specification EV Charge Inlet CCS1
114-XXXXX	Ultrasonic Weld Connection Spec. (180° DC-Contact)
114-13000	Micro MATE-N-LOK Connectors
108-94519	Actuator-Specification

*Table 3***2.2. Other Documents**

Specification	Description
IEC 62196-1: 2014/06	General requirements
IEC 62196-2: 2016/02	Dimensional compatibility and interchangeability requirements for AC pin and contact-tube accessories
IEC 62196-3: 2014/06	Dimensional compatibility and interchangeability requirements for DC and AC/DC pin and contact-tube vehicle couplers
SAE J1772: 2016/02	SAE Electric Vehicle and Plug in Hybrid Electric Vehicle Conductive Charge Coupler

*Table 4*

### 3. REQUIREMENTS

#### 3.1. Design and Construction

The product has been designed to withstand its environment and the effects it has on it.

#### 3.2. Material

The Material data is available in the IMDS (International Material Data System of the Automotive Industry).

#### 3.3. Product Ratings

#### Dimensions

Mating-Face Geometry

compatible with IEC 62196-2 Sheet 2-I  
and IEC 62196-3 Sheet 3-IIIa  
See Drawing

Screw Points

#### Environmental conditions

Ambient temperature

-40 °C .... +50 °C

Max. altitude

5000m above sea-level

Protection degree

IP5KX with flaps closed condition  
IP6KX with flaps opened condition  
IPX7 Temp. reduce to 85°C




Figure 2

## **Electrical Properties**

Max. charging performance	<b>19 kW</b> (AC) / 500 kW (DC)
Type of charging current	AC / DC
Number of AC-phases	1
Number of Terminals	7 (PE, L1, L2/N, DC+, DC-, CS, CC)
Rated current	80A AC / 500A DC
Rated voltage	250V AC / 1000V
Signal pin rated current	2A
Signal pin rated voltage	30V
Type of signal transmission	Analog
Insulation resistance of adjacent contacts	200MΩ
Resistant coding	acc. IEC 61851-1
Light option	White/Green/Red/Blue nom. Voltage 11V/20mA Allowed Voltage Range 8...16V

## **Mechanical Properties**

Mating / un-mating endurance	<= 10000 cycles
Insertion force	typical <100N (depending on connector)
Retention force	typical <100N (depending on connector)
Mechanical Stability of charging socket	max. 500N in all directions (max. Lever-Length 100mm)
Vibration Level	LV214 PG17 Severity 2 (Body mount)

## **Temperature Sensoring**

Temperature Sensor Type	PT1000
Type of Sensor	DIN EN 60751
Recommended measuring current	nominal 0.1mA / max. 1mA continuous or corresponding pulse/pause ratio
Temperature Sensor Offset DC (steady state)	max. -5K
Temperature Sensor Offset AC (steady state)	-12K TYP.
Proposed Shutdown DC	- continuous monitored dT/dt (Temperature rise per time) > 1,5K/sec <ul style="list-style-type: none"> <li>• Delta T between DC+ and DC- &gt;12K</li> <li>• 85°C measured temperature at sensor (Equivalent to max. contact temperature 90°C)</li> </ul>
Proposed Shutdown AC	78°C measured temperature at sensor (Equivalent to max. contact temperature 90°C)

## **Actuator**

See TE Actuator-Specification TE-108-94519

## Installation

Orientation  
Max. Angle

see picture below  
 $180^{\circ} - 60^{\circ} / +5^{\circ}$




Figure 3



### 3.4. Performance requirements and Test descriptions

The product shall be designed to meet the electrical, mechanical, and environmental performance requirements specified in table 5. All tests shall be performed in the room temperature, unless otherwise specified.

### 3.5. Test Requirements and procedures summary:

#### General Test

Test Items	Requirements	Procedures
<b>OPTICAL INSPECTIONS</b>		
Visual and Dimensional examination	Meets requirements of product drawing	Acc. To DIN EN 60512-1-1:2003-01, E 0.1
<b>MECHANICAL INSPECTIONS</b>		
Mechanical stability of the charging socket	Max. Force at initial crack; >500N.	At a mated condition of dummy plug and charge inlet HSG, Max. initial breakage force applied on the dummy plug at 100mm distance recorded.  As per Special mechanical test
Function of the Primary and Secondary lock / latch play	The latch must be checked by pulling the inserted pins $\leq 10\text{N}$	The primary locking latch device must latch with an audible click while pins insertion and checked by pulling the pins by force $\leq 10\text{N}$  Acc. to LV214: 2010-03, E 6.2
	At the final stop, it must be possible to lock the secondary locking device.	At final position of secondary lock, it should be locked.  Acc. to LV214: 2010-03, E 6.3
Actuation forces of the secondary lock	Closing forces of the secondary lock  Closing Force of Sec. Lock AC $F_C < 50\text{N}$  Closing Force of Sec. Lock DC $F_C < 50\text{N}$	The secondary lock actuation from pre-lock to end-lock $F_C < 50\text{N}$  Acc. to LV214: 2010-03, E 6.4
	Closing NOK forces of the secondary lock, selectively loaded  Closing NOK Force of Sec. Lock AC $F_{C\text{ NOK}} > F_C + 50\text{N}$  Closing NOK Force of Sec. Lock DC $F_{C\text{ NOK}} > F_C + 50\text{N}$	The secondary lock actuation from pre-lock to end-lock at contact pin half insertion $F_{C\text{ NOK}} > F_C + 50\text{N}$  Acc. to LV214: 2010-03, E 6.4

	Contact insertion forces  Value Determination	Acc. to LV214:2010-03, E 8.1												
Contact retention in the charge inlet housing	Contact removal force, Primary lock only  Contact Ø3, CP and PP $F_{S\leq 1mm} > 120N$  Contact Ø6, PE $F_{S\leq 1mm} > 120N$  Contact Ø6, AC $F_{S\leq 1mm} > 120N$  Contact Ø8, DC $F_{S\leq 1mm} > 180N$	Acc. to LV214:2010-03, E 8.2.1												
	Contact removal force, Primary and secondary lock  Value Determination	-												
Vibration Test   <b>Key</b> X frequency, Hz Y power spectral density, (m/s²)²/Hz 1 standard random test profile 2 additional profile in case of $f_n < 30$ Hz	No physical damage of housings and contacts, no derogation of function; the connection may not open during the test.  Test VII Commercial vehicle, sprung masses, Table 12  <table><caption>Table 12 — Values for PSD and frequency</caption><thead><tr><th>Frequency Hz</th><th>PSD (m/s²)²/Hz</th></tr></thead><tbody><tr><td>10</td><td>18</td></tr><tr><td>20</td><td>36</td></tr><tr><td>30</td><td>36</td></tr><tr><td>180</td><td>1</td></tr><tr><td>2 000</td><td>1</td></tr></tbody></table> <b>NOTE</b> r.m.s. acceleration value = 57,9 m/s².	Frequency Hz	PSD (m/s²)²/Hz	10	18	20	36	30	36	180	1	2 000	1	Acc. To ISO16750-3:2012, 4.1.2.7  (Acceleration 57.9 m/s² (5g))
Frequency Hz	PSD (m/s²)²/Hz													
10	18													
20	36													
30	36													
180	1													
2 000	1													
Mechanical shock  	Operation mode not in function  Level of sharpness level 2 Acceleration 500 m/s² (50g) Pulse form half-sinusoidal Pulse duration 6 ms Number of axes 3 axis (X, Y, Z) Shocks per axis 10 shocks (10 per direction) Total number of shocks 30 shocks	Acc. to ISO 16750-1, 4.2.2.2  (10 successive shocks in 3 axis X, Y and Z is 30 shocks)												


ELECTRICAL INSPECTIONS		
Functional Test	<p>Measure the 4,4kOhm Coding-Resistor, R5</p> <p>Measure the resistance of the signal pins to the related 12pos header pins.</p> <p>Check the PCB socket contacts for wear</p> <p>Measure the three temperature sensors and validate versus actual charge inlet temperature</p> <p>Drive actuator in lock and unlock position as per drawing</p> <p>Measure contact resistance for all power contact terminals (AC, PE, and DC)</p>	As per customer drawing
Temperature Shock	<p>The product requirements shall be maintained during the test.</p> <p><math>T_{min} - 40^{\circ}\text{C}</math>, <math>T_{max} 85^{\circ}\text{C}</math> Dwell Time - 45min each, 144 cycles</p>	<p>Acc. to IEC 60068-2-2 (Vibration)</p> <p>Acc. to IEC 60068-2-14 (Environment)</p>
Insulation Resistance	$R_{iso} > 200\text{M}\Omega$ at 1000V DC	Acc. to ISO 60512-3-1
Temperature Rise	<p>Temperature Rise with HPC (High power charging) cooling system Supplied current 500A, 600A, and 700A to inlet, Monitoring T-rise, terminal temp. <math>90^{\circ}\text{C}</math> max.</p> <p>Refer <i>Figure 4</i>, <i>Figure 5</i> and <i>Figure 6</i> for T-Rise curve</p>	-
ENVIRONMENTAL INSPECTIONS		
Aging in Dry Heat	The product requirements shall be maintained during the test.	<p>Acc. To IEC 60068-2-2</p> <p>Temp <math>85^{\circ}\text{C}</math> Test Duration - 120 h</p>
Humidity	<p>The product requirements shall be maintained during the test.</p> <p>The test is concluded with functional test in normal climate.</p>	<p>Acc. to IEC 60068-2-78</p> <p>Temp <math>65^{\circ}\text{C}</math> 93% humidity 100h</p>

Degree of Protection	Grade	Acc. To below specs
	Dust (with flap closed) <ul style="list-style-type: none"> <li>- IP5KX</li> <li>- IP6KX</li> </ul> Water (with flap removed) <ul style="list-style-type: none"> <li>- IPX5</li> <li>- IPX6</li> <li>- IPX7</li> <li>- IPX9K</li> </ul> 1) No medium must penetrate in quantities, which do not impair performance and study (possible use of water finding paste and visual inspection)	ISO 20653 – High velocity water ISO 20654 – Strong high velocity water ISO 20656 – High pressure/steam-jet cleaning ISO 20655 – Temporary Immersion ISO 20657 – Dust protection ISO 20659 – Dust Tight

Table 5

#### 4. TEMPERATURE RISE CURVES:

##### 4.1. 500A T-Rise curve



500A continuous current until 12 min at Ambient temperature of 20°C

Figure 4

LTR	REVISION RECORD	DWN	APVD	DATE
1	INITIAL DOCUMENT	SUPRIYA S	AMRUTHA R C H	27 NOVEMBER 2024
A	RELEASE TO PRODUCTION	SUPRIYA S	AMRUTHA R C H	27 NOVEMBER 2024
A1	ELECTRICAL PROPERTIES- MAX. CHARGING PERFORMANCE VALUE UPDATED	ABHIJIT N S	KASHYAP P B	20 NOVEMBER 2024