

	Table of Contents	Page
1.	Introduction	4
1.1	Purpose	4
1.2	Scope	4
1.3	Conclusion	4
1.4	Product Description	4
1.5	Test Samples	4
1.6	Qualification Test Sequence	5
2.	Summary of Testing	6
2.1	Examination of Product	6
2.2	Termination Resistance	6 ~ 8
2.3	Mating & Un-mating	8
2.4	Insulation Resistance	9
2.5	Dielectric Withstanding Voltage	10
2.6	Vibration & Physical shock	10
2.7	Solder Ability	10
2.8	Resistance to Soldering Heat	10
2.9	Durability	10
2.10	Industrial Gas SO2	10
2.11	Salt Spray	10
2.12	Current Rating	10
3.	Test Methods	11
3.1	Examination of Product	11
3.2	Insulation Resistance	11
3.3	Dielectric Withstanding Voltage	11
3.4	Contact / Termination Resistance	11
3.5	Durability	11
3.6	Humidity (Steady)	11
3.7	Thermal Shock	11
3.8	Vibration (Random)	11
3.9	Physical Shock	12
3.10	Temperature Life	12
3.11	Mating Force	12
3.12	Un-mating Force	12
tyco	Electronics SPEC No:	REV: PAGE:
-7	501-51064	A 2 of 12 This controlled document is subject to change. Use StarTEC to verifi

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU OTHER THAN TO TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORISATION FROM TYCO ELECTRONICS.

Tyco Electronics Singapore Pte Ltd

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

3.13	Solder Ability	12
3.14	Resistance to Soldering Heat	12
3.15	Current Rating	12
3.16	Industrial Gas SO2	12
3.17	Salt Spray	12

tyco

501-51064

SPEC No:

Electronics

064

REV:

Α

Tyco Electronics Singapore Pte Ltd

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

PAGE:

Qualification Test Report

1. Introduction

1.1 Purpose

Testing was performed on Serial ATA (SATA) plug and receptacle connectors, so as to determine its conformance to the requirements of Design Objectives 108-51052-1 Rev A.

1.2 Scope

This report covers the electrical, mechanical and environmental performance of, Serial ATA (SATA) plug & receptacle connector manufactured by Tyco Electronics Manufacturing (S) Pte Ltd.

1.3 Conclusion

The Serial ATA (SATA) plug & receptacle connector meets all the electrical, mechanical and environmental requirements of Design Objectives 108-51052-1 Rev A.

1.4 Product Description

The Serial ATA (SATA) plug connector, housing material is made of high temperature thermoplastics, glass filled, UL94V-0. The contacts are made of Brass. Contacts finish were 0.76 μ m min. Au on mating area and 1.91 μ m min. Sn on solder area, over 1.27 ~ 2.54 μ m Ni on entire contact.

The Serial ATA (SATA) receptacle connector, housing material is made of high temperature thermoplastics, glass filled, UL94V-0. The contacts are made of phosphor bronze. Contacts finish were Au over nickel and Tin over nickel.

1.5 Test Samples

The test samples used for the qualification were randomly selected from production and the conditions of the parts used for each test were summarized in the table below:

Description	Part No.
Serial ATA (SATA) Connector, Plug (15+7+4P)	84998-2
Serial ATA (SATA) Connector, Receptacle (Backplane)	1735284-1, -2, -3 & -4

tuco /	Fleetrenice	SPEC No:	REV:	PAGE:
tyco	Electronics	501-51064	А	4 of 12

Tyco Electronics Singapore Pte Ltd

Test	Test Group							
	1	2	3	4	5	6	7	8
		I	Т	est Seq	uence (a)	I	
Examination of product	1,5	1,9	1,8	1,8	1,5	1,5	1,4	1,3
Low level Contact resistance	2,4	3,7	2,4,6		2,4	2,4	3	
Insulation Resistance				2,6				
Dielectric withstanding voltage				3,7				
Current rating			7					
Solder ability								2
Soldering Heat resistivity							2	
Mating force		2						
Un-mating force		8						
Durability	3	4(b)						
Vibration (Random)		5						
Physical shock		6						
Reseating			5					
(manually plug/unplug 3 time)								
Humidity				5				
Temperature life			3					
Thermal shock				4				
Salt spray					3			
Industrial Gas (SO2)						3		

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER. DISCLOSURE IS MADE BY YOU OTHER THAN TO TYCO ELECTRONICS PERSONNEL_WITHOUT WRITTEN AUTHORISATION FROM TYCO ELECTRONICS.

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

2. Summary of Testing

2.1 Examination of Product – All Groups

All samples were visually inspected under the scope and found to be free from any physical damages such as cracks, change of colour, corrosion etc.

2.2 Termination Resistance - <u>Test Group 1, 2, 3, 5, 6 & 7</u>

All samples meet the requirement of 30 m Ω (maximum) initial termination resistance. All samples meet the requirement of ΔR 15 m Ω (maximum) after test / environmental conditions.

Test Group (TG)	1 (Durability)		
Test Condition	Initial	After	
Sample size	5	5	
No. of measurement	50	50	
Overall average	15.42	15.35	
Overall minimum	14.29	14.37	
Overall maximum	17.88	17.31	
ΔR (max)	-	0.62	

All Termination Resistance Measurement in $\ensuremath{m\Omega}$

Test Group (TG)	2 (Vibration & Physical Shock)			
Test Condition	Initial	After Physical Shock		
Sample size	5	5		
No. of measurement	50	50		
Overall average	15.45	15.51		
Overall minimum	12.86	14.49		
Overall maximum	17.54	16.93		
$\Delta \mathbf{R}$ (max)	-	2.47		

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU OTHER THAN TO TYCO ELECTRONICS PERSONNEL_WITHOUT WRITTEN AUTHORISATION FROM TYCO ELECTRONICS.

CO /	Electronics	SPEC No:	REV:	PAGE:
/		501-51064	Α	6 of

Tyco Electronics Singapore Pte Ltd

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

12

ty

Test Group (TG)	3 (Temperature Life)				
Test Condition	Initial	After Temperature Life	After Reseating		
Sample size	5	5	5		
No. of measurement	50	50	50		
Overall average	15.32	15.32	15.26		
Overall minimum	13.69	13.64	13.61		
Overall maximum	17.18	17.51	17.39		
$\Delta \mathbf{R}$ (max)	-	0.60	1.06		

Test Group (TG)	5 (Salt Spray)			
Test Condition	Initial	After Salt Spray		
Sample size	5	5		
No. of measurement	50	50		
Overall average	14.97	17.55		
Overall minimum	13.85	15.16		
Overall maximum	16.77	27.91		
ΔR (max)	-	12.80		

Test Group (TG)	6 (Industrial Gas SO2)			
Test Condition	Initial	After SO2		
Sample size	5	5		
No. of measurement	50	50		
Overall average	15.45	16.36		
Overall minimum	12.86	14.26		
Overall maximum	17.54	21.47		
$\Delta \mathbf{R}$ (max)	-	5.56		

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU OTHER THAN TO TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORISATION FROM TYCO ELECTRONICS.

tuco		SPEC No:	REV:
tyco Electronics		501-51064	А

PAGE: 7 of 12

Tyco Electronics Singapore Pte Ltd

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

Test Group (TG)	7 (Solder Heat Resistivity)		
Test Condition	Initial	After Solder heat resistivity	
Sample size	5	5	
No. of measurement	50	50	
Overall average	15.38	15.76	
Overall minimum	14.14	14.38	
Overall maximum	16.51	17.91	
$\Delta \mathbf{R}$ (max)	-	2.49	

2.3 Mating & Un-mating – Test Group 2

The mating force meets the requirement of 2.0kgf (Max).

The un-mating force meets the requirement of 0.40kgf (Min) after 500 cycle of durability.

All force measurements in Kgf.

Test Group (TG)	2		
Test Condition	1st Cycle Mating	Final Cycle Un-mating	
Sample size	5	5	
Number of measurement	5	5	
Average	0.833	0.754	
Minimum	0.794	0.634	
Maximum	0.878	0.889	

ò	ŝ	
ON THAT I	ECTRONIC	
Ш	E	õ
N CON	TYCO	TOOT
O DC	ΤO	C L L C
D TO Y(THAN	TVCOT
SCLOSE	OTHER	N EDOM
ID IS DI	YOU	OTT A ST
LAN	ВΥ	I O I
DENTIA	MADE	TILL A LET
INFI	SI	ET C
THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO	FURTHER DISCLOSURE IS MADE BY YOU OTHER THAN TO TYCO ELECTRONICS'	SOURCELLS IN OUT A STRUCTURE A LEADER AND THAT
RM⊿	DIS	10 10
HIS INFO	URTHER	TANOS DE
E.	Ē.	-2

CO /	Electronics	SPEC No:	REV:	PAGE: 8 of 12
•		501-51064	A	0 01 12
			This controlled document is a	ubject to change Lise StarT

Tyco Electronics Singapore Pte Ltd

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

tu

2.4 Insulation Resistance – Test Group 4

All insulation resistance readings between adjacent contacts were greater than $1000M\Omega$ (initial & final).

Test Group (TG)	4 (Thermal Shock & Humidity)		
Sample Condition	Mated		
Test Condition	Initial	After Humidity	
Sample size	5	5	
Number of measurement	50	50	
Average	6.248E+13	1.323E+14	
Minimum	2.192E+13	1.470E+13	
Maximum	9.561E+13	5.154E+14	

Test Group (TG)	4 (Thermal Shock & Humidity)		
Sample ID	SATA Backplane Receptacle		
Sample Condition	Un-mated		
Test Condition	Initial	After Humidity	
Sample size	5	5	
Number of measurement	50	50	
Average	5.188E+13	1.047E+14	
Minimum	3.359E+13	1.345E+13	
Maximum	9.998E+13	4.786E+14	

Test Group (TG)	4 (Thermal Shock & Humidity)	
Sample ID	SATA Plug	
Sample Condition	Un-mated	
Test Condition	Initial	After Humidity
Sample size	5	5
Number of measurement	50	50
Average	6.995E+13	6.739E+13
Minimum	2.575E+13	1.663E+13
Maximum	9.999E+13	2.008E+14

REV:

Α

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER. DISCLOSURE IS MADE BY YOU OTHER THAN TO TYCO ELECTRONICS PERSONNEL_WITHOUT WRITTEN AUTHORISATION FROM TYCO ELECTRONICS.

tyco	/	Electronics
------	---	-------------

501-51064

SPEC No:

Tyco Electronics Singapore Pte Ltd

This controlled document is subject to change. Use StarTEC to verify the latest revision. Un-controlled copies may be printed from StarTEC for reference.

2.5 Dielectric Withstanding Voltage – Test Group 4

No dielectric breakdown or flashover or leakage of current greater than 5mA occurred when a test voltage of 500 VAC was applied between adjacent contacts of mated and unmated connector assemblies.

2.6 Vibration & Physical Shock - Test Group 2

No Sample failed the electrical discontinuity.

2.7 Solder Ability – Test Group 8

All contact leads showed more than 95% solder coverage with no voids and pins hole observed.

2.8 Soldering Heat Resistivity– Test Group 7

No physical damage was observed after reflow.

2.9 Durability – Test Group 1 & 2

No physical damage was observed after durability.

2.10 Industrial Gas SO2 – Test Group 6

No physical damage was observed after mixed flowing gas.

2.11 Salt Spray – Test Group 5

No physical damage was observed after salt spray.

2.12 Current Rating – Test Group 3

Temperature rise meets the requirement of less than 30°C

Sample size	5
No. of measurement	20
Overall average	11.52
Overall minimum	10.36
Overall maximum	12.74

Tyco Electronics Singapore Pte Ltd

3 Test Methods

3.1 Examination of Products

Samples were physically examined under the microscope before and after each test conditions for any physical damage or abnormalities on housing and contacts.

3.2 Insulation Resistance

Insulation resistance was measured between adjacent contacts of connector, using a test voltage of 500 VDC. Record reading after 1 minute. (EIA-364-21)

3.3 Dielectric Withstanding Voltage

A test potential of 500 Vdc was applied between adjacent contacts of connector. This potential was held for 1 minute with a current leakage not greater than 5mA. (EIA-364-20, Method B)

3.4 Contact/Termination Resistance

Measurements shall be made on mated connector, at a voltage of 20mv max open circuit at a current of 100mA. (EIA-364-23)

3.5 Durability

Subject connector to 500 cycles of repeated mate and un-mate, with an operation speed of 200 cycles per hour. (EIA-364-09)

3.6 Humidity (Steady)

Subject mated connectors to relative humidity of $90\sim95\%$ RH, temperature of $40\pm2^{\circ}$ C for 96 hours. (EIA-364-31, Method II, Condition A)

3.7 Thermal Shock

Subjected mated connectors to temperature -55°C to +85°C for 10 cycles, each temperature dwell time 30 minutes. (EIA-364-32, Condition I)

3.8 Vibration (Random)

Subject mated connectors for 30 minutes in each of 3 mutually perpendicular planes. Frequency of 50 ~ 2000Hz with 5.35 g's RMS. (EIA-364-28, Condition V, Letter A)

REV:

Α

tyco

501-51064

SPEC No:

Tyco Electronics Singapore Pte Ltd

PAGE:

Electronics

3.9 Physical Shock

Subject mated connector to 50Gs half sine pulses of 11ms duration along the 3 mutually perpendicular planes. (EIA-364-27, Condition H)

3.10 Temperature Life

Subject mated connector to $85\pm2^{\circ}$ C for 500 hours. (EIA-364-17, Method A, Condition III)

3.11 Mating Force

Mate connector assembly at a rate of 12.5mm per minute.

3.12 Un-mating Force

Un-mate connector assembly at a rate 12.5mm per minute.

3.13 Solder Ability

Immerse solderable portion of contact in molten solder at 245°C for 5 seconds.

3.14 Resistance to Soldering Heat

Test connector per EIA-364-56B, procedure 6, level 4.

3.15 Current Rating

Wire contact P1, P2, P8 & P9 in parallel for power. Wire contact P4, P5, P6, P10 & P12 in parallel for return.

Apply 6A total DC current to parallel contacts P1, P2, P8 & P9 and return from parallel contact P4, P5, P10 & P12.

3.16 Industrial Gas SO2

Electronics

Subject mated samples to 25ppm of SO2 gas, 96%RH, 25°C for 24 hours per AMP 109-5107.

3.17 Salt spray

Subject mated samples to 5% salt concentration for 24 hours per AMP 109-5101.

REV:

Α

tyco

501-51064

SPEC No:

Tyco Electronics Singapore Pte Ltd

PAGE: