APPLICATION SPECIFICATION

MINI MIC REC. CONTACT FOR SINGLE WIRE SEALING

WITH 5.6 mm OUT. DIA.

SCOPE

This specification covers the requirements for application of MINI MIC REC. CONTACTS.

P.N.s involved are listed in the table of Fig. 7.

GENERAL

These contacts are suitable for 0,35 -1,5 mm2 wire, with single wire seals.

Each wire is inserted into a discrete wire seal before to be crimped into the contact.

The insulation barrel is crimped so that the wire seal is gripped in order to avoid any movement of the seal.

The contacts are suitable for single wire only.

The indications on the figures are valid for receptacle contacts.

1. CRIMPING

RELEASED PER ECN ET0039/

REVISION RECORD

FIRST ISSUE

The following information contains nomenclature, crimping conditions, crimp data for mini-applicators, insertion of wire seals on cables, mending or replacement of parts and checks.

IPL 444 P.C. 0933 OR S. SERRA AMP ITALIA 8.p.A. DALLA RIVA Corso F.III Cervi, 15 COLLEGNO (TORINO) CHY REVISED EC ETOD-0416-99 11. P NO REY. LOC. REVISED EC ETOO-0488-37 114-20062 REVISED EC ETOD-0154-97 B NAME

DIST.

034

0

REV


SHEET

Ī

ME APPLICATION SPECIFICATION FOR MINI-MIC CONTACT FOR SINGLE WIRE SEALING WITH 5.6 mm OUT.DIA.

1 OF 6

1.1 NOMENCLATURE






Fig. 1

2. CRIMPING CONDITIONS

Refer to nomenclature (Par. 1.1) see Fig. 1 Fig. 2 and Fig. 3.

1.	Cut-off tab length	0,3 mm MAX				
2.	Front bellmouth	$0,10 \times 45^{\circ} MAX$				
	Rear bellmouth	$0,25 \times 60^{\circ} MIN$				
3.	Bend up	5° MAX				
	Bend down	5° MAX				
	Bend right	5° MAX				
	Bend left	5° MAX				
	Rolling	5° MAX				
4.	Cable end protrusion	0,2 to 0,7 mm				

(brush length) 5. Insulation stripping

length 3,0 to 3,5 mm 6. Wire barrel seam must be neatly closed.

2.83

035

166

AMP ITALIA S.p.A. Corso F.III Cervi, 15 COLLEGNO (TORINO) LOC. SHEET I 2 OF 6

114-20062

NO

REV. (1





Fig. 2



<u>Fig. З</u>

3. CRIMP DATA

3.1 For applicator crimping see Fig. 7.

4. INSERTION OF RUBBER WIRE SEAL ON THE CABLE

When the rubber seal is installed on cable, the end of the cable insulation shall be positioned from the edge of the rubber seal, as shown in Fig. 4. This length is usually regardless of cable size.

NOTE: Seals are supplied lubricated. This lubrication must not be removed.




Fig. 4

AMP


AMP ITALIA S.p.A. Corso F.III Cervi, 15 COLLEGNO (TORINO) I 3 OF 6


NO 114-20062


(1.

5. CORRECTION OR REPLACEMENT OF PARTS

When defects and/or improper applications are found on parts to be installed, as shown in Fig. 5, rework to set up properly, or replace with new part.









The end of the cut wire shall appear neat without any bend of stranded conductor

The conductor shall be free from nick, cut and scrape.


The wire insulation must have smooth surface in a round form without damage, groove or recessed surface.



The end of the wire shall be straight without bend and untidiness after insertion of the wire seal. The bent wire seal be checked out



The flanges of the rubber seal shall be free from cut and damage. Any seal having such defects shall be discarded, and replaced with new part.




Insertion of rubber seal shall be done straightly and evenly. If flanges are in tilt condition, the plug must be corrected so that flanges are perpendicular to contact center line.

Fig. 5

5.1 After crimping, the part of the cable insulation that is inside the seal shall be in good condition and within the requirements shown in Figure 5. Check by visual inspection in the transition area (between wire and insulation barrel), as indicated in Figure 6.

After crimping the rubber seal must protude from the insulation crimp without any damage



After crimping no parts of insulation or rubber in the wire crimp is allowed

Part of rubber seal must stick out from transition hole

Tilt shape of rubber wire is not allowed





Fig. 6

5.2 Crimped contacts should appear as illustrated in Par. 1.1 (Nomenclature).

LOC.



Flg. 7

(Dimensions are in mm)

REC. CONTACT

DADE NO	WIRE	LITER CRAT	STRIP	WIRE BARREL CRIMP			INS. BARREL CRIMP		
PART NO.	SIZE mm ²			HEIGHT + 0,05	WIDTH (REF.)	CRIMPER TYPE	HEIGHT (REF.)	WIDTH (REF.)	CRIMPER TYPE
282110-1	1,5	2,2÷2,4 (828905-1)	3,0+3,5	1,39	2,28	F	4 , 00	3,68	0
	1 0	1,9 : 2,1 (828904-1)		1,22	2,28	F	3,80	3,68	0
	0, 7 5	1,9÷2,1 (828904-1)		1,14	2,28	F	3,75	3,68	0
282403-1	0,5	1,5÷1,7 (828904-1)	3,0:3,5	1,09	1,78	F	3,75	3,68	0
	0,35	1,45÷1,55 (828904-1)		1,02	1,78	F	3,70	3,68	0