



REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
	A	-	-	-

SPECIFICATIONS

INPUT VOLTAGE: 3.0
INPUT FREQUENCY: 2.5 KHZ
ELECTRICAL STROKE: +/- 1.000 " [25.4]
SENSITIVITY: .65 mv / VOLT / .001"
SENSITIVITY: 25.6 mv / VOLT / m.m
LINEARITY: 0.25% OF FULL RANGE
PHASE SHIFT: +1.0 DEGREES
PRIMARY IMPEDANCE: 1665 OHMS
SECONDARY IMPEDANCE: 1660 OHMS

REVISIONS			
REV.	DESCRIPTION	DATE:	APPR.
A	REVISED PER ECR/ECN #287	12/15/00	R.E.A.



MATERIAL:

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES TOLERANCES ARE: ANGLES: +/- 0.5 DEG. FRACTIONS: +/- 1/64 DECIMAL: XX= +/- .01 XXX= +/- .005	DRAFTSMAN: R.E.A.	DATE: 08 MAR 00	Macro Sensors Div. of Howard A. Schaevitz Technologies, Inc.	
	CHECKER:	DATE:		
	APPROVED:	DATE:	TITLE PR 750 1000-010 OUTLINE	
	APPROVED:	DATE:	A C.A.G.E. No. 06WW0	DRAWING No. 010912600010
FINISH:		APPROVED:	DATE:	SCALE: NONE
				SHEET No. 1 of 1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-	TE Connectivity			
		CHK	-				
DIMENSIONS: INCHES		APVD	-	NAME PR 750 1000-010 OUTLINE			
		PRODUCT SPEC					
		APPLICATION SPEC					
MATERIAL		WEIGHT		SIZE A2	CAGE CODE 00779	DRAWING NO. C=010912600010	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 of 1	REV A	