

# **Product Specification**

#### 23-Nov-2018 Rev A

# **USB Type-C Connector**

#### 1 Scope:

#### 1.1 Contents

This specification covers the requirements for product performance, test methods and quality assurance provisions of TE Connectivity USB type C connector.

Applicable product description and part numbers are as shown in Appendix 1.

## 2. Applicable Documents:

The following documents form a part of this specification to the extent specified herein. In the event of conflict between the requirements of this specification and the product drawing, the product drawing shall take precedence. In the event of conflict between the requirements of this specification and the referenced documents, this specification shall take precedence.

#### 2.1 TE Connectivity Specification:

- A. 109-5000: Test Specification, General Requirements for Test Methods
- B. 501-115162: Qualification Test Report

#### 2.2 Commercial Standard and Specification:

- A. ANSI/EIA 364-C
- B. Universal Serial Bus Type-C Connector and Cables Assemblies Compliance Document

#### 3. Requirements:

## 3.1 Design and Construction:

Product shall be of the design, construction and physical dimensions specified on the applicable product drawing.

#### 3.2 Materials:

A. Contact (Receptacle)

Material: Copper alloy

B. Housing (Receptacle)

Thermo Plastic, UL 94 V-0

C. Shell (Receptacle)

Material: Stainless steel

D. Middle plate (Receptacle)

Material: Stainless steel

#### 3.3 Ratings:

- A. Voltage Rating: 30 V Max.
- B. Current Rating:
  - (1). Connection in parallel between 4 pair VBUS pins and GND pins: 1.5A/pin Max, SBU1 and SBU2 1.0A/pin , Signal pins contact: 0.25A Min.
  - (2). Working with single circuit between pair VBUS pins and GND pins: 3A/pin Max, Signal pins contact: 0.25A Min.
- C. Temperature Rating: -40°C to 80°C (Including temperature rising)



# 108-115145

# 3.4 Performance Requirements and Test Descriptions:

The product shall be designed to meet the electrical, mechanical and environmental performance requirements specified. All tests shall be performed in the room temperature, unless otherwise specified.

Temperature: 15°C ~ 35°C

Humidity : 25% ~ 85% R.H.

Pressure : 650mmHg ~ 800mmHg

# 3.5 Test Requirements and Procedures Summary

#### Table.1

|   | Test Item                             | Procedures  | Requirements  |  |  |  |  |  |  |
|---|---------------------------------------|---|---|--|--|--|--|--|--|
|   | Examination                           |   |   |  |  |  |  |  |  |
| 1 | Visual examination of product         | Visual, dimensional and functional aspects meet requirements of product drawing and applicable instructions on customer drawing, and application specification.   | Meets requirements of product drawing and no defects.   |  |  |  |  |  |  |
|   | Electrical                            |   | ,   |  |  |  |  |  |  |
| 2 | Low Level<br>Contact<br>Resistance    | EIA-364-23 The low level contact resistance (LLCR) measurement is made across the plug and receptacle mated contacts and does not include any internal paddle cards or substrates of the plug or receptacle. Measure at 20 mV (max) open circuit at 100 mA        | 40 mΩ Max initial for VBUS, GND and all other contacts. Maximum change (delta) of 10 mΩ after environmental stresses.   |  |  |  |  |  |  |
| 3 | Insulation resistance                 | EIA-364-21 Applicable to both receptacle and plug. Apply 500V DC. Apply the above specified voltage between adjacent contacts for 1 minute.   | >100 M $\Omega$ insulation resistance between adjacent contacts of unmated and mated connectors.<br>100M $\Omega$ Min.  |  |  |  |  |  |  |
| 4 | Dielectric<br>withstanding<br>voltage | EIA-364-20, Method B. Applicable to both receptacle and plug. 100V AC (rms) for 1 minute at sea level.  | No break down shall occur when voltage is applied between adjacent contacts of unmated and mated connectors.  Leakage of electricity is less than 0.5 mA.             |  |  |  |  |  |  |
| 5 | Temperature rise                      | EIA-364-70, Method 1., Current rating for signal and power Pin, 3 hours, 1. Connection in parallel between 4 pairs VBUS pins and GND pins, each single circuit 1.5 A(DC 9V), 2. Working with single circuit between pair VBUS pins and GND pins, 3 A (DC 9V) Min. | Temperature rise of the outside shell surface of the mated connector pair above the VBUS and GND contacts shall not exceed 30°C above ambient temperature.  30°C Max. |  |  |  |  |  |  |
|   | Mechanical                            |   |   |  |  |  |  |  |  |
| 6 | Durability                            | EIA-364-09<br>10,000 cycles<br>Test speed:200 cycles/hour Max.  | Meet insertion / extraction force, no evidence of physical damage.  |  |  |  |  |  |  |
| 7 | Random<br>vibration                   | EIA-364-28, Condition VII-D, 2 hours in each of 3 mutually perpendicular directions. Both mating halves should be fixed rigidly.  (Power Spectral Density 0.02g²/Hz, Overall rms 3.10 g)  | No evidence of physical damages and no discontinuity longer than 1 microsecond.   |  |  |  |  |  |  |

Rev A 2 of 6



# **Production Specification**

108-115145

Table.1(cont.)

| Tabl | e.1(cont.)            |   |  |
|------|-----------------------|---|--|
|      | Test Item             | Procedures  | Requirements   |
| 8    | Sine vibration        | EIA-364-28B   | No evidence of physical damages and no discontinuity longer than 1 microsecond.      |
|      |                       | Amplitude: 1.52 mm(0.06 inch);  |  |
|      |                       | Frequency: 10 Hz up to 50 Hz in 1 minute, then 55 Hz  |  |
|      |                       | down to 10 Hz;  |  |
|      |                       | 2 hours in each of 3 mutually perpendicular   |  |
|      |                       | directions (X、Y、Z).   |  |
| 9    | Mechanical shock      | EIA-364-27B,half sine,30 G,duration 11 ms;X, Y,   | No evidence of physical damages and no discontinuity longer than 1 microsecond.      |
|      |                       | Z,3 times each direction, total 18 times.   |  |
| 10   | Insertion force       | EIA-364-13  | Between 5 N and 20 N before and after  |
|      |                       | Maximum rate 12.5mm/min   | durability.  |
| 11   | Extraction force      | EIA-364-13  | Extraction force:  |
|      |                       | Maximum rate 12.5mm/min   | I: no less than 8 N and no more than 20 N  |
|      |                       |   | before and after 1,000 cycles durability. II: no less than 6 N and no more than 20 N |
|      |                       |   | before and after 10,000 cycles durability.   |
| 12   | Wrenching             |   | ≥75N; (left, right, up, down)  |
|      | strength              | Apply a force on plug inserted into receptacle at a   | ≥65N; (insertion direction)  |
|      | (Reference)           | distance of 15 mm from the edge of the receptacle,  | 10,000 cycles  |
|      |                       | five directions (left, right, up, down and insertion  | No evidence of physical damages.   |
|      |                       | directions), speed : 25 mm/min,   |  |
|      |                       | Refer to Appendix 1 for test fixture  |  |
| 13   | Strength              | Test force: F3=F4=2kgf  | No evidence of physical damages.   |
|      | durability            | Applied to a plug when inserted at a distance of 15   |  |
|      |                       | mm from the edge of the receptacle. Apply 15 N force for 3,000 cycles .                     |  |
|      |                       | Speed: 15 times/min.  |  |
|      |                       | Refer to Appendix 2 for test fixture.   |  |
| 14   | 360° rotation         | Apply additional 800 g weight at a distance of 10 cm  | No discontinuity during rotation.  |
|      |                       | from the edge of receptacle, hold 10 seconds  |  |
| 15   | Tongue strength       | separately in degree 90,180, 270 and 360.  Test method: 45° insertion into receptacle,until | 70 N Min.  |
|      | 5 5 5 5 5 5 5 6 6 6 6 | tongue of receptacle is destroyed.  |  |
| 16   | Slant insertion       |   | No mechanical damage.  |
|      |                       | 1   | Contact resistance: $\triangle$ R =10m $\Omega$ Max                                  |
|      |                       | in Appendix 3].   | Scrape damage on surface allowed.  |
|      | Environmental         |   | T  |
| 17   | Thermal shock         | EIA-364-32, Method A, Condition I, duration A-4<br>(-55°-+85°C, 10 cycles)                  | No mechanical damage.  |
|      |                       | Recovery: 2 hours at ambient  |  |
|      |                       | atmosphere.   | Contact resistance: $\Delta$ R =10m $\Omega$ Max.                                    |
|      |                       | -55°C+0/-3°C: 30 minutes,   | Insulation resistance >100M $\Omega$   |
|      |                       | 25°C+/-10°C: 5 minutes Max  |  |
|      |                       | 85°C+3/-0°C: 30 minutes   |  |
|      |                       | 25°C+/-10°C: 5 minutes Max  |  |
|      | 1                     | <u>l</u>  | 1  |

Rev A 3 of 6



Table.1(cont.)

| Table | .1(cont.)                          |  | T   |
|-------|------------------------------------|--|---|
|       | Test Item                          | Procedures   | Requirements  |
| 18    | Thermal<br>disturbance             | EIA-364-32 Cycle the mated connector pair 10 times between 15°C and 85°C. Ramp > 2°C/min Dwell > 5 mins (ensure contacts reach extreme temperature) Humidity not controlled.   | No mechanical damage. $ \mbox{Contact resistance: } \Delta \mbox{ R =10m } \Omega \mbox{ Max.}                                    $   |
| 19    | Thermal cycling                    | EIA-364-32 Cycle the mated connector pair 500 times between 15°C and 85°C.Ramp > 2°C/min Dwell > 5 mins (ensure contacts reach extreme temperature).Humidity not controlled.   | No mechanical damage.<br>Contact resistance: $\Delta$ R =10m $\Omega$ Max.<br>Insulation resistance >100M $\Omega$                    |
| 20    | Salt spray                         | EIA-364-26B, temp. 35+/-2°C, 100% RH, Salt NaCl mist 5%.Clean and brush after 48 hours continuous spray on samples, , 35 degree baking within no more than 16 hours.   | No mechanical damage. $ \mbox{Contact resistance: } \Delta \mbox{ R =10m } \Omega \mbox{ Max}. $                                      |
| 21    | Cyclic temperature and humidity    | EIA-364-31B, Method IV, 25 ℃~65 ℃; 95% RH, total 240 hours  S.1 25 ℃~65 ℃,90-98%RH, 2.5 hours  S.2 65 ℃, 90-98%RH, 3 hours  S.3 65 ℃~25 ℃,80-98%RH, 2.5 hours  S.4 25 ℃~65 ℃,90-98%RH, 2.5 hours  S.5 65 ℃, 90-98%RH, 3 hours  S.6 65 ℃~25 ℃,80-98%RH, 2.5 hours  S.7 25 ℃, 2 hours, 90-98%RH  S.7a -10 ℃, 3 hours  S.7 25 ℃, 3 hours, 90-98%RH  S.1 – S.7 1 cycle 24 hours  10 cycles (240 hours) | No mechanical damage. $ \mbox{Contact resistance: } \Delta \mbox{ R =10m } \Omega \mbox{ Max.} $ Insulation resistance >100M $\Omega$ |
| 22    | Temperature life                   | EIA-364-17A, Method A, condition 4 $105^\circ\!$   | No mechanical damage.<br>Contact resistance: $\Delta$ R =10m $\Omega$ Max.<br>Insulation resistance >100M $\Omega$                    |
| 23    | Temperature life (preconditioning) | EIA-364-17A, Method A, condition 4 105 $^{\circ}$ C , 72 hours, mated condition.   | No mechanical damage.<br>Contact resistance: $\Delta$ R =10m $\Omega$ Max.<br>Insulation resistance >100M $\Omega$                    |
| 24    | Mixed flowing gas                  | EIA-364-65, class IIA, 120 hours unmated, 120 hours mated (240 hours total).  RH% 70+/-2, Temp. 30+/-1°C, Cl2: 10+/-3 ppb,  NO2: 200+/-50 ppb, H2S: 10+/-5 ppb, SO2:  100+/-20 ppb   | No mechanical damage. No change to performance. Contact resistance: $\Delta$ R =10m $\Omega$ Max.                                     |
| 25    | Resistance to soldering heat       | EIA-364-56,<br>Reflow cycles: 3<br>260°C for 30 seconds  | No evidence of physical damages   |
| 26    | Solderability                      | EIA-364-52,  Temperature: 260+/-5°C  Immersion time: 5+/-0.5 seconds   | Solderable area shall have a minimum of 95% solder coverage.  |

**NOTE:** (1) Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in the Product Qualification and Prequalification Test Sequence shown in table 2.

Rev A 4 of 6



# 3.6 Product Qualification Test Sequence

# Table.2

| $\overline{}$     | I dbie.2                              |         |            |          |         |            |      |      |      |      |      |         |                |         |         |         |
|-------------------|---------------------------------------|---------|------------|----------|---------|------------|------|------|------|------|------|---------|----------------|---------|---------|---------|
| Item/Test group A |                                       |         | В          | С        | D       | Е          | F    | G    | Н    | I    | J    | K       | L              | M       | N       | О       |
| 1                 | Visual inspection                     | 1,<br>6 | 1,         | 1, 18    | 1       | 1          | 1    | 1,7  | 1, 7 | 1, 3 | 1,6  | 1       | 1              | 1,<br>3 | 1,<br>9 | 1,<br>3 |
| 2                 | Contact resistance                    | 2,<br>5 | 2, 5, 7, 9 | 3, 15    | 4,<br>7 | 2, 5, 7, 9 | 2, 8 | 2, 4 | 2, 4 |      | 2, 5 | 2, 5, 7 | 2, 5, 7, 9, 11 |         | 2,<br>6 |         |
| 3                 | Insulation resistance                 |         |            | 17       |         |            | 9    | 5    | 5    |      |      |         |                |         | 3,<br>7 |         |
| 4                 | Dielectric<br>withstanding<br>voltage |         |            | 2, 16    |         |            | 10   | 6    | 6    |      |      |         |                |         | 4,<br>8 |         |
| 5                 | Temperature rise                      | 4       |            |          |         |            |      |      |      |      |      |         |                |         |         |         |
|                   | Reseating<br>(3 cycles)               |         | 8          |          |         | 8          |      |      |      |      |      | 6       | 10             |         |         |         |
| 6                 | Durability<br>(50 cycles)             | 3       | 3          |          | 2       | 3          |      |      |      |      | 3    | 3       | 3              |         |         |         |
|                   | Durability<br>(1,000 cycles)          |         |            | 6        |         |            |      |      |      |      |      |         |                |         |         |         |
|                   | Durability<br>(10,000 cycles)         |         |            | 9        |         |            |      |      |      |      |      |         |                |         |         |         |
| 7                 | Random vibration                      |         |            | 12       | 5       |            |      |      |      |      |      |         |                |         |         |         |
| 8                 | Sine vibration                        |         |            | 13       | 6       |            |      |      |      |      |      |         |                |         |         |         |
| 9                 | Mechanical shock                      |         |            | 14       |         |            |      |      |      |      |      |         |                |         |         |         |
| 10                | Insertion force                       |         |            | 4, 7, 10 |         |            | 3, 6 |      |      |      |      |         |                |         |         |         |
| 11                | Extraction force                      |         |            | 5, 8, 11 |         |            | 4, 7 |      |      |      |      |         |                |         |         |         |
| 12                | Wrenching<br>strength                 |         |            |          |         |            | 5    |      |      |      |      |         |                |         |         |         |
| 13                | Strength durability                   |         |            |          |         |            |      | 3    |      |      |      |         |                |         |         |         |
| 14                | 360° rotation                         |         |            |          |         |            |      |      | 3    |      |      |         |                |         |         |         |
| 15                | Tongue strength                       |         |            |          |         |            |      |      |      | 2    |      |         |                |         |         |         |
| 16                | Slant insertion                       |         |            |          |         |            |      |      |      |      |      |         |                |         | 5       |         |
| 17                | Thermal shock                         |         | 4          |          |         |            |      |      |      |      |      |         |                |         |         |         |
| 18                | Thermal disturbance                   |         |            |          |         |            |      |      |      |      |      |         | 8              |         |         |         |
| 19                | Thermal cycling                       |         |            |          |         | 6          |      |      |      |      |      |         |                |         |         |         |
| 20                | Salt spray                            |         |            |          |         |            |      |      |      |      | 4    |         |                |         |         |         |
| 21                | Cyclic temperature and humidity       |         | 6          |          |         |            |      |      |      |      |      |         |                |         |         |         |
| 22                | Temperature life                      |         |            |          |         |            |      |      |      |      |      | 4       |                |         |         |         |
| 23                | Temperature life (preconditioning)    |         |            |          | 3       | 4          |      |      |      |      |      |         | 4              |         |         |         |
| 24                | Mixed flowing gas                     |         |            |          |         |            |      |      | 1    |      | 1    |         | 6              |         |         | 1       |
| 25                | Resistance to soldering heat          |         |            |          |         |            |      |      |      |      |      |         |                | 2       |         |         |
| 26                | Solderability                         |         |            |          |         |            |      |      |      |      |      |         |                |         |         | 2       |
|                   | Sample size (PCS)                     | 5       | 5          | 5        | 5       | 5          | 5    | 5    | 5    | 5    | 5    | 5       | 5              | 5       | 5       | 5       |





Figure 2. Recommended reflow temp profile


Rev A 5 of 6




Appendix 1: Wrenching strength test fixture: F1, F2, F3, F4, F5 directions.



Appendix 2: Strength durability test fixture: F3, F4 directions.



Appendix 3: Slant insertion strength test fixture:



The applicable product descriptions and part numbers are as shown in Appendix.4.

| Product Part No. | Description  |
|------------------|--|
| 2337857-1        | USB Type-C Receptacle, Dual row SMT, Vertical Type |
|                  |  |
|                  |  |
|                  |  |

Appendix.4

Rev A 6 of 6