

# MOUNTING INSTRUCTION MU27P - Receptacle

PRJ-14-000003352

A4 printed version TCPN: YSPEC-408-157000-1

#### THIS IS A CLASS 1 DOCUMENT WHICH IS NONCONFIDENTIAL.

The information contained within this document is the property of TE Connectivity. It is supplied in confidence and the commercial security of the contents must be maintained. It must not be used for any purpose other than that for which it is supplied nor may any information contained in it be disclosed to unauthorised persons. It must not be reproduced in whole or in part without obtaining written permission from TE Connectivity (TE).

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions and design specifications.

\*Trademark. TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product and/or company names may be trademarks of their respective owners.



# **Table of Contents**

1.	INT	RODUCTION	3
2.	BIL	L OF MATERIAL	3
2	2.1	Introduction	3
2	2.2	BOM of MU. LOCO UNIT CONTROL	4
2	2.3	BOM of TYPICAL AEM-7 MU	4
2	2.4	BOM of COMMUNICATION INTERCITY	5
2	2.5	BOM of COMMUNICATION COMMUTER	
2	2.6	Exploded view	6
2	2.7	Overall dimensions	
2	2.8	Materials	7
3	TF	CHNICAL CHARACTERISTICS	7
	3.1	Applicable standards	7
_	3.2	Electrical characteristics	
	3.3	Mechanical characteristics	
3	3.4	Climatic characteristics	8
4	MO	UNTING	•
4.	IVIO		
	l.1	Panel cutting	8
	.2	Fixing receptacle	
	1.3	Preparation of the cable	
4	1.4	Cable implantation into the receptacle	9
4	<b>l.</b> 5	Contacts crimping	
4	l.6	Mounting inserts on the receptacle	10
5.	CO	NTACT CRIMPING	10
5	i.1	Manual crimping tools DMC	10
6.	MA	INTENANCE OPERATIONS	10
6	5.1	Spare parts	10



#### 1. INTRODUCTION

The MU27P connector is a standard connector for the American railway especially for locomotives. This connector is completely designed according to 2 standards:

- **AAR S-512**: Manual of Standards and Recommended Practices Locomotives and Locomotive Interchange Equipment (27 point control plug and receptacle)
- **APTA RP-E-019-99**: Recommended Practice for 27-Point Jumper and Receptacle Hardware for locomotives and Locomotive-Hauled Equipment

This document is an operating instruction to mount the receptacle. There is also the same type of documentations for the installation of the plug and the dummy. The respective references are 408-157000-2 and 408-157000-3.

#### 2. BILL OF MATERIAL

#### 2.1 Introduction

There are 4 types of connector corresponding to 4 functions on the loco. Each connector is differentiated by colour and/or by the position of insulators. The 4 types of connectors are named as follows:


 MU. LOCO UNIT CONTROLS: Position insulators at 0° and black colour for the body Commercial reference: 27P-REC-1-01





 COMMUNICATION INTERCITY: Position insulators at 42° and blue colour for the body Commercial reference: 27P-REC-2-01






- TYPICAL AEM-7 MU: Position insulators at 77,5° and white colour for the body




Commercial reference: 27P-REC-3-01





COMMUNICATION COMMUTER: Position insulators at 0° and red colour for the body Commercial reference: 27P-REC-4-01





#### **BOM of MU. LOCO UNIT CONTROL**

Item	Part number	Quantity	Designation	Weight (g)
	YG-UC-211283A-JG06	1	Receptacle body	1070.33
2	1504-0018A4	1	Axis of cover	3.95
3	1504-0005A4	1	Spring	3.56
4	1504-0019A4	1	Cover gasket	14.29
5	YA-UC-211297A-VN00	1	Receptacle gasket	52.30
6	Y0000000-7105-06-I	2	Self-locking ring	0.17
7	YK-UC-211276A-QK00	1	Mixed insulator	124.81
8	YK-UC-211315A-VP00	27	Sleeve	1.86
9	YK-UC-211275A-QK00	1	Male insulator	162.65
10	YS-UC-211945A-AA1A	24	Male contact 12/14 AWG	14.43
	YS-UC-211946A-AA1A	3	Male contact 10 AWG	14.29
12	CHCM08x25-I	3	Screw CHC M8x25	17.24
13	W-08-I	3	Washer	5.10
14	YG-UC-211287A-JG06	1	Cover	376.80

Customer drawing: C-E1894-211942 **BOM of TYPICAL AEM-7 MU** 

Rev [A]



# Instruction sheet

CLASS 1-Public

Item	Part number	Quantity	Designation	Weight (g)
1	YG-UC-211282A-JG05	1	Receptacle body	1070.35
2	1504-0018A4	1	Axis of cover	3.95
3	1504-0005A4	1	Spring	3.56
4	1504-0019A4	1	Cover gasket	14.29
5	YA-UC-211297A-VN00	1	Receptacle gasket	52.30
6	Y0000000-7105-06-I	2	Self-locking ring	0.17
7	YK-UC-211276A-QK00	1	Mixed insulator	124.81
8	YK-UC-211315A-VP00	27	Sleeve	1.86
9	YK-UC-211275A-QK00	1	Male insulator	162.65
10	YS-UC-211945A-AA1A	24	Male contact 12/14 AWG	14.43
	YS-UC-211946A-AA1A	3	Male contact 10 AWG	14.29
12	CHCM08x25-I	3	Screw CHC M8x25	17.24
13	W-08-I	3	Washer	5.10
14	YG-UC-211287A-JG05	1	Cover	376.80

Customer drawing: C-E1894-211943

#### **BOM of COMMUNICATION INTERCITY**

Item	Part number	Quantity	Designation	Weight (g)
	YG-UC-211283A-JG07	1	Receptacle body	1070.33
2	1504-0018A4	1	Axis of cover	3.95
3	1504-0005A4	1	Spring	3.56
4	1504-0019A4	1	Cover gasket	14.29
5	YA-UC-211297A-VN00	1	Receptacle gasket	52.30
6	Y0000000-7105-06-I	2	Self-locking ring	0.17
7	YK-UC-211276A-QK00	1	Mixed insulator	124.81
8	YK-UC-211315A-VP00	27	Sleeve	1.86
9	YK-UC-211275A-QK00	1	Male insulator	162.65
10	YS-UC-211945A-AA1A	24	Male contact 12/14 AWG	14.43
11	YS-UC-211946A-AA1A	3	Male contact 10 AWG	14.29
12	CHCM08x25-I	3	Screw CHC M8x25	17.24
13	W-08-I	3	Washer	5.10
14	YG-UC-211287A-JG07	1	Cover	376.80

Customer drawing: C-E1894-212085




#### **BOM of COMMUNICATION COMMUTER**

Item	Part number	Quantity	Designation	Weight (g)
1	YG-UC-211281A-JG04	1	Receptacle body	1070.33
2	1504-0018A4	1	Axis of cover	3.95
3	1504-0005A4	1	Spring	3.56
4	1504-0019A4	1	Cover gasket	14.29
5	YA-UC-211297A-VN00	1	Receptacle gasket	52.30
6	Y0000000-7105-06-I	2	Self-locking ring	0.17
7	YK-UC-211276A-QK00	1	Mixed insulator	124.81
8	YK-UC-211315A-VP00	27	Sleeve	1.86
9	YK-UC-211275A-QK00	1	Male insulator	162.65
10	YS-UC-211945A-AA1A	24	Male contact 12/14 AWG	14.43
	YS-UC-211946A-AA1A	3	Male contact 10 AWG	14.29
12	CHCM08x25-I	3	Screw CHC M8x25	17.24
13	W-08-I	3	Washer	5.10
14	YG-UC-211287A-JG04	1	Cover	376.80

Instruction sheet

Customer drawing: C-E1894-212086

#### 2.6 **Exploded view**





- 1- Receptacle
- 2- Receptacle gasket
- 3- Axis
- 4- Self-locking ring
- 5- Spring
- 6- Cover
- 7- Mixed insert

- 8- Sleeve
- 9- Male contact
- 10- Barrel
- 11- Male insert
- 12- Washer
- 13- ScrewCHC M8x25
- 14- Cover gasket



#### 2.7 Overall dimensions





#### 2.8 Materials

Designation	Materials
Receptacle	Aluminium
Receptacle gasket	Neoprene
Axis	A2 Stainless steel
Self-locking ring	A2 Stainless steel
Spring	A2 Stainless steel
Cover	Aluminium
Mixed insert	Polycarbonate
Sleeve	Neoprene
Male contact	Silver plated brass
Diabolo	Beryllium copper with silver plated
Male insert	Polycarbonate
Washer A2 Stainless steel	
Screw CHC M8x25 A2 Stainless steel	
Cover gasket Neoprene	

#### 3. TECHNICAL CHARACTERISTICS

# 3.1 Applicable standards and documents

- Reference standard : AAR Standard S-512
- ♦ Recommended pratice for 27-points jumper and receptacle : APTA RP-E-017-99 & APTA RP-E-019-99
- Recommended pratice for wiring of passenger equipment: APTA RP-E-002-98
- Standard for insulation integrity: APTA SS-E-001-98



#### 3.2 Electrical characteristics

♦ Minimal creepage distance (mated connector) : 18.2 mm

♦ Minimal air clearance (mated connector): 16.2 mm

♦ Comparative Tracking Index (CTI) of insulators : 600 Volt

♦ Service voltage : 600 Volts maxi

♦ Withstand voltage: (NF EN 50-124-1/A2): 1500 Volt maxi

Continuous service current : 30A

#### 3.3 Mechanical characteristics

◆ Crimping pulling resistance: 180 N per contact

#### 3.4 Climatic characteristics


◆ Temperature class: - 40°C to + 100°C

Salt spray resistance: 48 hours

#### 4. MOUNTING


#### 4.1 Panel cutting

Cut the panel according to the dimensions below without any sharps or edges



#### 4.2 Fixing receptacle

Attach the receptacle to the panel using 4 screws M8 torqued + washer (not include in the kit)



Tightening torque: 20 N/m

Instruction sheet




CLASS 1-Public

# 4.3 Preparation of the cable

Strip the external sheath of about 120 mm

Strip on 13mm the 27 cables




## 4.4 Cable implantation into the receptacle


Pass the cable through the receptacle



Insert sleeves into the mixed insert



Pass the cables through the sleeves




# Instruction sheet

#### **Contacts crimping**

Crimp the contacts by using the tools corresponding to each cable section cross. See section 5



#### Mounting inserts on the receptacle 4.6



#### **CONTACT CRIMPING** 5.

#### **Manual crimping tools DMC** 5.1



Cable cross sections	Manual crimping tools	
	Hand crimper	Die
Gauge 14	HX4	Y543
Gauge 12	HX4	Y543
Gauge 10	HX4	Y543

#### **MAINTENANCE OPERATIONS**

In case of need to dismantle the receptacles, process in the reverse way of the operations described on the chapter 4

#### 6.1 **Spare parts**

	Caliber	Cable cross section	Number of contacts	Commercial reference	Drawings
I	0	AWG12 and 14	24	27P-KITCON-24P12-3P10	C-S1894-212124
	0	AWG10	3	2/F-KITGON-24F12-3F10	U-31094-212124

15 June 2016