

GASKET SEALED (VENTED)

SPST
28 VDC
300 AMP
0.5 $\pm$ 0.15 VDC
9 - 25 AMP

CONTINUOUS
24 TO 30 VDC
18 VDC
0.5 V. TO 7.0 V.

-55°C TO +71°C
50,000 CYCLES MIN.
100,000 CYCLES MIN.
2 LBS. 8 OZ.

SPST-NC
28 VDC
5 AMP

IND

GEN



BAT

SW

ALARM

APP

E



NOTE:
1. THIS UNIT MEETS THE MATERIAL
AND WORKMANSHIP REQUIREMENTS
OF MIL-R-6106.

FIND NO	QTY	PART OR IDENTIFYING NO	NAME, MATERIAL OR DESCRIPTION	FSCD NO	DRAWING OR SPECIFICATION	MATERIAL OR NOTE
11	1	39529-001	OVERLAY			
10	1	32492-010	CUTOUT ASSEMBLY - PRIMARY			
9	5	51810-031	WASHER - LOCK, NO. 10 SPL IT			STEEL
8	2	51807-071	WASHER - LOCK 3/8 X .688 X .094 SPL IT			STEEL
7	2	51704-161	WASHER - FLAT 5/8 X .390 X .064			STEEL
6	5	51702-851	WASHER - FLAT 7/16 X 13/64 X .032			STEEL
5	4	51200-020	SCREW - 4 X 1/4 PAN HD. SHI. MTL.			
4	5	50410-086	NUT - 10-32 X 3/8 X 1/8 HEX.			BRASS
3	2	50407-166	NUT - 3/8-24 X 5/8 X 7/32 HEX.			BRASS
2	1	10967-002	PLATE - BASE COVER			
1	1	16043-001	PLATE - NAME			

HARTMAN ELECTRICAL MANUFACTURING
MANSFIELD, OHIO

CUTOFF - REVERSE CURRENT
300 AMP, 28 VDC

SIZE	CODE IDENT	DMC NO.

DR BY	RLS	99/11/17
CHK BY	PS	99/11/17
ENGR	JA	99/11/23
MFG	GC	99/11/29
RELEASE		
CONTR NO.		
GOVT APPL		

C	74063	A-700ZG
SCALE	NONE	SHEET