# **SD MEMORY CARD Connector**

# 1. INTRODUCTION

## 1.1. Purpose

Testing was performed on the Tyco SD MEMORY CARD Connector to determine its conformance to the requirements of Product Specification 108-57504 Rev. O.

# 1.2. Scope

This report covers the electrical, mechanical, and environmental performance of the SD MEMORY CARD Connector.

#### 1.3. Conclusion

The SD MEMORY CARD Connector meets the electrical, mechanical, and environmental performance requirements of Product Specification 108-57504 Revision O.

## 1.4. Product Description

The SD MEMORY CARD Connector is designed for printed circuit board applications. The contacts are copper alloy, gold plated on the contact interface and tin plating on the soldertail, all over nickel under-plated. The housing material is glass filled insulating polymer, UL94V-0.

## 1.5. Test samples

The test samples were randomly selected from normal current production lots, and the following part numbers were used for test:

Test Group	Quantity	Description		
A, B, C, D, E, F,	5EA.	SD MEMORY CARD Connector		

Samuel Hou 03-Se	p-2004 Wei-Jer Ke	03-Sep-2004
DR	DATE APVD	DATE

FZ00-0206-04





1.6. Qualification Test Sequence

Test Group							
Test or Examination	Α	В	С	D	E	F	
	Test Sequence (a)						
Examination of Product	1, 7	1, 6	1, 5	1, 5	1	1, 3	
Contact Resistance	2, 6	2, 5	2, 4	2, 4			
Dielectric Withstanding	4						
Voltage							
Insulation Resistance	3						
Mating Force		3					
Unmating Force		4					
Durability	5						
Contact Retention Force					3		
Solderability						2	
Resistance to Reflow					2		
Soldering Heat							
Temperature Life				3			
Salt Spray			3				

Figure 1.

NOTE: (a) Numbers indicate sequence in which tests are performed.

(b) Discontinuities shall not take place in this test group, during tests.

Rev O 2 of 3



# 2. TEST RESULT

GP	TEST	SPEC.	DATA			
		GFLO.	Mean	σ	Max.	Min.
	Contact Resistance	80mΩ Max.	49.06	3.097	52.5	43.3
	Insulation Resistance	1,000MΩ Min.500VDC	999x10⁵		999x10 <sup>5</sup>	999x10 <sup>5</sup>
A	Dielectric Withstanding Voltage	500V AC for 1 minute	ок		ок	ок
	Durability	10,000 cycles	OK		ок	OK
	Contact Resistance	100mΩ Max	78.12	5.322	86.3	72.4
	Appearance	No Damaged	OK		OK	OK
	Contact Resistance	80m Ω Max.	47.98	4.047	53.6	42.5
	Mating Force	4.2 kgf Max.	1.115	0.075	1.24	1.02
В	Unmating Force	0.21kgf Min	0.693	0.052	0.78	0.62
	Contact Resistance	80m Ω <b>Ma</b> x	54.01	1.108	55.6	52.1
	Appearance	No Damaged	OK		OK	OK
	Contact Resistance	80mΩ Max.	53.44	1.626	56.2	51.2
С	Salt Spray	Exposing in a heat chamber at a temperature of 35°C for 48 hour	ок		ок	ок
	Contact Resistance	100mΩ Max	60.95	1.272	63.2	59.2
	Appearance	No Damaged	OK		OK	OK
	Contact Resistance	80m Ω Max.	54.3	0.612	55.2	53.3
D	Temperature Life	Temperature 85°C for 96 hours	OK		OK	OK
	Contact Resistance	100mΩ Max	56.56	0.744	57.6	55.3
	Appearance	No Damaged	OK		ок	ok
Е	Resistance to Reflow Soldering Heat	No physical damage shall occur.	ок		ок	ок
	Contact Retention Force	0.25 kgf Min.	0.318	0.007	0.33	0.31
F	Solder ability	240℃ for 5 sec. Max.	OK		ОК	OK
	Appearance	No Damaged	OK		ОК	OK

Figure 2

Rev O 3 of 3