

## 1. INTRODUCTION

#### 1.1 Purpose

Testing was performed on High Density+ Card Edge Power Connector (part number 2343428-1) to determine its conformance to requirements of product specification 108-128089, Revision A.

#### 1.2 Scope

This report covers the electrical, mechanical, and environmental performance of the High Density+ Card Edge Power Connector (part number 2343428-1). Testing was performed at TE Shanghai Testing Laboratory between 18-Apr-2019 and 31-May-2018.

#### 1.3 Conclusion

High Density+ Card Edge Power Connector (part number 2343428-1) conformed to the electrical, mechanical, and environmental performance requirements of product specification 108-128088, Revision B.

#### 1.4 Test Specimens

Test specimens were representative of normal production lots. Specimens identified with the following part numbers were used for test:

Test Group	Quantity	Part Number	Description
	9 pcs (3 ea.)	2343428-1	High Density+ Card Edge Power Connector
#2,4,5	9 pcs (3 ea.)	2344001-2	Mating side test PCB
	9 pcs (3 ea.)	2344001-1	Mounting side test PCB,
	6 pcs 2343428-1		High Density+ Card Edge Power Connector
#1			Mating side test PCB
6 pcs 2344001-1 Mount		2344001-1	Mounting side test PCB,
#3,7	6 pcs (3 ea.)	2343428-1	High Density+ Card Edge Power Connector

#### 1.5 Environmental Conditions

Unless otherwise stated, the following environmental conditions prevailed during testing: Temperature:  $15^{\circ}$ C to  $35^{\circ}$ C Relative Humidity 25% to 75%

#### 1.6 Qualification Test Sequence

	Test group						
Test Description	1	2	3	4	5	6	7
		Test sequence (a)					
Initial examination of product	1	1	1	1	1	1	1
Lowe level contact resistance	3,7	2,6		2,5	2,5		
Contact resistance (power contact)		3,7		3,6			
Insulation resistance			2,6				

<sup>© 2022</sup> TE Connectivity Ltd. family of companies. PRODUCT INFORMATION 1-800-522-6752 All Rights Reserved. \*Trademark

Dielectric Withstanding Voltage			3,7				
Temperature rise vs current		4					
Vibration, sinusoidal	5						
Mechanical shock	6						
Mating force	2						
Un-mating force	8						
Durability	4						
Contact retention force						2	
Solderability							2
Thermal shock			4		3		
Humidity/temperature cycling.			5		4		
Temperature life				4(b)			
Mixed flowing gas		5(b)					
Final examination	9	8	8	6	6	3	3

#### Note

- (a) Numbers indicate sequence in which tests are performed.
- (b) Precondition specimens with 10 durability cycles

# 2. SUMMARY OF TESTING

2.1 Initial examination– All Test Groups

All specimens submitted for testing were representative of normal production lots. A Certificate of Conformance was issued by Product Assurance. Where specified, specimens were visually examined and no evidence of physical damage detrimental to product performance was observed.

2.2 Low Level Contact Resistance- Test Group 1, 2, 4, 5.

Test Group		Test	LLCR (mΩ)		Shaa	امديا
		Condition	AVG	MAX	Spec	Jud.
	Dowor	Initial	0.24	0.30		OK
#1	Power	Final	0.26	0.34		OK
#1	Signal	Initial	6.72	8.49		OK
	Signal	Final	6.99	9.80	Signal:	OK
	Davian	Initial	0.24	0.29	20 mΩ	OK
#2	Power	Final	0.36	0.53	max.	OK
#2	Signal	Initial	6.24	7.84	Power:	OK
		Final	7.00	12.63	0.7 mΩ	OK
	Power	Initial	0.23	0.29	max.	OK
#4	rowei	Final	0.33	0.47		OK
	Signal	Initial	6.53	8.32		OK
		Final	6.79	8.68		OK



Dr	Power	Initial	0.24	0.30	OK
#5		Final	0.31	0.41	OK
#5	Cianal	Initial	6.94	8.60	OK
	Signal	Final	7.19	8.85	OK

2.3 Contact resistance (power contact only) - Test Group 2, 4,

Test Group		Test	CR(mΩ)	Snoo	lud	
Test Git	Test Group		AVG	MAX	Spec	Jud.
#2	Power	Initial	0.24	0.29		OK
#2	Fower	Final	0.33	0.44	0.6 mΩ	OK
#4	#4 Dower	Initial	0.25	0.29	max.	OK
#4	FOWEI	Power Final	0.34	0.46		OK

## 2.4 Insulation resistance– Test Group 3

All insulation resistance measurements between power conductors were greater than 5000 megohms, and all insulation resistance measurements between signal conductors were greater than 500 megohms.

2.5 Dielectric Withstanding Voltage – Test Group 3

No dielectric breakdown or flashover occurred.

2.6 Temperature rise vs current – Test Group 2

All specimens were soldered on TE mounting test PCB 2344001-1, and mated with TE mating side PCB 2344002-1. At the max current load shown below, the temp rise is within the requirement of  $\Delta$  t max = 30°C,

Toot Croup	Test Group PCB		Current	T-rise(°C)		Spec	Jud.
Test Group	FCB	Test Condition	Current	AVG	MAX	Spec	Juu.
#2	Mating PCB : 6 * 2 Ounce Mounting PCB : 6 * 2 Ounce	Ston U	41.7A / pin	22.83	26.35	30.0°C Max	OK
#2	Mating PCB : 6 * 5 Ounce Mounting PCB : 6 * 6 Ounce	Ston Q	51.5 A / pin	28.7	29.7	30.0°C Max	OK

2.7 Vibration, sinusoidal – Test Group 1

No discontinuity greater than 1 microsecond were detected; No physical damage.

2.8 Mechanical shock – Test Group 1

No discontinuity greater than 1 microsecond were detected; No physical damage.

2.9 Mating force and Unmating force – Test Group 1

Mating force measurements of all specimens which were soldered on mounting PCB were less than 102.3N, with average 94.8N. and Un-mating force measurements of all specimens which were soldered on mounting PCB were more than 12N, with average 33.04N. \*Thickness of mating PCB is ~1.58mm.

2.10 Durability – Test Group 1

No physical damage occurred to the specimens as a result of mating and unmating the specimens 200 times.

2.11 Contact retention force – Test Group 6

All retention force measurements for Power contact were more than 10N per contact. All retention force measurements for Signal contact were more than 5N per contact.

2.12 Solderability – Test Group 7

All of test specimens get more than 95% coverage.

2.13 Thermal shock – Test Group 3, 6

No evidence of physical damage was visible as a result of exposure to thermal shock.

2.14 Humidity-temperature cycling – Test Group 3, 5

No evidence of physical damage was visible as a result of exposure to Humidity-temperature cycling

2.15 Temperature life– Test Group 4

No evidence of physical damage was visible as a result of exposure to 250hours at 105  $^\circ\!\!\mathbb{C}$  temperature life.

2.16 Mixed flowing gas- Test Group 2

No evidence of physical damage was visible as a result of the Class IIA MFG exposure for 14days.

2.17 Final examination of product – All Test Groups

Specimens were visually examined and no evidence of physical damage detrimental to product performance was observed.

## 3. TEST REQUIREMENTS AND PROCEDURES SUMMARY

Test Description	Requirement	Procedure
Initial examination of product	Meets requirements of product	EIA-364-18
	drawing.	Visual and dimensional (C of C)
		inspection per product drawing.

ELECTRICAL		
Low Level Contact Resistance	Signal contact: 20 m $\Omega$ max. Power contact: 0.7 m $\Omega$ max.	EIA-364-23 Subject specimens to 100 mA maximum and 20 mV maximum open circuit voltage
Contact resistance (power contact only)	At 41.7A for power, 0.6 m $\Omega$ maximum	EIA-364-06
Insulation Resistance	5000 MΩ minimum between all power conductors,	EIA-364-21



	500 M $\Omega$ minimum between all signal conductors;	500+/-10% VDC, 2 minutes hold. Test between adjacent contacts
	One-minute hold with no breakdown or flashover	EIA-364-20, Condition I. 1200 V for power contact and 1000V for signal contact at sea level. Test between adjacent contacts.
Temperature rise vs current	Temperature rise: 30°C max. over ambient temperature	EIA-364-70, Method 1. Stabilize at a single current level until 3 readings at 5-minute intervals are within 1°C See table 2

MECHANICAL		
Vibration, sinusoidal	No discontinuities of 1 microsecond or longer duration. See Note	EIA-364-28, Test condition I, Subject mated specimens to 10-55- 10 Hz Traversed in 1 minutes at 1.52mm amplitude 2 hours each of 3 mutually perpendicular planes;
Mechanical shock	No discontinuities of 1 microsecond or longer duration. See Note	EIA-364-27, Test Condition A. Subject mated specimens to 50 G's half-sine shock pulses of 11 milliseconds duration. Three shocks in each direction applied along 3 mutually perpendicular planes, 18 total shocks
Mating force	120N max. *Mating with 1.57mm thick PCB.	EIA-364-13, Method A. Measure force necessary to mate specimens at a maximum rate of 12.7 mm per minute
Un-mating force	12N min.	EIA-364-13, Method A. Measure force necessary to mate specimens at a maximum rate of 12.7 mm per minute
Durability	200 cycles See Note	EIA-364-9, Mate and un-mate specimens for 200 cycles at a maximum rate of 500 cycles per hour
Contact retention force	10N min. per power pin 5N min. per signal pin	EIA-364-29 Measure force necessary to remove individual contact from the housing at a maximum rate of 12.7mm per minute
Solderability	Solderable area shall have a minimum of 95% solder coverage. See Note.	TE Spec. 109-11-11, Test Method A.

ENVIRONMENTAL				
Thermal shock	See Note	EIA-364-32, Method A, Test		
		condition I, Subject specimens to		



		5cycles between -55 and 105°C with 30 minute dwells at temperature extremes and 1 minute maximum transition between temperatures
Temperature life	See Note	EIA-364-17, Method A, Test condition 4, Test condition C. Subject mated specimens to 105°C for 250 hours
Humidity/temperature cycling.	See Note	EIA-364-31, Method III. Subject mated specimens to 10 cycles (10 days) between 25 and 65°C at 90 to 95% RH
Mixed flowing gas	See Note	EIA-364-65, Class IIA (4 gas). Subject mated specimens to environmental Class IIA for 14 days(7 days unmated, LLCR, followed by 7 days mated)

# NOTE

Shall meet visual requirements, show no physical damage, and meet requirements of additional tests as specified in the Product Qualification and Requalification Test Sequence