



SP3-90-6

Gas Discharge Surge Protectors

GAS DISCHARGE SURGE PROTECTORS

DC to 3000 MHz Operation

The surge protectors offered by Laird Technologies are an integral part of any antenna installation in protecting sensitive equipment from surges caused by lightning. The ultra-fast gas discharge tube design gives quick response to power surges and dumps the excess power safely to the ground. A ground lug terminal is supplied to provide superior grounding. The units have the ability to withstand multiple lightning strikes. The SP3-90-6 passes DC voltage, so it is also suitable for systems that pass DC power through the coax, such as remote amplifiers.

FEATURES

- Ultra fast gas discharge
- Multiple strike 6 KA discharge
- 0.4 db max insertion loss

APPLICATIONS

- Lightning protection for antenna systems
- 900 MHz to 2.4 GHz antenna systems
- WiMAX

| PARAMETER | MIN | TYP | MAX | UNITS |
|--|------|-----------------------------------|------|---------|
| Frequency Range | DC | | 3000 | MHz |
| Insertion Loss | .1 | .2 | .4 | dB |
| VSWR | | 1.2 : 1 | | |
| DC Breakdown Voltage | 72 | 90 | 108 | V |
| Impulse Discharge (5 times, 8/20 µsec) | 6000 | | | A |
| Impedance | | 50 | | Ohm |
| Insulation Resistance (DC 100 V) | 50 | | | Meg Ohm |
| Input Power (@2.4 GHz) | | | 42 | W |
| Operating Temperature | -40 | | +85 | C |
| Weight | | 5.8 (164) | | oz (g) |
| Dimensions (includes connectors) | | 2.75 x 1.25 x 1.75 (70 x 32 x 44) | | in (mm) |

SYSTEM ORDERING

SP3-90-6-BFF DC to 3000 MHz, 6 KA, bulkhead N female to N female, 90 V surge protector

SP3-90-6-BFM DC to 3000 MHz, 6 KA, bulkhead N female to N male, 90 V surge protector

NOTES:

* All shipments F.O.B. Schaumburg, IL 60173

TE TECHNICAL SUPPORT CENTER

| | |
|-------------------|-----------------------|
| USA: | +1 (800) 522-6752 |
| Canada: | +1 (905) 475-6222 |
| Mexico: | +52 (0) 55-1106-0800 |
| Latin/S. America: | +54 (0) 11-4733-2200 |
| Germany: | +49 (0) 6251-133-1999 |
| UK: | +44 (0) 800-267666 |
| France: | +33 (0) 1-3420-8686 |
| Netherlands: | +31 (0) 73-6246-999 |
| China: | +86 (0) 400-820-6015 |

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original