



YS4303

Directional Yagi Antenna 430-450 MHz

Directional gamma matched Yagi antennas are focused on economy and high performance. This UHF Yagi series has a 9.1 dBi antenna gain and operates on the 430-450 MHz frequency range. It is manufactured using high strength 6061-T6 aluminum to withstand heavy ice, high wind, and other harsh conditions.

FEATURES AND BENEFITS

- Every Yagi is tuned on a network analyzer for best power match and lowest VSWR.
- All Yagi antennas ship complete with a high-quality cast aluminum mounting kit that includes stainless steel hardware and allows vertical or horizontal orientation during installation (VHF models require light assembly).

APPLICATIONS

- Point-to-point directional and multiple point to omnidirectional outdoor antenna applications used by private organizations and government agencies around the globe.
- Typical applications include transportation such as railroad switching, remote locations reporting examples that include oil fields and weather conditions and meter data transmissions for utilities.

ELECTRICAL SPECIFICATION

Model Name	YS4303
Operating Frequency (MHz)	430-450
VSWR	< 2:1
Return Loss - Max (dB)	-10
Gain (dBi)	9.1
Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	300
Polarization	Vertical or horizontal
Pattern	Directional
Vertical Plane 3 dB Beamwidth	114°
Horizontal Plane 3 dB Beamwidth	115°
Tuning	Fixed tune
Transmitting/Receiving	Both
Front-to-Back Ratio (dB)	17


MECHANICAL SPECIFICATION	
Dimensions – L x H – cm (inches)	51.4 x 34.6 (20.3 x 13.6)
Boom Diameter – cm (inches)	2.22 (0.875)
Material	Aluminum
Color	Silver
Lightning Protection	Lightning arrestor – LABH350NN (sold separately)
Mounting	Yagi mounting kit

ENVIRONMENTAL SPECIFICATION	
Operating Environment (Indoor or Outdoor)	Outdoor
Operating Temperature – °C (°F)	-30 to +70°C (-22 to +158°F)
Storage Temperature – °C (°F)	-30 to +70°C (-22 to +158°F)
Rated Wind Velocity – km/hr (mph)	241 (150)
Equivalent Flat Area – sq. m (sq. ft.)	0.04470 (0.48115)

CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR
YS4303	N/A	N-Female

RADITION PATTERNS



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original