



## NMOHPC

### High Performance NMO Mount 0-6000 MHz

Laird's high frequency, high performance permanent 3/4" NMO mount provides extended frequency range up to 6 GHz. It allows you to deploy antennas in frequency ranges above traditional LMR195 equivalent.

### FEATURES AND BENEFITS

- High-performance up to 6 GHz
- 78 Rockwell Hardness brass material resists corrosion
- Gold plated contact provides superior conductivity
- Available coax options: LMR195 equivalent, 17' RG58A/U or 17' RG58U
- Available in other coax lengths and connector options

### SPECIFICATIONS

Operating Frequency (MHz)	0-6000
Mount Type	3/4", NMO
Installation Hole Size	3/4"
Ingress Protection	IP67 sealed out mount surface (fully IP67 rated when terminated to antenna with IP67 provisions)
Operating Temperature - °C (°F)	-40°C to +85°C (-40°F to +185°F)
Included Hardware	O-Ring and NMO ring adapter included

## CONFIGURATION

PART NUMBER	CABLE LENGTH	CONNECTOR	CABLE TYPE
NMOHPCFMUHM518	17 ft.	Mini UHF Male	RG-58A/U
NMOHPCFSMAM518	17 ft.	SMA Male	RG-58A/U
NMOHPCFTNCM518	17 ft.	TNC Male	RG-58A/U
NMOHPCFRPSMM518	17 ft.	RP-SMA Male	RG-58A/U
NMOHPCFFMEM18	17 ft.	FME Male	RG-58A/U
NMOHPCFUHF518	17 ft.	UHF PL259 Male	RG-58A/U
NMOHPCF518	17 ft.	No Connector	RG-58A/U
NMOHPCGMUHM518	17 ft.	Mini UHF Male	RG-58A/U
NMOHPCGSMAM518	17 ft.	SMA Male	RG-58A/U
NMOHPCGTNCM518	17 ft.	TNC Male	RG-58A/U
NMOHPCGRPSMM518	17 ft.	RP-SMA Male	RG-58A/U
NMOHPCGFMEM518	17 ft.	FME Male	RG-58A/U
NMOHPCGUHF518	17 ft.	UHF PL259 Male	RG-58A/U
NMOHPCG518	17 ft.	No Connector	RG-58A/U
NMOHPCNMUHM518	17 ft.	Mini UHF Male	Low Loss 195
NMOHPCNSMAM518	17 ft.	SMA Male	Low Loss 195
NMOHPCNTNCM518	17 ft.	TNC Male	Low Loss 195
NMOHPCNRPSMM518	17 ft.	RP-SMA Male	Low Loss 195
NMOHPCNFMEM518	17 ft.	FME Male	Low Loss 195
NMOHPCNUHF518	17 ft.	UHF PL259 Male	Low Loss 195
NMOHPCN518	17 ft.	No Connector	Low Loss 195
NMOHPCAA518	17 ft.	No Connector	Laird Teflex
NMOHPCW518	17 ft.	No Connector	Laird High Performance Teflex
NMOHPC	No Cable	No Connector	No Cable

### te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

©2021 TE Connectivity. All Rights Reserved.

11/21 Original

### TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

