

HK6/36 & HK12/2 inserts

1. INTRODUCTION

1.1 Purpose

This document provides the qualification summery of TE Connectivity HK6/36 & HK12/2 inserts of HDC connector.

1.2 Scope

This specification covers the electrical, mechanical, and environmental performance of HK6/36-042 & HK12/2-014 insert. Testing was performed at the Shanghai Electrical Components Test Laboratory.

1.3 Conclusion

Based on the test results, all meet the requirements according to TE Connectivity Design Objectives 108-137053.

1.4 Product Description

Name	Remarks
HDC-HK12/2-014M	
HDC-HK12/2-014F	
HDC-HK6/36-042M	
HDC-HK6/36-042F	

1.5 Qualification Test Sequence

			Те	st Gro	up		
Test and Examination	Α	В	С	D	Е	F	G
		1	Test	Seque	nce 1)		
Visual and dimensional examination	1,6	1,5	1,3	1,11	1,3	1,8	1,6
Durability of marking	2						
Polarisation and coding (If application)	3						
Pull out force of terminations for Crimped connections	7 ª						
Contact retention force in insert	4						
Mechanical strength impact	5						
Mechanical Operation (Durability)		3					
Vibration, Random							3
Shock							4
Contact Resistance		2,4		2,8		2,5	2,5
Temperature Rise Test			2				

©2012 TE Connectivity (Shanghai) Co. Ltd Shanghai P.R.C. All International Rights Reserved Information is TE Connectivity Confidential & Proprietary. Do Not Reproduce or Distribute

Page 1 of 7



Dielectric Voltage Withstand Test		3,9		6	
Insulation Resistance		4,10		7	
Cold		5			
Dry Heat		6			
Damp Heat, cyclic				4	
Rapid Change of temperature (Temperature Cycle)				3	
Corrosion		7			
Protection against electric shock			2		

* Notes:

- Numbers indicate the sequence in which the tests are performed.
 ^a test items are for themselves separate tests and are performed on new specimens.

2. TEST PROCEDURE

Gen	General						
No.	Description	Test procedure according	Requirements				
2.1	Visual and dimensional examination	Meets requirements of product drawing	Visual and dimensional examination IEC 60512-1-1/-2, Test 1a and 1b 6.2 of EN 61984				

Мес	Mechanical						
2.2 Durability of marking marking made by impressio		(If marking made by impression, molding, pressing or engraving or the like are not	Test piston: Size 1 Wet test with liquid: water Duration: 10 cycles Force:5N IEC 60068-2-70 Test Xb, 7.3.2 of EN61984				
2.3	3 Polarisation and coding against incorrect mating according to 6.3 & 6.9.1 of EN 61984 No damage likely to impair function		For unenclosed connector (internal connections) 20N For enclosed connector (external connections) 1.5 x Mating force, but not higher than 80N Test 13e of IEC 60512-13-5				
	Pull out force of terminations	See 6.6 of EN 61984	See 6.6 of EN 61984				
2.4	^a for Crimped connections	The conductor shall not slip out of crimp barrel and pull out force as specified in Table 1 of EN 60352-2	Visual tests on the crimp barrel and tensile strength test of the crimp connection as specified in IEC 60352-2.				
2.5	Contact retention force in insert	No axial displacement likely to impair normal operation, min 50N force for each pin or socket, 6.18.2 of EN 61984	Test load applied in axial direction, test speed:20mm/min, permissible shift contacts of 1.0mm, Test 15a of IEC 60512-15-1				



2.6	Mechanical strength impact	Connector and internal insulation shall no damage to impair normal use. A reduction of clearance and creepage distance is not allowed. 6.18.1 & 6.18.3 of EN 61984	Dropping height: - 750mm for specimens of mass≤250g - 500mm for specimens of mass>250g Dropping cycles:8 positions in 45%tep, one cycles per position IEC 60512-7-2 Test 7b
2.7	Mechanical Operation (Durability)	500 operation cycles without load No damage likely to impair normal use 6.14.1 of EN 61984	Shall be engaged and disengaged by means of A) a device simulating normal operating conditions at the speed of approximately 50mm/min B) manual mating/un-mating 300 Max. cycle per hour IEC 60512-9-1 Test 9a, 7.3.9 of EN 61984
2.8	Vibration, Random	No damage likely to impair function No discontinuities greater than t>1µs	Frequency:5~150Hz Per EN 61373, Category 1, Class B (IEC60068-2-6 Test Fc)
2.9	Shock	No damage likely to impair function No discontinuities greater than t>1µs	Acceleration:50m/s ² Duration:30ms Total 18 shocks(three positive and three negative in each of the three orthogonal axes), Per EN 61373

Elec	Electrical					
		Initial For Signal: Max.5 mΩ For Power: Max.3 mΩ		Test current: 1A		
2.10	Contact Resistance	Final	The change of contact resistance shall be no more than 50 % of the reference value or \leq 5 m Ω . The higher value is permissible.	Measure pointsb at the end of the termination Max three contacts per specimen plus protective earthing, if any IEC 60512-2-2 Test 2b		
2.11	Temperature Rise Test	temperat	of the ambient temperature and the ure rise ($\triangle T$) of a connector shall ed the upper limiting temperature N 61984			
2.12	Dielectric Voltage Withstand Test	6.13 of E HK12/2: For Powe For Signa HK6/36: For Powe	er : 8 KV al : 4 KV	Impulse test voltage according to Table 8, applied three impulses of each polarity and interval of at least 1s between impulses. 7.3.12 of EN 61984		
2.13	Insulation Resistance	Not less	than 400MΩ	Test voltage 1000V DC Time:60s IEC 60512-3-1 Test 3a Method B		



Env	ironmental		
2.14	Cold	No damage likely to impair function	Subject mated specimen to -40°C Duration time:16h, Test Ab Per IEC 60512-11-10 Test 11j (IEC 60068-2-1)
2.15	Dry Heat	No damage likely to impair function	Subject mated specimen to +125°C Duration time:168h Test Bb Per IEC 60512-11-9 Test 11i (IEC 60068-2-2)
2.16	Damp Heat, cyclic	No damage likely to impair function	Subject mated specimen to Min ambient temperature: 25°C Max ambient temperature: 45°C Number of cycles:21 Duration time:12h+12h Variant 1 IEC 60512-11-12 Test 11m
2.17	Rapid Change of temperature (Temperature Cycle)	No damage likely to impair function	Subject mated specimen to Ta=-40 \pm 2°C to Tb=+125 \pm 2°C, duration t1: 1h each extreme, 100 cycles IEC 60512-11-4 Test 11d (IEC 60068-2-14 Test Na)
0.40	Corrosion	No damage likely to impair function	Test 1: Flowing mixed gas corrosion according to test 11g, method 1 or method 4 (Table 1) Duration time: 4day (96h) IEC 60512-11-7 Test 11g 7.3.14 of EN 61984
2.18	(Alternative)	Per 6.21 of EN 61984	Test 2: Sulphur dioxide test with general condensation of moisture according to EN ISO 6988 Duration time:24h (1 test cycle) 7.3.14 of EN 61984
2.19	Protection against electric shock	no live parts shall be accessible by test finger, 6.4.2.2 or 6.4.2.3 of EN 61984	Unenclosed connector. Test finger or 50mm sphere pressed with 20N against the surface as specified by the manufacture Mated specimen and socket connector (if application) 7.3.6.1 of EN 61984
^b mea		elves separate tests and are performed on new conductors as close as possible to the termina ulated.	-



3. SUMMARY OF TEST RESULTS:

Examination of product – all test group

Test Group	Test Item		Test Result	Requirement	Judgment
	Visual and dimensior examination	nal	No physical damage	Meets requirements of product drawing	passed
	Durability of marking		Marking shall be readable	Marking shall be readable	passed
	Polarisation and codi	ng	No physical damage	require provision against incorrect mating	passed
Group A	Contact retention force in insert		No axial displacement likely to impair normal operation	Axial displacement <1.0mm when test speed: 20mm/min, min 50N force for each pin or socket	passed
	Mechanical strength	impact	No physical damage	No damage likely to impair function	passed
	Visual and dimensior examination	al	No physical damage	Meets requirements of product drawing	passed
	Pull out force of terminations	For crimped connections	0.14mm ² contact: 28.46N 2.5 mm ² contact: 300.28N	0.14mm ² : 18N Min 2.5mm ² : 230N Min	passed
	Visual and dimensior examination	al	No physical damage	Meets requirements of product drawing	passed
	Contact Resistance		HK12/2: For Signal: 2.49 mΩ Max. For Power: 0.85 mΩ Max. HK6/36: For Signal: 2.80 mΩ Max. For Power: 0.94 mΩ Max.	For Signal: Max.5 mΩ For Power: Max.3 mΩ	passed
Group B	Mechanical Operation (Durability)		No physical damage	After 500 operation cycles, No damage likely to impair normal use	passed
	Contact Resistance		HK12/2: For Signal: 5.18 mΩ Max. For Power: 1.69 mΩ Max. HK6/36: For Signal: 5.85 mΩ Max. For Power: 1.74 mΩ Max.	The change of contact resistance shall be no more than 50 % of the reference value or $\leq 5 \text{ m}\Omega$. The higher value is permissible	passed
	Visual and dimensior examination	al	No physical damage	Meets requirements of product drawing	passed
	Visual and dimension examination	nal	No physical damage	Meets requirements of product drawing	passed
Group C	Temperature Rise Te	st	55.56 ℃	The sum of the ambient temperature and the temperature rise≤125℃	passed
	Visual and dimension examination	nal	No physical damage	Meets requirements of product drawing	passed
Group D	Visual and dimensior examination	nal	No physical damage	Meets requirements of product drawing	passed



	1		1	
	Contact Resistance	HK12/2: For Signal: 3.15 mΩ Max. For Power: 0.96 mΩ Max. HK6/36: For Signal: 2.92 mΩ Max. For Power: 0.82 mΩ Max.	For Signal: Max.5 mΩ For Power: Max.3 mΩ	passed
	Dielectric Voltage Withstand Test	No physical damage	No damage likely to impair function	passed
	Insulation Resistance	>1.17x10 ¹² Ω	Not less than 400MΩ	passed
	Cold	No physical damage	No damage likely to impair function	passed
	Dry Heat	No physical damage	No damage likely to impair function	passed
	Corrosion	No physical damage	No damage likely to impair function	passed
	Contact Resistance	HK12/2: For Signal: $3.48 \text{ m}\Omega$ Max. For Power: $1.31 \text{ m}\Omega$ Max. HK6/36: For Signal: $4.61 \text{ m}\Omega$ Max. For Power: $1.18 \text{ m}\Omega$ Max.	The change of contact resistance shall be no more than 50 % of the reference value or $\leq 5 \text{ m}\Omega$. The higher value is permissible	passed
	Dielectric Voltage Withstand Test	No breakdown or flashover	No breakdown or flashover	passed
	Insulation Resistance	>8.53x10 ¹¹ Ω	Not less than 400MΩ	passed
	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed
	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed
Group E	Protection against electric shock	No electric shock occurred	No electric shock	passed
	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed
	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed
	Contact Resistance	HK12/2: For Signal: 2.67 m Ω Max. For Power: 0.83 m Ω Max. HK6/36: For Signal: 2.62 m Ω Max. For Power: 0.89 m Ω Max.	For Signal: Max.5 mΩ For Power: Max.3 mΩ	passed
	Rapid Change of temperature (Temperature Cycle)	No physical damage	No damage likely to impair function	passed
Group F	Damp Heat, cyclic	No physical damage	No damage likely to impair function	passed
	Contact Resistance	HK12/2: For Signal: 3.90 mΩ Max. For Power: 1.12 mΩ Max. HK6/36: For Signal: 4.16 mΩ Max. For Power: 1.71 mΩ Max.	The change of contact resistance shall be no more than 50 % of the reference value or $\leq 5 \text{ m}\Omega$. The higher value is permissible	passed
	Dielectric Voltage Withstand Test	No breakdown or flashover	No breakdown or flashover	passed
	Insulation Resistance	>5.42x10 ¹¹ Ω	Not less than 400MΩ	passed



	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed
Group G	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed
	Contact Resistance	HK12/2: For Signal: 2.86 mΩ Max. For Power: 0.94 mΩ Max. HK6/36: For Signal: 3.02 mΩ Max. For Power: 1.03 mΩ Max.	For Signal: Max.5 mΩ For Power: Max.3 mΩ	passed
	Vibration, Random	No breakdown or flashover	No damage likely to impair function No discontinuities greater than t>1µs	passed
	Shock	No breakdown or flashover	No damage likely to impair function No discontinuities greater than t>1µs	passed
	Contact Resistance	HK12/2: For Signal: 3.57 mΩ Max. For Power: 1.32 mΩ Max. HK6/36: For Signal: 3.89 mΩ Max. For Power: 1.14 mΩ Max.	The change of contact resistance shall be no more than 50 % of the reference value or $\leq 5 \text{ m}\Omega$. The higher value is permissible	passed
	Visual and dimensional examination	No physical damage	Meets requirements of product drawing	passed