




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	11MAR2024	AN	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED				COLOURED IDENTIFICATION TRIANGLE
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (NOM) (W)		
	mm.	in.	mm.	in.	mm.	in.	
RBK-ILS-125-NR500	10.80	0.425	1.70	0.067	1.50	0.059	WHITE


PRODUCT INFORMATION

- 1 FLAME RETARDANT
- 2 OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN
COLOUR: BLACK
INNER LINER: THERMOPLASTIC HOT MELT ADHESIVE
COLOUR: LIGHT AMBER
- 3 LONGITUDINAL CHANGE 0 TO -15%
- 4 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±:
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±:
FINISH -

DWN	11MAR2024
AYESHABANU N	
CHK	11MAR2024
BASAVARAJA D A	
APVD	11MAR2024
VLADIMIR NEMEC	
PRODUCT SPEC	108-120003
APPLICATION SPEC	114-120014
WEIGHT	-
CUSTOMER DRAWING	



NAME
RBK-ILS-125-NR500
DUAL WALL, HEAT-SHRINKABLE TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-RBK-ILS-125-NR500	-
SCALE		SHEET	REV
NTS		1 OF 1	A