



MODEL 45017

High Temp Glass NTC Thermistor

- Superior Long Term Stability
- Glass Hermetic Seal
- Use up to 250°C
- 6000 ohm Resistance @ 25°C
- Interchangeable $\pm 0.2^{\circ}\text{C}$, 0°C to 70°C
- Pressed Disk Ceramic Sensor
- High sensitivity
- Thermally conductive epoxy coating
- 32 AWG, 3" (7.6 cm) long Gold plated Dumet leads
- RoHS Compliant

FEATURES

- Glass Hermetic Seal
- 6000 Ohm Resistance @ 25°C
- Interchangeability
- Excellent High Temperature Performance
- Superior Long Term Stability
- High Sensitivity
- Thermally Conductive Epoxy Coating
- RoHS Compliance


APPLICATIONS

- High Moisture Applications
- Low to Mid Range Temperature Applications
- Tight Tolerance Instrumentation
- Applications Requiring Excellent Stability
- Applications Requiring Sensing Small Changes in Temperature
- Non-condensing Moisture Environments
- Allows use in Applications World-wide

PERFORMANCE SPECS

Parameter	Units	Value
Resistance @ 25°C	Ohms	6000
Tolerance 0°C to 70°C	°C	± 0.2
Beta Value 25/85	K	3978
Tolerance on Beta Value	%	0.8
Time response in air	Seconds	< 2.5
Dissipation Constant in air	mW/°C	10
Insulation Resistance (Min. of 100 Mohms for 1 sec.)	Volts	500

MECHANICAL DETAILS



RESISTANCE VS. TEMPERATURE TABLE

Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms	Temp °C	K-Ohms
-55	578.400	-13	39.170	29	5.046	71	1.0160	113	0.2819
-54	537.400	-12	37.060	30	4.836	72	0.9818	114	0.2744
-53	499.300	-11	35.060	31	4.633	73	0.9490	115	0.2670
-52	464.400	-10	33.200	32	4.441	74	0.9179	116	0.2600
-51	432.100	-9	31.470	33	4.260	75	0.8875	117	0.2531
-50	402.300	-8	29.810	34	4.084	76	0.8587	118	0.2464
-49	374.600	-7	28.240	35	3.919	77	0.8307	119	0.2398
-48	349.000	-6	26.780	36	3.762	78	0.8038	120	0.2337
-47	325.300	-5	25.400	37	3.610	79	0.7780	121	0.2275
-46	303.500	-4	24.100	38	3.466	80	0.7532	122	0.2217
-45	283.200	-3	22.880	39	3.328	81	0.7292	123	0.2161
-44	264.500	-2	21.720	40	3.197	82	0.7060	124	0.2105
-43	247.000	-1	20.620	41	3.069	83	0.6839	125	0.2052
-42	230.900	0	19.600	42	2.949	84	0.6623	126	0.1998
-41	215.900	1	18.620	43	2.835	85	0.6418	127	0.1948
-40	201.900	2	17.700	44	2.726	86	0.6218	128	0.1900
-39	189.000	3	16.840	45	2.621	87	0.6027	129	0.1852
-38	176.900	4	16.020	46	2.521	88	0.5843	130	0.1806
-37	165.700	5	15.240	47	2.425	89	0.5664	131	0.1761
-36	155.300	6	14.500	48	2.333	90	0.5491	132	0.1716
-35	145.600	7	13.810	49	2.246	91	0.5326	133	0.1676
-34	136.600	8	13.150	50	2.162	92	0.5166	134	0.1633
-33	128.200	9	12.530	51	2.081	93	0.5012	135	0.1593
-32	120.300	10	11.940	52	2.004	94	0.4862	136	0.1556
-31	113.000	11	11.380	53	1.930	95	0.4718	137	0.1519
-30	106.200	12	10.850	54	1.859	96	0.4580	138	0.1481
-29	99.830	13	10.350	55	1.792	97	0.4447	139	0.1447
-28	93.890	14	9.879	56	1.727	98	0.4316	140	0.1412
-27	88.320	15	9.429	57	1.665	99	0.4191	141	0.1377
-26	83.130	16	9.000	58	1.605	100	0.4071	142	0.1345
-25	78.280	17	8.595	59	1.548	101	0.3954	143	0.1313
-24	73.720	18	8.209	60	1.493	102	0.3842	144	0.1284
-23	69.460	19	7.844	61	1.440	103	0.3733	145	0.1252
-22	65.490	20	7.497	62	1.389	104	0.3626	146	0.1223
-21	61.760	21	7.167	63	1.341	105	0.3525	147	0.1196
-20	58.270	22	6.853	64	1.294	106	0.3426	148	0.1167
-19	54.990	23	6.554	65	1.2500	107	0.3330	149	0.1140
-18	51.900	24	6.272	66	1.2070	108	0.3240	150	0.1115
-17	49.020	25	6.000	67	1.1650	109	0.3149		
-16	46.330	26	5.744	68	1.1260	110	0.3064		
-15	43.770	27	5.499	69	1.0880	111	0.2979		
-14	41.400	28	5.267	70	1.0510	112	0.2899		

ORDERING INFORMATION

MODEL 45017

High Temp Glass NTC Thermistor

Model Number	Description	Ω @25°C	MOQ
090054	45017 THERM	6,000	100
091536	45017-BP THERM	6,000	100

* For quantities less than Minimum Order Quantity – contact distribution

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Tel: 800-440-5100
customercare.tfse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.