

# **HQ-008 Inserts**

#### 1. INTRODUCTION

#### 1.1 Purpose

This document provides the qualification summery of TE Connectivity HQ-008 inserts of HDC connector.

## 1.2 Scope

This specification covers the electrical, mechanical, and environmental performance of HQ-008 inserts. Testing was performed at the Shanghai Electrical Components Test Laboratory.

#### 1.3 Conclusion

Based on the test results, all meet the requirements according to TE Connectivity Design Objectives 108-137115.

## 1.4 Product Description

Name	Remarks
HQ-008-M	
HQ-008-F	

#### 1.5 Qualification Test Sequence

			Test	Group		
Test or Examination	А	В	С	D	Е	F
			Test Se	quence <sup>1)</sup>		
Visual and dimensional examination	1,6	1,5	1,3	1,11	1,3	1,6
Durability of marking	2					
Polarisation and coding	3					
(If application)	3					
Pull out force of terminations	7a					
Only for Crimped connections	7~					
Contact retention force in insert	4					
Mechanical strength impact	5					
Mechanical Operation (Durability)		3				
Vibration, Random						3
Shock						4
Contact Resistance		2,4		2,8		2,5
Temperature Rise Test			2			
Dielectric Voltage Withstand Test				3,9		
Insulation Resistance				4,10		
Cold				5		
Dry Heat				6		
Corrosion				7		
Protection against electric shock					2	

#### Notes:

- 1) Numbers indicate the sequence in which the tests are performed.
- 2) a test items are for themselves separate tests and are performed on new specimens.



# 2. TEST PROCEDURE

Gener	General					
No.	Test Items	Requirements	Condition according to			
2.1	Visual and dimensional examination	Meets requirements of product drawing	Visual and dimensional examination IEC 60512-1-1/-2, Test 1a and 1b 6.2 of EN 61984			

Mecha	anical		
2.2	Durability of marking	Marking shall be still readable according to 6.2 of EN61984 (If marking made by impression, molding, pressing or engraving or the like are not subjected to this test)	Test piston: No. 1 Wet test with liquid: water Duration: 10 cycles Force: 5N IEC 60068-2-70 Test Xb 7.3.2 of EN61984
2.3	Polarisation and coding	For multi-pole connector, require provision against incorrect mating according to 6.3 & 6.9.1 of EN 61984 No damage likely to impair function	For unenclosed connector (internal connections) 20N For enclosed connector (external connections) 1.5 x Mating force, but not higher than 80N Test 13e of IEC 60512-13-5
	Pull out force of terminations	See 6.6 of EN 61984	See 6.6 of EN 61984
2.4	<sup>a</sup> for Crimped connections	The conductor shall not slip out of crimp barrel and pull out force as specified in Table 1 of EN 60352-2	Visual tests on the crimp barrel and tensile strength test of the crimp connection as specified in IEC 60352-2.
2.5	Contact retention force in insert	No axial displacement likely to impair normal operation. Min 20N force for each pin or socket; 6.18.2 of EN 61984	Test load applied in axial direction, test speed:20mm/min, permissible shift contacts of 1.0mm, Test 15a of IEC 60512-15-1
2.6	Mechanical strength impact	Connector and internal insulation shall no damage to impair normal use. A reduction of clearance and creepage distance is not allowed. 6.18.1 & 6.18.3 of EN 61984	Dropping height: - 750mm for specimens of mass≤ 250g - 500mm for specimens of mass>250g Dropping cycles:8 positions in 45° step, one cycles per position IEC 60512-7-2 Test 7b



2.7	Mechanical Operation (Durability)	500 operation cycles without load No damage likely to impair normal use 6.14.1 of EN 61984	Shall be engaged and disengaged by means of A) a device simulating normal operating conditions at the speed of approximately 50mm/min B) manual mating/un-mating 300 Max. cycle per hour IEC 60512-9-1 Test 9a 7.3.9 of EN 61984
2.8	Vibration, Random	No damage likely to impair function No discontinuities greater than t>1µs	Frequency:5~150Hz Per EN 61373, Category 1, Class B (IEC60068-2-6 Test Fc)
2.9	Shock	No damage likely to impair function No discontinuities greater than t>1µs	Acceleration:50m/s² Duration:30ms Total 18 shocks(three positive and three negative in each of the three orthogonal axes) Per EN 61373

Electr	Electrical						
		Initial	Max.5mΩ				
2.10	Contact Resistance	Final	The change of contact resistance shall be no more than 50 % of the reference value or $\leq$ 5 m $\Omega$ . The higher value is permissible	Test current: 1A Measure points <sup>b</sup> at the end of the termination Max three contacts per specimen plus protective earthing, if any IEC 60512-2-2 Test 2b			
2.11	Temperature Rise Test	and the connec limiting	m of the ambient temperature e temperature rise ( $\triangle$ T) of a stor shall not exceed the upper temperature EN 61984	Length of test cable see table 7 of 7.3.8 of EN 61984 Carry its rated current Upper limiting temperature:125℃ (Table 5b) IEC 60512-5-1 Test 5a			
2.12	Dielectric Voltage Withstand Test	voltage	hover or breakdown of EN 61984	Impulse test voltage according to Table 8, applied three impulses of each polarity and interval of at least 1s between impulses. 7.3.12 of EN 61984			
2.13	Insulation Resistance	Not les	s than 400MΩ	Test voltage 1000V DC Time:60s IEC 60512-3-1 Test 3a Method B			

Environmental					
2.14	Cold	No damage likely to impair function	Subject mated specimen to -40°C Duration time:16h, Test Ab Per IEC 60512-11-10 Test 11j (IEC 60068-2-1)		



2.15	Dry Heat	No damage likely to impair function	Subject mated specimen to +125°C Duration time:168h Test Bb Per IEC 60512-11-9 Test 11i (IEC 60068-2-2)
2.16	Corrosion (Alternative)	No damage likely to impair function Per 6.21 of EN 61984	Test 1: Flowing mixed gas corrosion according to test 11g, method 1 or method 4 (Table 1) Duration time: 4day (96h) IEC 60512-11-7 Test 11g 7.3.14 of EN 61984
		1 01 0.21 01 210 01304	Test 2: Sulphur dioxide test with general condensation of moisture according to EN ISO 6988 Duration time:24h (1 test cycle) 7.3.14 of EN 61984
2.17	Protection against electric shock	no live parts shall be accessible by test finger, 6.4.2.2 or 6.4.2.3 of EN 61984	Unenclosed connector. Test finger or 50mm sphere pressed with 20N against the surface as specified by the manufacture Mated specimen and socket connector (if application) 7.3.6.1 of EN 61984

<sup>&</sup>lt;sup>a</sup> test items are for themselves separate tests and are performed on new specimens.

## 3. SUMMARY OF TEST RESULTS:

# Examination of product – all test group

Test Group	Test Item	Requirement	Test Result	Judgment
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Durability of marking	Marking shall be still readable	Not applicable(marking made by engraving)	passed
	Polarisation and coding	No damage likely to impair function	No damage likely to impair function	passed
Group A	Contact retention force in insert	No axial displacement likely to impair normal operation. Min 20N force for each pin or socket	No axial displacement likely to impair normal operation.	passed
	Mechanical strength impact	Connector and internal insulation shall no damage to impair normal use. A reduction of clearance and creepage distance is not allowed.	No damage likely to impair function	passed
	Visual and dimensional Meets request examination drawing	Meets requirements of product drawing	No damage likely to impair function	passed

<sup>&</sup>lt;sup>b</sup> measuring point: at the conductors as close as possible to the termination, if this is not possible, the conductor resistance shall be recalculated.



	Pull out force of terminations  a for Crimped connections	0.14mm <sup>2</sup> : 18N Min 4.0 mm <sup>2</sup> : 310N Min	0.14mm <sup>2</sup> : 27.71N 4.0 mm <sup>2</sup> : 337.37N	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Contact Resistance	Max.5mΩ	2.12mΩ Max.	passed
	Mechanical Operation (Durability)	500 operation cycles without load No damage likely to impair normal use	No damage likely to impair function	passed
Group B	Contact Resistance	The change of contact resistance shall be no more than 50 % of the reference value or ≤5 mΩ. The higher value is permissible	1.43 mΩ Max.	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
Group C	Temperature Rise Test	The sum of the ambient temperature and the temperature rise ( $\Delta T$ ) of a connector shall not exceed the upper limiting temperature	45.92 ℃	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Contact Resistance	Max.5mΩ	2.05 mΩ Max.	passed
	Dielectric Voltage Withstand Test	No flashover or breakdown of voltage	No flashover or breakdown of voltage	passed
	Insulation Resistance	Not less than $400M\Omega$	>2.43 x10 <sup>12</sup> Ω	passed
	Cold	No damage likely to impair function	No damage likely to impair function	passed
Group D	Dry Heat	No damage likely to impair function	No damage likely to impair function	passed
	Corrosion	No damage likely to impair function	No damage likely to impair function	passed
	Contact Resistance	The change of contact resistance shall be no more than 50 % of the reference value or ≤5 mΩ. The higher value is permissible	1.62 mΩ Max.	passed



	Dielectric Voltage Withstand Test	No flashover or breakdown of voltage	No flashover or breakdown of voltage	passed
	Insulation Resistance	Not less than 400MΩ	>1.36 x10 <sup>12</sup> Ω	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
Group E	Protection against electric shock	no live parts shall be accessible by test finger	no live parts shall be accessible by test finger	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed
	Contact Resistance	Max.5mΩ	2.73 mΩ Max.	passed
	Vibration, Random	No damage likely to impair function No discontinuities greater than t>1µs	No damage likely to impair function No discontinuities greater than t>1µs	passed
Group F	Shock	No damage likely to impair function No discontinuities greater than t>1µs	No damage likely to impair function No discontinuities greater than t>1µs	passed
	Contact Resistance	The change of contact resistance shall be no more than 50 % of the reference value or ≤5 mΩ. The higher value is permissible	0.96mΩ Max.	passed
	Visual and dimensional examination	Meets requirements of product drawing	No damage likely to impair function	passed