



T7112DS PRINTER

THERMAL TRANSFER PRINTER (300dpi)

TECHNICAL DATASHEET

TTDS-286 issue 1, July 2023

The T7112DS printer is a strong, 24hour cycle industrial 300dpi thermal transfer printer. This double side printer enables top and bottom printing with 1 print pass. Specially designed to print on a wide range of TE Connectivity (TE) identification heat shrink sleeves and tubing. Labels, and cable markers can also be printed using the single side print functionality.

The T7112DS printer is now also available bundled, with the latest version of TE Connectivity printing software, WinTotal. Please see page 3, for Printer order details.

Features

- High accuracy printing
- Single and Double-sided printing
- Easy to use
- Small footprint
- Easy to fit accessories
- High definition for 2D barcodes & graphics
- Full color touch screen
- Help video's Loaded on printer

Applications

- Industrial environments

Approvals / Declarations

- CE
- FCC Class A
- CB
- cULus
- CCC
- RCM
- UKCA

For the latest issue of the printer, Cutter and Perforator EU Declaration of conformity please download:

"CE_CERT_N84-00009_C1" for the T7112DS-PRINTER

These documents can be found at the TE document centre:

<http://www.te.com/commerce/DocumentDelivery/DDEController>

Environmental

A downloadable declaration and further information covering RoHS and REACH compliance can be found at the 'TE Product Compliance Support Centre':

<http://www.te.com/en/resources/product-compliance.html>

Specifications

The printer's 300dpi resolution, combined with recommended labels, cable markers, and identification heat shrink sleeves and tube. Along with the thermal transfer ribbons, meet all relevant TE performance specifications.

Print quality and print performance can only be guaranteed on TE printable products when specific TE printer and ribbons are used.

The current list of recommended printers and ribbons combinations can be found in TE document 411-121005 'Identification Printer Product Ribbon Matrix'.

This document can be found at the TE document centre:

HELP

For help and assistance please contact your local TE Connectivity representative. Alternatively, please contact your local Identification specialist by consulting TE document "411-121057" This document can be found at the TE document centre:

<http://www.te.com/commerce/DocumentDelivery/DDEController>

PRINTER ORDERING INFORMATION

DESCRIPTION	PART NUMBER
T7112DS-PRINTER	1-2186576-1
T7112DS-SWARE-PRINTER (Note 1)	1-2186577-1

PRINTER PROPERTIES

PERFORMANCE

PRINT SPEED:	30, 40, 50, 75, 100, 125, 150mm/s. (1, 1.5, 2, 3, 4, 5 and 6in/s)
PRINT WIDTH MAX:	105.7mm (4.16 in).
PRINT DEFINITION:	300 dpi Thermal Transfer
LABEL WIDTH: CARRIER & TUBE WIDTH:	10 - 110mm (0.4 - 4.33 in). 9 - 114mm (0.25 - 4.5 in).
LABEL HEIGHT: LABEL THICKNESS:	3mm (0.12 in) minimum height without Label backfeed. 4mm (0.16 in) minimum with label backfeed to 4,000mm (157.5 in) maximum. Label thickness 0.03 - 0.60mm (0.001- 0.024 in). Tube thickness up to 1.1mm (0.043 in).
INTERNAL ROLL CAPACITY:	205mm (8 in) Maximum outside roll diameter, inside core diameter 38.1 – 100mm (1.5 – 4 in).
INK RIBBONS	25.4mm (1 inch) core, ink inside or outside, variable length up to 450m (1476 ft) Width 25 - 114mm (0.98 - 4.49 in)
OPERATING TEMPERATURE, HUMIDITY:	+5°C to +40°C (+41°F to +104°F). 10 - 85% non condensing.
SENSOR	Variable position Gap & Reflective (automatic calibration).
ELECTRICAL REQUIREMENTS:	100 to 240 VAC- 50/60Hz, PFC.
POWER CONSUMPTION:	Standby<10W / Typical 150W / Maximum 300W.
PHYSICAL CHARACTERISTICS:	Depth: 594mm (23.4 in). Height: 395mm (15.6 in). Width: 248mm (9.76 in). Weight: 21kg (46.3 lb).
ELECTRONICS:	RAM 256MB, Processor speed 800MHz, Memory IFFS flash 50MB, Slot for SD memory card up to 512GB.
INTERFACES:	RS232C 1,200 to 230,400 baud/8 bit. USB 2.0 Hi-speed device to connect a PC. Ethernet 10/100 BASE-T. LPD, IPv4, IPv 6, RawIP printing, DHCP, HTTP, FTP, SMTP, SNMP, TIME, NTP, Zeroconf, SOAP web ser- vice. 1 x USB host at the operation panel for Service Key or USB memory stick. 1 x USB host at the operation panel for USB WLAN stick 2.4 GHz 802.11b/g/n. 2 x USB host at printer rear for Keyboard, barcode scanner, USB memory stick, USB Bluetooth adapter, USB WLAN stick 2.4 GHz 802.11b/g/n + 5 GHz a/n/ac with rod antenna. WLAN 802.11b/g/n, hotspot or infrastructure mode GHz.

Note 1, T7112DS-SWARE-PRINTER comprises the latest full version of WinTotal version USB user license with the basic printer.

PRINTER SPARE PARTS ORDERING INFORMATION

300 dpi Printhead	
Description:	T7112DS-PRINthead
Part number:	1-2186578-1
Drive roller	
Part number:	T32/T71-DR4-DRIVE-ROLLER
Description:	1-2186505-1
Media Sensor	
Description:	T32/T71-PRINTER-LABEL-SENSOR
Part number:	1-2186515-1

For full details of replacement parts please consult TE document 404-121056, T7112DS PRINTER ILLUSTRATED PARTS LIST


PRINTER ACCESSORY ORDERING INFORMATION

Cutter:	
Description:	T711DS-CUTTER
Part number:	1-2186581-1
Perforator:	
Description:	T7112DS-PERFORATOR
Part number:	1-2186582-1
Universal reel holder:	
Description:	PRINTER-UNIVERSAL-REEL-HOLDER
Part number:	EC9926-000

For more details regarding printer accessories please consult TTDS-260, and for more details concerning the Universal payoff please consult TTDS-259.



SOFTWARE



SOFTWARE ORDERING INFORMATION

WINTOTAL 7 (Dongle)	
Description	WINTOTAL-7-DONGLE
Part number	1-2186545-1
WINTOTAL 7 (Licence)	
Description	WINTOTAL-7-END-USER-LICENCE
Part number	1-2186546-1

For full compatibility with T7112DS printers please use WinTotal Version 7.2.01 or later.

Cable Markers and Labels are fully supported by WINTOTAL printing software, available from the TE product store:

www.te.com/wintotal

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts and WinTotal are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2023 TE Connectivity Ltd. family of companies All Rights Reserved.

