

SPECIFICATION CONTROL DRAWING

55PC0816

TITLE

WIRE, RADIATION-CROSSLINKED, MODIFIED, ETFE-INSULATED,
GENERAL PURPOSE, NORMAL AIRFRAME

Date


07-16-04

Revision

B

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

CONDUCTOR - NICKEL-COATED HIGH STRENGTH
COPPER ALLOY



INSULATION - RADIATION-CROSSLINKED,
MODIFIED ETFE

CONSTRUCTION DETAILS

PART NUMBER 1/	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	CONDUCTOR DIAMETER (in.)			FINISHED WIRE					
			LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
							LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC0816-26-*	26	19 x 38	.0175	.0183	.0191	49.4	.0366	.0385	.0404	1.55	1.70
55PC0816-24-*	24	19 x 36	.0225	.0233	.0241	30.1	.0416	.0435	.0454	2.18	2.34
55PC0816-22-*	22	19 x 34	.0285	.0293	.0301	18.6	.0476	.0495	.0514	3.12	3.30
55PC0816-20-*	20	19 x 32	.0365	.0375	.0385	11.4	.0561	.0580	.0599	4.64	4.85
55PC0816-18-*	18	19 x 30	.0452	.0464	.0476	7.1	.0659	.0680	.0701	6.94	7.27
55PC0816-16-*	16	19 x 29	.0514	.0527	.0538	5.5	.0737	.0760	.0783	8.80	9.17

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

COLOR: White preferred

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

IDENTIFICATION AND COLOR STRIPING DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

INSULATION ELONGATION AND TENSILE STRENGTH:

Total Insulation,

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

INSULATION FLAWS:

Spark Test, 3.0 kV (rms)

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS: .010 in. (nominal) total insulation

SHRINKAGE: 230 ± 3°C for 1 hour, 0.125 in. (maximum) in 12 in.

VOLTAGE WITHSTAND TEST (Post Environmental):

2500 volts (rms)

PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators.

1/ Example: AWG 22, white: 55PC0816-22-9

AWG 22, white with black stripe: 55PC0816-22-90

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE
ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

tyco
Electronics

Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297