

# Validation Test Report

### 250 AMPIP POD

June 23, 2016.



| Tested &<br>Reported By | Reviewed | Approved |                | From June 20, 2016 |  |  |  |  |
|-------------------------|----------|----------|----------------|--------------------|--|--|--|--|
|                         | Ву       | Ву       | Test Date      | To June 23, 2016   |  |  |  |  |
| 8                       | (~)      | east)    | Classification | Unrestricted       |  |  |  |  |

## • TE CONNECTIVITY RELIABILITY TEST REPORT

Test Name: Validation for 250 AMPIP POD.

#### 1. Introduction

#### 1-1 Purpose

Testing was performed on the 250 AMPIP POD to determine

if it conformance to the requirements of Product Specification 108-5100, Rev.B1

This experiment is intended to verify the reliability of the HSG material change.

(Applied resin: PA66, PN: 1573672-2)

#### 1-2 Scope

This report covers the electrical, mechanical, environmental performance requirements of the 250 AMPIP POD.

The testing was performed between June 20, 2016 and June 22, 2016.

#### 1-3 Test Samples

The test samples were randomly selected from normal current production lots.

| P/N        | Description                  |  |  |  |  |  |  |
|------------|------------------------------|--|--|--|--|--|--|
| 1-171706-1 | 250 AMPIP POD                |  |  |  |  |  |  |
| 2232112-1  | 250 SERIES FASTON RECEPTACLE |  |  |  |  |  |  |

#### 1-4 Conclusion

The 250 AMPIP POD meets the electrical, mechanical performance requirements of Product Specification 108-5100, Rev.B1

#### 1-5 Attachment

1) Test Result

# 1) Test Result

# - Test Group 1

| NO. | Test Items              | Test Condition | Acceptance criteria | Unit |               | Test Result |       |       |       |       |       |       |       |          |
|-----|-------------------------|----------------|---------------------|------|---------------|-------------|-------|-------|-------|-------|-------|-------|-------|----------|
|     |                         |                |                     |      | Wire<br>(AWG) | S1          | S2    | S3    | S4    | S5    | Min.  | Max.  | Avg.  | Judgment |
| 1   | Contact Retention Force | Initial        | 8 kgf Min.          | kgf  | -             | 24.29       | 26.03 | 23.83 | 25.44 | 24.37 | 23.83 | 26.03 | 24.79 | ОК       |

# - Test Group 2

| NO. | Test Items               | Test Condition | Acceptance criteria                | Unit | Test Result   |      |      |      |      |      |      |      |      |          |
|-----|--------------------------|----------------|------------------------------------|------|---------------|------|------|------|------|------|------|------|------|----------|
|     |                          |                |                                    |      | Wire<br>(AWG) | S1   | S2   | S3   | S4   | S5   | Min. | Max. | Avg. | Judgment |
| 1   | Insulation<br>Resistance | Initial        | 500 MΩ Min.                        | GΩ   | -             | 7.48 | 7.71 | 7.75 | 7.96 | 7.71 | 7.48 | 7.96 | 7.72 | OK       |
| 2   | Dielectric Strength      | Initial        | No abnormalities shall be evident. | -    | -             | ОК   | ОК   | OK   | ОК   | ОК   | -    | 1    | -    | ОК       |