

923 Receptacle angled rotatable speedtec

9-pin Earth-to-Housing Connection according to VDE 0627

flange mount /Flange 25x25

B ED C 091 NN 00 00 1116 000 B G C 091 N 00 00 1116 000



Contact Arrangement mating view





Technical Data

number of pins

protection type rotation range

rated current rated voltage

mating cycles

Material

housing insulation insert

temperature range

Electrical Data

pollution degree over voltage category

max. height for operation

rated insulation voltage (L-L)

power

signal

zinc diecast / chromated PA 6.6 mod., UL 94/V0 FKM

9

5

330°

4 (3+PE)

power

6000 V

500

ĪII

2000 m

max. 30 A* 630V (AC/DC)

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

-20 °C to 130 °C

when connected IP 66/67

signal

2500 V

max. 7 A* 250 V (AC/DC)

Contacts (not part of product contents)


Tools (not part of product contents)

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.


While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





Montagefenster



Main Dimensions Receptacle angled rotatable

*for max. wire cross-section pay attention to the cross-section of used contacts