

723 htec Receptacle angled rotatable

speedtec

5+2-pin insulation insert Code 8 (pin) Earth-to-Housing Connection according to VDE 0627 Protection Against Contact according to VDE 0623 **Electrically Protective Separation according to VDE 0140** flange mount /Flange 28x28

H 56 C 422 NN 00 00 0300 000 H G C 422 N 00 00 0300 000



Contact Arrangement mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz







*for max. wire cross-section pay attention to the cross-section of used contacts

Electrical Data rated current rated voltage rated insulation voltage (L-L)

Technical Data

number of pins

protection type

rotation range

mating cycles

temperature range

power

signal

6000 V 500

2000 m

3 III

5 (4+PE)

power

max. 30 A*

-20 °C to 130 °C

when connected IP 66/67

850V/DC 630V/AC 50V/DC 30V/AC

signal

1500 V

max. 1.2 A*

2

3309

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

zinc diecast / chromated

PA 6.6 mod., UL 94/V0

pollution degree over voltage category max. height for operation

Material

housing insulation insert seals

FKM Contacts (not part of product contents)

Tools (not part of product contents)

2018