

a) Part as supplied.



b) Part after unrestricted recovery.



NOTES:



Moulded Part Material: -25C (Black); Elastomer/Silver Composites, Fluid Resistant

Kits to include cleaning tissue, 1 piece 100 grit emery cloth & 1 piece of atum, and S1125 adhesive kit 5 and S1184 conductive adhesive kit 3.

Kit to be used in conjunction with TCFS installation procedure.

Dimensions in mm [inches for reference]

	Entransiana in Timir [interes for Telesconde]												
Part No.	A MIN	J		М	A/F		P	JO					
		MIN a	MAX b	THREAD	NÚT	NOM	±10% b	REF b					
TCFS-12	7.4 [.29]	11 [.43]	5.0 [.20]	M12 X 1.5	17 [.67]	24 [.94]	50 [1.97]	15 [.59]					
TCFS-16	10.1 [.40]	15 [.59]	6.0 [.24]	M16 X 1.5	22 [.87]	29 [1.14]	65 [2.56]	17 [.67]					
TCFS-20	14.1 [.56]	17 [.67]	7.2 [.28]	M20 X 1.5	27 [1.06]	34 [1.34]	77 [3.03]	20 [.79]					
TCFS-24	19.1 [.75]	21 [.83]	8.5 [.33]	M24 X 1.5	30 [1.18]	38 [1.50]	90 [3.54]	25 [.98]					
TCFS-30	24.1 [.95]	25 [.98]	10.0 [.39]	M30 X 1.5	36 [1.42]	47 [1.85]	115 [4.53]	30 [1.18]					
TCFS-36	30.1 [1.19]	35 [1.38]	15.8 [.62]	M36 X 1.5	41 [1.61]	52 [2.05]	140 [5.51]	30 [1.18]					

F 191									
DIMENSIONS:	DWN P. VU	170CT2016	MATERIA		E NOTES	FINISH		SEE NOT	ES
mm [INCHES] TOLERANCES UNLESS	CHK N. NAGAR	170CT2016							
OTHERWISE SPECIFIED:	APVD M. POPE	170CT2016	TE Connectivity					I.y	
0 PLC	PRODUCT SPEC —	NAME ADAPTOR ASSEMBLY							
2 PLC ± - 3 PLC ± -	APPLICATION SPEC					_			
4 PLC ± – ANGLES ± –	_		SIZE	CAGE CODE	DRAWING NO				RESTRICTED TO
	WEIGHT		A4	00779	C- TOFS	S-XX-XX	X - 0XX -	-25CE	_
	CUSTOMER DR	AWING				scale D1	CHEET	1 OF	1 REV 2

Connectivity

2016 By TE