





for customer
release 20.09.2019



Mounting Detail



Third Angle Projection



	Date	Name	mm	Scale		Drawing No:	
Create	18.09.2019	Stock		1:1		07-2-2-15 928	
Edited	23.09.2019	WalzA		General Tolerances DIN ISO 2768 cL			
Check	23.09.2019	Stock					NSN.:

Circuit Diagram

	Circuitry made with toggle at		
	keyway	center	opposite keyway
Pole 1			
Pole 2			

Actuation

- locking keyway side
- locking center position
- locking opposite keyway side



Construction

Material, Casing Thermoplast GF
Material, Cover GD-ZnAl4Cu1
Connections Faston DIN 46 244-A6,3-0,8
Protection Interior IP 65 IEC 60529
Connections IP 00 IEC 60529

Mechanical Data

Current carrying parts CuZn-Alloy
Contacts Ag
Ambient Temperature Range -40°C to +85°C
Storage Temperature Range -40°C to +85°C
Life Cycle (nominal Load) 100.000 operations

Electrical Data

Voltage 12 V DC ohmic Load 20A
28 V DC ohmic Load 20A
28 V DC inductive Load at L/R = 5 ms 15A
28 V DC lamp Load 7A

Min. Rating 12 V DC, 20 mA

It is recommended to use gold-plated contacts
for lower currents or voltages.

For this drawing we reserve the copyright
in accordance with DIN ISO 16016

	Date	Name	mm	Scale		Drawing No:
Create	20.09.2019	Stock		1:1		07-2-2-15 928
Edited	23.09.2019	WalzA	General Tolerances DIN ISO 2768 cL			
Check	23.09.2019	Stock				