



M5600

Software Protocol Specification

5600 Service

UUID	F000AB30-0451-4000-B000-000000000000
------	--------------------------------------

AVAILABLE CHARACTERISTICS

Name	UUID	Bytes	Read / Write	Notified
Data	F000AB31-0451-4000-B000-000000000000	14	Read	YES
Data Rate	F000AB31-0451-4000-B000-000000000000	12	Read / Write	YES
Status	F000AB3F-0451-4000-B000-000000000000	1	Read	NO

DATA CHARACTERISTIC BYTES FIELDS

0	1	2	3	4	5	6	7	8	9	10	11	12	13
T LSB	T MSB	P LSB	P	P	P MSB	Pmin LSB	Pmin	Pmin	Pmin MSB	Pmax LSB	Pmax	Pmax	Pmax MSB

T is a 16-bits signed integer, equals 0x7FFF if erroneous.
 P, Pmin and Pmax are 32-bits signed integers, equal 0x7FFFFFFF if erroneous.

T is a temperature value with 0.01°C accuracy.
 P, Pmin and Pmax are pressure values with 0.1Pa accuracy

CONVERSION

Temperature (°C) = T / 100

Pressure (Pa) = P / 10

Pressure (Psi) = P / 10 / 6894.7

DATA RATE CHARACTERISTIC BYTES FIELDS

0	1	2	3	4	5	6	7	8	9	10	11
Data rate LSB	Data rate	Data rate	Data rate MSB	Min LSB	Min	Min	Min MSB	Max LSB	Max	Max	Max MSB

Data rate, Min and Max are 32 bits unsigned integers.
 Data rate is the actual sensor data rate in milliseconds.
 Min is the minimum admissible data rate in milliseconds.
 Max is maximum minimum admissible data rate in milliseconds.

NB. Only Data rate can be written.

STATUS

0x00	OK
0x01	Sensor error

NB. All signed integers use two's complement representation.

Battery Service

UUID	F000180F-0451-4000-B000-000000000000
------	--------------------------------------

AVAILABLE CHARACTERISTICS

Name	UUID	Bytes	Read / Write	Notified
Data	F0002A19-0451-4000-B000-000000000000	2	Read	YES

DATA CHARACTERISTIC BYTES FIELDS

Byte 0	Byte 1
Battery Level (%)	Status

0% to 100% represents a supply voltage from 2.0V to 3.0V with 1%/bit resolution.

STATUS

0x00	Discharging
0x01	Charging

Device Name Service

UUID	F000FA00-0451-4000-B000-000000000000
------	--------------------------------------

AVAILABLE CHARACTERISTICS

Name	UUID	Bytes	Read / Write	Notified
Device Name	F000FA01-0451-4000-B000-000000000000	18	Read/Write	NO
Default Device Name	F000FA02-0451-4000-B000-000000000000	18	Read	NO

Both Device Name and Default Device name are in ASCII format. Unused bytes should be nulled.

Default Device Name is "TESS 5600".

te.com/sensorsolutions

Android is a trademark of Google Inc.

Google Play is a trademark of Google Inc.

iOS is a trademark or registered trademark of Cisco in the U.S. and other countries and is used under license.

Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

Android and Windows are trademarks of their respective owners.

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, MEAS, TE Connectivity, TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.