

Tyco Electronics Corporation 300 Constitutional Drive Menlo Park, CA. 94025 U.S.A.

Raychem

No: RB-109 Rev: F Date: December 14, 2005 Page 1 of 15

SolderSleeve Devices Specification For Commercial Wire Splices

Table of Contents

Chapte	er	Pages
1.0 1.1 1.2	General Requirements Design of the Electrical Connection-Reminder Concerning The Approval Procedure Supplier's Responsibility	3 3
2.0 2.1 2.2 2.3	Definition of the Test Specimens Introduction Definition of the Conductor Cross-Sectional Area Big Cross-Sectioned Test Specimens (bigger than 6mm ²)	3 3 3 3
3.0 3.1 3.2 3.3	Environmental Conditions for the Vehicle Connections Temperature Classification Vibration Classification Sealing Classification	4 4 4 4
4.0	Normal Atmospheric Test Conditions	4
5.0 5.1	Electrical Tests Contact Resistance	5
5.1.1 5.1.2 5.2 5.2.1 5.2.2 5.2.3 5.2.3	Test method according to millivolt level Test method using specified test current Insulation Resistance Unsealed connections Sealed connections Measurement conditions Dielectric Withstand Voltage	5 6 6 7 7 7
6.0	Mechanical Tests	8
6.1 6.2	Tensile Strength Abrasive Wear	8 8

Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	5	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 2 of 15

7.0	Aging and Endurance Tests	8
7.1	Vibrations of the Connection	8
7.2	Thermal Shocks	9
7.3	Periodic Current Intensity Test	10
7.4	Endurance (Temperature – Humidity)	10
7.4.1	Temperature endurance	11
7.4.2	Humidity endurance	11
8.0	Sealing	11
8.1	Immersion	11
8.2	Sealing after Bending	12
8.3	Sprinkling	13
9.0	Miscellaneous Tests	13
9.1	Resistance to Fluids	13
9.2	Vertical Combustion	13
10.0	Visual Sequence	13
11.0		14
11.0	Test Sequence	14

ty	CO

Tyco Electronics Corporation**Raychem**300 Constitutional DriveMenlo Park, CA. 94025 U.S.A.

No: RB-109 Rev: F Date: December 14, 2005 Page 3 of 15

1.0 General Requirements

1.1 Design of the Electrical Connections - Reminder Concerning the Approval Procedure. The Specification RB 109 is a general specification regarding electrical stub splices requirements. Products corresponding to the present specification may undergo additional tests in compliance with the customer's standards or specifications prior to receiving the customer's approval.

1.2 Supplier's Responsibility The specific requirements of a customer may apply to all or part of the present specification after approval by both Tyco Electronics and the customer(s).

2.0 Definition of the Test Specimens

2.1 Introduction

Because of the large number of possible configurations for each splice, two types of test specimens shall be prepared (a minimum and a maximum) which shall represent the minimum and maximum cross-sectional areas applicable for each splice. These test specimens shall consist of a SOLDERSLEEVE DEVICE and usually two 200mm maximum length standard conductors with identical cross-sectional areas. However, a third wire can be added if necessary in order to approach as closely as possible the desired cross-sectional area. The qualification shall be obtained using: either the customer's wire or a common wire clearly designated

2.2 Definition of the Conductor Cross-Sectional Area

For each test specimen, a standard conductor shall be used for which the doubling of the cross-sectional area is as close as possible to the cross-sectional area specified in a detail specification; a third and smaller wire may be added if necessary to reach the desired cross-sectional area. However, in order to have test specimens which represent the authentic conditions, the cross-sectional area of the conductor should not be greater than 3mm^2 .

2.3 Big Cross-Sectioned Test Specimens (sections greater than 6mm²).

If the cross-sectional area of the so-defined test specimen is greater than 3mm², a standard conductor for which the cross-sectional multiple is as close as possible to the specified cross-sectional area shall be used. In each specific case, every measurement shall be taken on two marked conductors.

Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	, , , , , , , , , , , , , , , , , , ,	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 4 of 15

3.0 Environmental Conditions for the Connections on Vehicles

They are submitted to variable parameters of temperature, vibration, humidity or exposure to various types of fluids depending on the position of the connections in the vehicles.

3.1 Temperature Classification

Four classes of environmental temperature have been determined for the connections in consideration of the raw materials involved.

Class	Environmental	Test
	temperature (TS)	temperature (TE)
1	-40°C to +85°C	-40°C to +100°C
2	-40°C to +100°C	-40°C to +125°C
3	-40°C to +125°C	-40°C to +150°C
4	-40°C to +150°C	-40°C to +175°C

3.2 Vibration Classification

Two classes of vibration have been determined:

- Class 1 (body): from 10 to 55 Hz, constant amplitude ±0.75mm from 55 to 500 Hz, with a constant acceleration of 10g.
- Class 2 (engine): from 10 to 55 Hz, constant amplitude ±1.5mm from 55 to 500 Hz, with a constant acceleration of 20g.

3.3 Sealing Classification

Three classes of sealing have been determined:

- Class 0: unsealed
- Class 1: sealed when sprinkled
- Class 2: sealed when immersed
- See paragraph 8 for further details.

4.0 Normal Atmospheric Test Conditions

- The normal atmospheric conditions are defined in the French standard register number NF C 20-600.
- The standard range of atmospheric conditions applicable to the tests and measurements of the present specification is the following:

Temperature	Relative humidity (%)	Atmospheric Pressure Pa (m bar)
23 ± 5	45 < HR < 75	860 < Pa < 1060

• Should it be impossible to carry out the tests in the above conditions, the atmospheric conditions that are actually used must be indicated in the test report.

tyco

Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	2	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 5 of 15

The relative humidity and the pressure may be omitted in the test report if they do not influence the results. The temperature and humidity must remain constant during the entire series of test.

5.0 Electrical Tests

5.1 Contact Resistances

The test is done with the electrical circuit described in this section. The resistance of the wire employed is deducted from the value measured. Method for measuring length and comparative equivalent lengths.



Re = the resistance of the specimen==> Ue = the voltage drop of the specimenRf = the resistance of an equivalent length of wire ==> Uf = the voltage drop of an
equivalent wireRc = the contact resistance==> Uc = the drop due to the connection
==> Ue - UfRcUc = Re - R==> Ue - Uf

- 5.1.1 Test method according to millivolt level
 - The voltage employed must be in compliance with the following characteristics:
 - open circuit voltage < 20 mV D.C.
 - short circuit intensity set at 100 mA.

tyco

Electronics

Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	2	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 6 of 15

The contact resistance value (Rc) is the difference between the specimen resistance (Re) and the resistance of an equivalent length of wire (Rf).

Requirement: Two_measurements per specimen shall be registered by inverting the direction of the current. The average value of these two measurements of contact resistance shall not be greater than 4 mOhms.

5.1.2 Test method using specified test current

The electromotive force of the current is less than 15 V DC. Unless specified otherwise in a customer specification, the short circuit intensity shall be set at 7 A/mm² per wire cross-section used (the actual cross-section calculated according to the measure of each strand \pm 0.01 mm).



The measurements shall be made after thermal stabilization.

Requirement: The voltage drop value (Uc) - in mV - is the difference between the voltage drop of the specimen (Ue) and the voltage drop of the equivalent length of wire (Uf). The calculated value: $RC = Uc \div I$, shall not be greater than 4 mOhms.

- 5.2 Insulation Resistance
- 5.2.1 Unsealed connections

Test Assembly:



A sheet of aluminum, which is connected to one of the ends of the measuring apparatus, is rolled around the connection in order to form a common framework. One of the wires is connected to the other end of the apparatus.



Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	5	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 7 of 15

5.2.2 Sealed connections



5.2.3 Measurement conditions

The measurement shall be done at 100 ± 15 V DC.

- a) Unsealed connection: test assembly in compliance with paragraph 5.2.1. The insulation resistance value can be recorded once a steady reading is obtainable. If a steady reading is not obtainable, the insulation resistance shall be recorded at the 60th s \pm 5 s after the current is applied.
- b) Sealed connections: test assembly in compliance with paragraph 5.2.2. The resistance value shall be recorded after immersion in the specified aqueous solution for 1 minute.

Requirement: insulation resistance should be \geq : than $10^2 \Omega$.

- 5.3 Dielectric Withstanding Voltage
 - The test assemblies for the sealed sleeves and the unsealed sleeves shall be the same as those in paragraph 5.2.1.
 - A test voltage of 2000 V R.M.S. at 50 Hz is applied for 60s ±5s between one of the connection wires and the framework.
 - There should not be any signs of flash-over, crackling, blow-out, beginning of arcing, or leakage current more than 1 mA.

tyco

Tyco Electronics Corporation 300 Constitutional Drive Menlo Park, CA. 94025 U.S.A.

Raychem

No: RB-109 Rev: F Date: December 14, 2005 Page 8 of 15

6.0 Mechanical Tests

6.1 Tensile Strength

The tensile test consists of pulling the two free ends of the assembled wires or two of the wires among the bundle installed if the specimen contains more than 2 wires.

The test shall be done with the heat-shrinkable sleeve installed.

The moveable clamp of the traction machine must move at a constant speed of 50mm/minute.

Assembly: force perpendicular to sample axis (or pealing)



The maximum force measured must be within the limits indicated in the table below:

wire section	mini rupture
in mm ²	in Newton
0.35	60
0.6	100
1	140
1.4	180
2	220
3	280

6.2 Abrasive Wear

The abrasive wear resistance of the insulation shall be in compliance with Standard BS G 195.

7.0 Aging and Endurance Tests

7.1 Vibrations on the Connection.

The vibration class, selected among those defined in paragraph 3.2. Is indicated in the SCD.

A voltage drop test is conducted through the splice (s) in order to detect any eventual micro cut-offs.

The connection is attached to the plate of the vibrating system for a total duration of 6 hours, divided into periods of 2 hrs. For each of the 3 axes (2 of which are horizontal, cf. figure below). The wires shall be slightly tight in order to eliminate any slackness.



Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	2	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 9 of 15

A test configuration of both the minimal and maximal cross-sections compatible with the splice shall be tested.



The variation in frequency is done by logarithmic scanning of one octave per minute. No micro cut-off longer than 1 μ s must appear during the test.

7.2 Thermal Shocks:

Test temperature (TE) is selected among those defined in paragraph 3.1., according to the temperature class application.

The splice undergoes 5 cycles as defined hereafter (also see following figure):

- a) Maintain the temperature in the test chamber at $-40^{\circ}C \pm 2^{\circ}C$ for 30 minutes.
- b) Raise the temperature in the test chamber to $TE^{\circ}C \pm 2^{\circ}C$ in a maximum of 30s.
- c) Maintain the temperature in the test chamber at $TE^{\circ}C \pm 2^{\circ}C$ for 30 minutes
- d) Return the temperature in the test chamber back to $-40^{\circ}C \pm 2^{\circ}C$ in a maximum of 30s.



Requirement: The difference between the contact resistance value after conditioning and the initial contact resistance shall be less than 4 mOhms. However, this contact resistance shall never be greater than 6 mOhms.

tyco

Tyco Electronics Corporation 300 Constitutional Drive	Raychem	No: RB-109 Rev [.] F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005 Page 10 of 15

N.B.: The voltage drop measurements before and after the climate test shall be in compliance with the procedure defined in paragraph 5.1.1.

SPECIAL REMARK: The_measurement points on the specimen must be protected against corrosion in order to have reliable results.

7.3 Periodic Current Intensive Test

The purpose of this test is to check the withstand strength of the splice when submitted to the current passage for which it is specified.

Definition of the nominal intensity of the splice:

-Splice nominal intensity is 7 A/mm²

-Since the cross-sectional area of the wires is sometimes slightly different from the theoretical cross-sectional area it is necessary to calculate the actual wire cross-sectional area according to the diameter of the individual strands.



Nominal intensity = 7A x the cross-sectional area of a strand multiplied by the number of strands measured ± 0.01 mm.

For the configurations of more than 2 wires only the 2 marked conductors shall be taken into consideration.

The length of the test shall be 500 of the above defined cycles. *Requirement*: Cf. paragraph 7.2

7.4 Endurance (Temperature – Humidity)

The purpose of this test, divided into 2 parts, is to check the splice aptitude for voltage transmission in extreme environmental conditions.

The first part consists of a temperature test and the second a high relative-humidity test. The procedure for the voltage periodic intensity test is identical to the one defined in paragraph 7.3; the test intensity is equal to 40% of the wire nominal intensity. The cross-sectional area of the conductor specimen (s) is defined in the S.C.D.

THE	
LUL	_
-	

Tyco Electronics Corporation	Raychem	No: RB-109
300 Constitutional Drive	5	Rev: F
Menlo Park, CA. 94025 U.S.A.		Date: December 14, 2005
		Page 11 of 15

- 7.4.1 Temperature endurance
 - The connections are submitted to a 15 days voltage test (360 cycles) at the maximal environmental temperature.
 - The temperature class selected among those indicated in paragraph 7.2 is found in the detail specification.

Requirement: Cf. paragraph 7.2

7.4.2 Humidity endurance

The connections are submitted to 3 cycles defined as below:

- 1 cycle
- (a) 24 hours voltage periodic intensity test (24 cycles) at $85^{\circ}C \pm 2^{\circ}C$, with 95 to 99% relative humidity.
- (b) maintenance at $23^{\circ}C \pm 5^{\circ}C$ for 24 hours without periodic intensity of current.

REMARKS: Only distilled water shall be used for this test.

Requirement: The difference between the contact resistance value after conditioning and the initial contact resistance shall be less than 6 mOhms. However, this contact resistance shall never be greater than 8 mOhms.

NB: The contact resistance measurements before and after the climate test shall be in compliance with the procedure defined in paragraph 5.1.1.

SPECIAL REMARK: The measurement points on the specimen must be protected against corrosion in order for the reading of the results to be reliable.

8.0 Sealing

8.1 Immersion (sealed splices Class 2 only).

- The assembled and cabled splices shall undergo 5 cycles of exposure.
- Each cycle consists of 30 minutes in dry air at temperature T, followed by 30 minutes of total immersion in a salt solution of 5% of the mass at 23°C±5°C according to the following figure:



Tyco Electronics Corporation No: RB-109 Raychem 300 Constitutional Drive Rev: F Menlo Park, CA. 94025 U.S.A. Date: December 14, 2005 Page 12 of 15



The transition time between the chamber and the bath does not exceed 30 seconds.

- The temperature class selected among those defined in paragraph 3.1 is indicated in the detail specification.
- At the end of the test the insulation resistance (cf. paragraph 5.2) shall be immediately measured on the specimens.

Requirements: identical to those defined in paragraphs 5.2.

NB: the sealing level required is equivalent to a withstanding of pressure and depression of 300 mbars.

Sealing after Bending. (Sealed splices Class 2)

- The test assembly shall be identical to the one defined in paragraph 6.1. The • speed of the tensile machine shall be 50 mm/min.
- The tensile machine shall be stopped as soon as the limit of 50 N (Newton) or, • for the smallest cross sectional area, 50% of the minimum stripping resistance specified in the \S 6.1



Requirement: The specimen shall then undergo the test specified in paragraph 5.2.2.

If this document is printed it becomes uncontrolled. Check for the latest revision. 2005 Tyco Electronics Corporation. All rights reserved.

8.2

300 C	Electronics Corporation onstitutional Drive Park, CA. 94025 U.S.A.	Raychem	No: RB-109 Rev: F Date: December 14, 200 Page 13 of 15	95
		- -	ed control point due to the rigidne as a counterbalance to one of th	
8.3		e IPX4 defined in the Fren	to the sprinkling test to check the ch standard register No. NFC after conditioning.	;
9.0 9.1	 specified temperature: motor oil at 100°C (15 W 40 manual transmission oil at 100°C (type cooling fluid at 100°C (type brake fluid at 70°C (type H1 motor fuel N at 23°C (90%) motor fuel O at 23°C (85%) diesel fuel oil at 23°C (90%) motor protection fluid at 23°C 	0 multigrade for gasoline a 00°C (HP 90) C at 50% or BASF -G at 3 D 55 or SHELL BS 38 or N of fluid C (*) + 7% ethyl a of fluid C (*) + 15% methyl of ASTM No. 3 + 10% pa °C wiped clean and 24 hrs at 2 cking, or sizeable swelling	50%) NEWLOOK 2001 BENDIX) Ilcohol + 3% methyl alcohol) yl alcohol) araxylene 23°C ± 5°C, the splices should sh	70 hrs 1 hr 1 hr 1 hr 24 hrs 24 hrs 24 hrs 1 hr
9.2	Vertical Combustion Shall be in compliance wit	h French standard NF C 32	2-070.	
10.0	Visual Inspection The specimen shall not sho improper shrinkage overheated or unde punctured or cracke solder flow hinders missing or destroyed	e rheated ed s desired electrical perform	ance, etc.	

• missing or destroyed adhesive insert (in sealed product only).

tyco

Electronics

Tyco Electronics Corporation 300 Constitutional Drive Menlo Park, CA. 94025 U.S.A.

Raychem

No: RB-109 Rev: F Date: December 14, 2005 Page 14 of 15

11.0 Test Sequence

		<u>GROUP 1</u>	
No.	Tests	Paragraph No.	Remarks
1 2	Visual inspection Contact resistance Rc (*1)	10 5.1.1.	minimum 4 splices per configuration
3 4	Contact resistance Rc (*2) Voltage periodic intensity	5.1.2. 7.3	
5 6	Contact resistance Rc (*1) Visual inspection	5.1.1. 10	Event. 5.1.2.
		GROUP 2	
No.	Tests	Paragraph No.	Remarks
1 2 3 4 5 6	Visual inspection Contact resistance Rc (*1) Insulation resistance Vibration Visual inspection Thermal shocks	10 5.1.1. 5.2 7.1 10 7.2	minimum 4 splices per configuration
7 8	Contact resistance Rc Visual inspection	5.1.1. 10	Event. 5.1.2.
	*1) Method according to milli*2) Method using specified test		
		GROUP 3	
No.	Tests	Paragraph No.	Remarks
1 2 3 4 5 6 7	Visual inspection Contact resistance Insulation resistance Withstand voltage Temperature endurance Contact resistance Humidity endurance	10 5.1.1. 5.2 5. 7.4.1. 5.1.1. 7.4.2.	minimum 4 splices per configuration
8	Contact resistance	5.1.1.	5.1.2. if confirmation required
9	Insulation resistance	5.2	-
10	Visual inspection	10	

If this document is printed it becomes uncontrolled. Check for the latest revision. 2005 Tyco Electronics Corporation. All rights reserved.

tyco

Electronics

Tyco Electronics Corporation 300 Constitutional Drive Menlo Park, CA. 94025 U.S.A.

Raychem

No: RB-109 Rev: F Date: December 14, 2005 Page 15 of 15

<u>GROUP 4</u>

No.	Tests	Paragraph. No.	Remarks
1	Visual inspection	10	minimum 4 splices
2	Insulation resistance	5.2	per configuration
3	Sealing in natural position	8.1	
4	Insulation resistance	5.2.	
5	Visual inspection	10	
6	Sealing after bending	8.2	
7	Insulation resistance	5.2	

Tests Not Included In The Groups

Tests	Paragraph No.	Remarks
Tensile strength of the wire-to-	6.1	20 samples per
wire connection	6.1	cross-sectional area.
Resistance to fluids	9.1	1 connection per test fluid
Abrasive wear	6.2	According to BS G 195
Combustion	9.2	According to NF C 32-070