<b>tyco</b> Electronics	Tyco Electronics C 300 Constitutional Menlo Park, CA 94	Drive	Raychem	Specification This Issue: Date: Replaces:	<b>RT-375</b> Issue 7 4 February 2004 Issue 6
	Fluoropolym		MOFIT <sup>®</sup> RT-375 TI xible, Clear, Flame R	UBING Resistant, Heat-Shrinka	ble
1.	SCOPE				
	extruded tubing wh	ose diameter wil		ible, flame resistant, electrica d size upon the application of be clear.	
2.	APPLICABLE DO	OCUMENTS			
		documents appl		d herein. Unless otherwise sp ents form a part of this specifi	
2.1	GOVERNMENT-F	URNISHED DO	DCUMENTS		
	Federal				
	O-S-1926	Sodium Ch	lloride, Technical		
	<u>Military</u>				
	MIL-H-5606	Hydraulic	Fluid, Petroleum Base, Air	craft, Missile and Ordnance	
	MIL-T-83133	Turbine Fu	el, Aviation, Grade JP-8		
	MIL-L-7808	Lubricating	g Oil, Aircraft Turbine Eng	gine, Synthetic Base	
	MIL-A-8243	Anti-icing	and Deicing - Defrosting F	Fluid	
	MIL-L-23699	Lubricating	g Oil, Aircraft Turbine Eng	gines, Synthetic Base	

2.2	OTHER PUBLIC	CATIONS
	American Societ	y for Testing and Materials (ASTM)
	D 2671	Standard Methods of Testing Heat-Shrinkable Tubing for Electrical Use
	(Copies of ASTN	M publications may be obtained from the American Society for Testing and Materials, 1916 Race Street, Philadelphia, Pennsylvania 19103 or via the ASTM website at http://www.astm.org).
	International Org	ganization for Standardization (ISO)
	ISO 846	Plastics – Evaluation of the action of Microorganisms
	(Copies of ISO p	publications may be obtained from the International Organization for Standardization, 1, rue de Varembé, CH-1211 Geneva 20, Switzerland or via the ISO website at http://www.iso.ch/iso/en/ISOOnline.frontpage)
	SAE Internationa	al
	AMS-DTL-2305	Insulating Sleeving, Electrical, Heat Shrinkable, General Specification for
	(Copies of SAE	publications may be obtained from SAE International, 400 Commonwealth Drive, Warrendale, PA 15096-0001 or via the SAE website at http://www.sae.org.)
3.	REQUIREMEN	NTS
3.1	MATERIALS	
		be fabricated from thermally stabilized, modified fluoropolymer and shall be crosslinked by all be homogeneous and essentially free from flaws, defects, pinholes, bubbles, seams, aminants.
3.2	PROPERTIES	
	The tubing shall	meet the requirements of Table 3.
4.	QUALITY ASS	SURANCE PROVISIONS
4.1	CLASSIFICATI	ON OF TESTS
4.1.1	Qualification Te	sts
		ts are those performed on tubing submitted for qualification as a satisfactory product and Il tests listed in this specification.

If this document is printed it becomes uncontrolled. Check for the latest revision.

#### 4.1.2 <u>Acceptance Tests</u>

Acceptance tests are those performed on tubing submitted for acceptance under contract. Acceptance tests shall be:

Dimensions Longitudinal Change Concentricity Tensile Strength Ultimate Elongation Secant Modulus Low Temperature Flexibility Flammability Heat Shock Clarity Stability

Statistical process control data may be used to demonstrate conformance for dimensions.

#### 4.2 SAMPLING INSTRUCTIONS

#### 4.2.1 Qualification Test Samples

Qualification test samples shall consist of 50 feet (15 m) of tubing. Qualification of any size within each size range specified below shall qualify all sizes within that size range.

#### Range of Sizes 3/64 through 1/4 3/8 through 2

#### 4.2.2 <u>Acceptance Test Samples</u>

Acceptance test samples shall consist of not less than 16 feet (5 m) of tubing selected at random from each compound batch or the first sleeving production lot of the batch compound. Physical property tests performed at this time qualify subsequent sleeving lots produced from the same compound batch.

#### 4.2.3 Lot Formation

A lot shall consist of all tubing of the same size, from the same production run, and offered for inspection at the same time.

#### 4.3 TEST PROCEDURES

Unless otherwise specified, perform tests on specimens which have been fully recovered by conditioning for 3 minutes in a  $200 \pm 5^{\circ}$ C ( $392 \pm 9^{\circ}F$ ) oven. Condition the test specimens (and measurement gauges, when applicable) for 3 hours at  $23 \pm 3^{\circ}$ C ( $73 \pm 5^{\circ}F$ ) and  $50 \pm 5$  percent relative humidity prior to all testing. Use mechanical convection type ovens in which air passes the specimens at a velocity of 100 to 200 feet (30 to 60 m) per minute.

### 4.3.1 Low Temperature Flexibility

For tubing of expanded diameter less than 1/4 inch (6 mm), cut three tubular specimens, 12 inches (300 mm) long, from the expanded tubing. For tubing of expanded diameter 1/4 inch (6 mm) or greater, cut three strip specimens, 1/4 inch (6 mm) wide and 12 inches (300 mm) long, from the expanded tubing. Recover the specimens in accordance with Section 4.3 and condition with appropriate mandrels for 4 hours at  $-55 \pm 2^{\circ}$ C (-67  $\pm 4^{\circ}F$ ). The mandrel diameter shall be 10 times the specimen thickness,  $\pm 10$  percent. For tubular specimens, the specimen thickness shall be equivalent to the outside diameter. While at the specified temperature, and without removing the specimens from the cold chamber, wrap the specimens 360° around the mandrel in approximately 2 seconds. Disregard any side cracking, caused by flattening of the specimens on the mandrel.

# 4.4 REJECTION AND RETEST

Failure of any sample of tubing to conform to any one of the requirements of this specification shall be cause for rejection of the lot represented. Tubing which has been rejected may be replaced or reworked to correct the defects and resubmitted for acceptance. Before resubmitting, full particulars concerning previous rejection and action taken to correct the defects shall be furnished to the inspector.

# 5. PREPARATION FOR DELIVERY

#### 5.1 FORM

The tubing shall be supplied on spools, unless otherwise specified.

# 5.2 PACKAGING

Packaging shall be in accordance with good commercial practice.

# 5.3 MARKING

Each container of tubing shall be permanently and legibly marked with the size, quantity, manufacturer's name, product name, and lot number.

	As Supplied		As Recovered							
	Inside Diameter Minimum		Inside Diameter Wall Thickness							
Size			Maximum		Minimum		Maximum		Nominal	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
3/64	.046	1.17	.023	0.58	.008	0.20	.012	0.30	.010	0.25
1/16	.063	1.60	.031	0.79	.008	0.20	.012	0.30	.010	0.25
3/32	.093	2.36	.046	1.17	.008	0.20	.012	0.30	.010	0.25
1/8	.125	3.17	.062	1.57	.008	0.20	.012	0.30	.010	0.25
3/16	.187	4.74	.093	2.36	.008	0.20	.012	0.30	.010	0.25
1/4	.250	6.35	.125	3.17	.009	0.23	.015	0.38	.012	0.30
3/8	.375	9.50	.187	4.74	.009	0.23	.015	0.38	.012	0.30
1/2	.500	12.70	.250	6.35	.009	0.23	.015	0.38	.012	0.30
3/4	.750	19.05	.375	9.50	.014	0.36	.020	0.51	.017	0.43
1	1.000	25.40	.500	12.70	.016	0.41	.022	0.56	.019	0.48
1-1/2	1.500	38.10	.750	19.05	.017	0.43	.023	0.58	.020	0.51
2	2.000	50.80	1.000	25.40	.017	0.43	.023	0.58	.020	0.51

# TABLE 1Tubing Dimensions

# TABLE 2Mandrel Dimensions for Bend Testing

Tubing Size	Mandrel Diameter		
	in.	mm.	
3/64 to 1/4 inclusive	$5/16 \pm 0.002$	$7.9 \pm 0.05$	
3/8 to 1/2 inclusive	$3/8 \pm 0.003$	$9.5 \pm 0.08$	
3/4 to 2 inclusive	$7/16 \pm 0.004$	$11.1 \pm 0.10$	

If this document is printed it becomes uncontrolled. Check for the latest revision.

Daga	6
Page	0

PROPERTY	UNIT	REQUIREMENT	<b>TEST METHOD</b>
PHYSICAL			
Dimensions	Inches (mm)	In accordance with Table 1	ASTM D 2671
Longitudinal Change	Percent	+0, -10	Note 1
Tensile Strength	psi (MPa)	3500 (24.1) minimum	ASTM D 2671
Ultimate Elongation	Percent	300 minimum	Note 2
Concentricity (Expanded)			ASTM D 2671
Sizes 3/64 through 1	Percent	70 minimum	
Sizes $1-1/2$ and $2$	Percent	60 minimum	
Secant Modulus (Expanded)	psi (MPa)	2.5 x 10 <sup>4</sup> (172) minimum	ASTM D 2671
Specific Gravity		1.90 maximum	ASTM D 2671
Low Temperature Flexibility		No cracking	Section 4.3.1
4 hours at $-55 \pm 2^{\circ}C (-67 \pm 4^{\circ}F)$			
Heat Shock		No dripping, flowing or cracking	Table 2
4 hours at $250 \pm 3^{\circ}C (482 \pm 5^{\circ}F)$			ASTM D 2671
Heat Resistance			ASTM D 2671
336 hours at $225 \pm 3^{\circ}C (437 \pm 5^{\circ}F)$			
Followed by test for:			
Ultimate Elongation	Percent	100 minimum	
Clarity Stability		Marking legible through tubing	AMS-DTL-23053
24 hours at $200 \pm 3^{\circ}C (392 \pm 5^{\circ}F)$		wall	
ELECTRICAL			
Dielectric Strength	Volts/mil	400 (15,760) minimum	ASTM D 2671
	(volts/mm)		Note 3
Volume Resistivity	ohm-cm	10 <sup>11</sup> minimum	ASTM D 2671
CHEMICAL			
Copper Mirror Corrosion		Noncorrosive	ASTM D 2671
16 hours at $160 \pm 2^{\circ}C (320 \pm 4^{\circ}F)$			Procedure A
Copper Contact Corrosion		No pitting or blackening of	ASTM D 2671
16 hours at $160 \pm 2^{\circ}C (320 \pm 4^{\circ}F)$		copper	Procedure B
Flammability		Self-extinguishing within	ASTM D 2671
		1 minute, 25% maximum flag	Procedure C
		burn	
Fungus Resistance			ISO 846 Method B
Followed by tests for:			
Tensile Strength	psi (Mpa)	3500 minimum <i>(24.1)</i>	Note 2
Ultimate Elongation	percent	300 minimum	ASTM D 2671
Dielectric Strength	Volts per mil	400 minimum (15,760)	ASTM D 2671
	(volts per mm)		
Water Absorption	Percent	0.5 maximum	ASTM D 2671
24 hours at $23 \pm 3^{\circ}C (73 \pm 5^{\circ}F)$			

# TABLE 3Requirements

If this document is printed it becomes uncontrolled. Check for the latest revision.

PROPERTY	UNIT	REQUIREMENT	<b>TEST METHOD</b>
Fluid Resistance			ASTM D 2671
24 hours at $50 \pm 3^{\circ}$ C (122 $\pm 5^{\circ}$ F) in:			Note 4
JP-8 Fuel (MIL-T-83133)			
Hydraulic Fluid (MIL-H-5606)			
Lubricating Oil, (MIL-L-23699)			
Lubricating Oil, (MIL-L-7808)			
5% NaCl, O-S-1926			
De-icing Fluid (MIL-A-8243)			
Water			
Followed by tests for:			
Tensile Strength	psi (MPa)	2000 (13.8) minimum	
Ultimate Elongation	Percent	250	
Dielectric Strength	Volts/mil	400 (15,760) minimum	
	(volts/mm)		

TABLE 3Requirements (continued)

NOTE 1: Condition the specimens for 3 minutes at  $200 \pm 3^{\circ}$ C ( $392 \pm 5^{\circ}$ F) and cool to room temperature before final measurements.

- NOTE 2: Use 1-inch (25.4-mm) bench marks, 1-inch (25.4-mm) initial jaw separation, and  $2 \pm .2$ -inch ( $50 \pm 5$ -mm) jaw separation speed.
- NOTE 3: Recover the specimens on the metal mandrels for 10 minutes, minimum, at  $175 \pm 2^{\circ}C (347 \pm 4^{\circ}F)$  or until the tubing is completely shrunk on the mandrels.

NOTE 4: To measure the dielectric strength, immerse the recovered specimens in the fluids prior to inserting the mandrels into the wiped and dried specimens.