RT-220 Specification



THERMOFIT® RT-220 Tubing Specification

TEC-108-120038

THERMOFIT[®] RT-220 Flexible, Heat-Shrinkable, Flame-Retarded Modified Fluoropolymer - Low Outgassing

RT-220 is a single wall heat-shrinkable tubing. It is made of a crosslinked fluoropolymer that provides it with flexibility. The material is also highly flame-retardant. RT-220 has a shrink ratio of 2:1.

RT-220 is resistant to abrasion, fluids, mechanical damage, and strain. The fluid resistance of RT-220 offers splash protection. RT-220 tubing is a low outgassing product RoHS compliant.


Continuous operating temperature -55 to 150°C (-67 to 302°F).

THIS IS A CLASS 1 DOCUMENT WHICH IS NONCONFIDENTIAL.

The information contained within this document is the property of TE Connectivity. It is supplied in confidence and the commercial security of the contents must be maintained. It must not be used for any purpose other than that for which it is supplied nor may any information contained in it be disclosed to unauthorized persons. It must not be reproduced in whole or in part without obtaining written permission from TE Connectivity (TE).

*Trademark. TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks. Other logos, product and/or company names may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclams all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions and design specifications.



RT-220 Specification



Table of Contents

1.	SCOPE					
2.	APPLICABLE DOCUMENTS 3					
	2.1. AMERICAN SOCIETY FOR TESTING AND MATERIAL32.2. INTERNATIONAL ORGANIZATION FOR STANDARDIZATION (ISO)32.3. MILITARY DOCUMENTS32.4.OTHER DOCUMENTS4					
3.	REQUIREMENTS4					
	3.1 MATERIALS 4 3.2 PROPERTIES 4					
4.	QUALITY ASSURANCE PROVISIONS4					
	4.1CLASSIFICATION OF TESTS44.1.1Qualification Tests44.1.2Acceptance Tests44.2SAMPLING INSTRUCTIONS54.2.1Qualification Test Samples54.2.2Acceptance Test Samples54.2.3Lot Formation54.2.3Lot Formation54.3TEST PROCEDURES54.3.1Dimensions and Longitudinal Change54.3.2Concentricity as Supplied64.3.3Weight per Length64.3.4Recovery Angle64.3.5Tensile Strength and Ultimate Elongation64.3.6Low Temperature Flexibility64.3.7Heat Shock74.3.8Dynamic Cut Through at Temperature74.3.10Copper Stability74.3.11Corrosive Effect84.3.12Fluid Resistance84.4REJECTION AND RETEST8					
5.	PREPARATION FOR DELIVERY8					
	5.1 FORM 5.2 PACKAGING 5.3 MARKING					
	<u>APPENDIX</u> 9					
	TABLE 1MANDREL DIMENSIONS FOR HEAT SHOCK9TABLE 2REQUIREMENTS9					



1. SCOPE

This specification covers the requirements for flexible electrical insulating, extruded tubing whose diameter will reduce to a predetermined size upon the application of heat in excess of $150^{\circ}C$ ($302^{\circ}F$).

1.1.FORM

Type 1: The tubing shall be flame retarded and shall be black or white.

2. APPLICABLE DOCUMENTS

This specification takes precedence over documents referenced herein. Unless otherwise specified, the latest issue of referenced documents apply. The following documents form a part of this specification to the extent specified herein.

2.1. AMERICAN SOCIETY FOR TESTING AND MATERIAL (ASTM)

ASTM D2671	Standard Methods of Testing Heat-Shrinkable Tubing for Electrical Use
ASTM D3032	Method of Testing Hookup Wire Insulation
ASTM E595	Test Method for Total Mass Loss and Collected Volatile Condensable
	Materials from Outgassing in a Vacuum Environment
ASTM G21	Standard Recommended Practice for Determining Resistance of
	Synthetic Polymeric Materials to Fungi

(Copies of ASTM publications may be obtained from the American Society for Testing and Materials, 1916 Race Street, Philadelphia, Pennsylvania 19103 or via the ASTM website at http://www.astm.org).

2.2. INTERNATIONAL ORGANIZATION FOR STANDARDIZATION (ISO)

ISO 846 Plastics-Evaluation of the action of microorganisms

(Copies of ISO publications may be obtained from the International Organization for Standardization, 1, rue de Varembé, CH-1211 Geneva 20, Switzerland or via the ISO website at http://www.iso.ch/iso/en/ISOOnline.frontpage)

2.3. MILITARY DOCUMENTS

MIL-G-5572	Gasoline, Aviation, Grades 80/87, 100/130, and 115/145
MIL-T-83133	JP-8 turbine fuel (NATO type F-34)
MIL-PRF-5606	Hydraulic Fluid, Petroleum Base, Aircraft, Missile and Ordnance
MIL-PRF-23699 MIL-STD-104	Lubricating Oil, Aircraft Turbine Engine, Synthetic Base Limits for Electrical Insulation Color

(Copies of Military documents are available online at http://quicksearch.dla.mil.)



RT-220 Specification



2.4. OTHER DOCUMENTS

RT-220 SCDRT-220 Tubing SCDUL 224Standard for Extruded Insulating Tubing

3. REQUIREMENTS

3.1. MATERIALS

The tubing shall be fabricated from thermally stabilized, modified fluoropolymer and shall be crosslinked by irradiation. It shall be homogeneous and essentially free from flaws, defects, pinholes, bubbles, seams, cracks, and inclusions.

3.2. PROPERTIES

The tubing shall meet the requirements of Table 2.

4. QUALITY ASSURANCE PROVISIONS

4.1. CLASSIFICATION OF TESTS

4.1.1. Qualification Tests

Qualification tests are those performed on tubing submitted for qualification as a satisfactory product and shall consist of all tests listed in this specification.

4.1.2. Acceptance Tests

Acceptance tests are those performed on tubing submitted for acceptance under contract. Acceptance tests shall be:

Dimensions Concentricity Longitudinal Change Recovery Angle Tensile Strength Ultimate Elongation 2% Secant Modulus Flammability Heat Shock

Statistical process control data may be used to demonstrate conformance for dimensions.



RT-220 Specification



4.2. SAMPLING INSTRUCTIONS

4.2.1. Qualification Test Samples

Qualification test samples shall consist of 50 feet (15 m) of black tubing. Qualification of any size within each size range specified below shall qualify all sizes within that size range. Black qualifies all colors.

Range of Sizes

3/64" through 1/4" 3/8" through 1"

For Dynamic Cut-Through test, size 3/16 shall qualify all sizes. For Fungus Resistance test, any size shall qualify all sizes.

4.2.2. Acceptance Test Samples

Acceptance test samples shall consist of not less than 5 m *(16 feet)* of tubing selected at random from each compound batch or the first sleeving production lot of the batch compound. Physical property tests performed at this time qualify subsequent sleeving lots produced from the same compound batch.

4.2.3. Lot Formation

A lot shall consist of all tubing of the same size, from the same production run, and offered for inspection at the same time.

4.3. TEST PROCEDURES

Dimensions can be found in RT-220 SCD or the specific drawing for the numbered size.

Unless otherwise specified, tests shall be performed on specimens which have been fully recovered by conditioning for 3 minutes in a $200 \pm 5^{\circ}$ C ($392 \pm 9^{\circ}$ F) oven. Prior to all testing, the test specimens (and measurement gauges, when applicable) shall be conditioned for 3 hours at $23 \pm 3^{\circ}$ C ($73 \pm 5^{\circ}$ F) and 50 ± 5 percent relative humidity. All ovens shall be of the mechanical convection type in which air passes the specimens at a velocity of 30 to 60 m (100 to 200 feet) per minute.

4.3.1. Dimensions and Longitudinal Change

Three 150-mm (6-inch) specimens of tubing, as supplied, shall be measured for length $\pm 1 \text{ mm} (\pm 1/32 \text{ inch})$, and inside diameter in accordance with ASTM D 2671, conditioned for 3 minutes in a 200 $\pm 5^{\circ}$ C (392 $\pm 9^{\circ}$ F) oven, cooled to 23 $\pm 3^{\circ}$ C (73 $\pm 5^{\circ}$ F) and then remeasured. Prior to and after conditioning, the dimensions of the tubing shall be in accordance with Table 1 and the longitudinal change shall be in accordance with Table 2. The longitudinal change shall be calculated as follows:



RT-220 Specification



Calculate the longitudinal change as follows:

 $LC = ((L_1 - L_0) / L_0) \times 100$

 $\begin{array}{ll} \mbox{Where:} & \mbox{LC} = \mbox{Longitudinal Change [percent]} \\ \mbox{L}_0 = \mbox{Length Before Conditioning [inches (mm)]} \\ \mbox{L}_1 = \mbox{Length After Conditioning [inches (mm)]} \\ \end{array}$

4.3.2. Concentricity as Supplied

Three 150-mm *(6-inch)* specimens of tubing, as supplied, shall be measured for minimum and maximum wall thickness. Concentricity shall be calculated as follows:

$$C = \frac{W_{min}}{W_{max}} \times 100$$

Where:	Vhere: C		Concentricity [Percent]
	Wmin	=	Minimum Wall Thickness
	W_{max}	=	Maximum Wall Thickness

4.3.3. Weight Per Length

A 305 \pm 0.8 mm (12 \pm 1/32-inch) length of tubing, as supplied, shall be weighed. The weight shall be multiplied by 100 and reported as kg/100 m (pounds/100 ft).

4.3.4. Recovery Angle

A length of tubing shall be cut such that the end of the tubing is 90 degrees to the longitudinal axis. The tubing shall be recovered in accordance with Section 4.3, and by means of an optical comparator or equivalent, the angle between the end and the longitudinal axis shall be measured. The deviation from 90 degrees shall be reported as the recovery angle.

4.3.5. Tensile Strength and Ultimate Elongation

Determine the tensile strength and ultimate elongation of the tubing in accordance with ASTM D 2671 using 25-mm (1-inch) bench marks, a jaw separation speed of $500 \pm 50 \text{ mm} (20 \pm 2 \text{ inches})$ per minute.

4.3.6. Low Temperature Flexibility

For tubing of expanded diameter 6 mm (1/4 inch) or greater, three strip specimens, 6 mm (1/4 inch) wide and 300 mm (12 inches) long, shall be cut from the expanded tubing. For tubing of expanded diameter less than 6 mm (1/4 inch) three tubular specimens, 12 inches (300 mm) long, shall be cut from the expanded tubing. The specimens shall be recovered in accordance with Section 4.3 and conditioned with appropriate mandrels for 4 hours at -55 ± 2°C (-67 ± 4°F). The mandrel diameter



shall be 10 times the specimen thickness, \pm 10 percent. For tubular specimens, the specimen thickness shall be equivalent to the outside diameter. While at the specified temperature, and without removing the specimens from the cold chamber, the specimens shall be wrapped 360 degrees around the mandrel in approximately 2 seconds. Any side cracking, caused by flattening of the specimens on the mandrel, shall be disregarded.

4.3.7. Heat Shock

Three 150-mm (6-inch) specimens of tubing shall be conditioned for 4 hours in a $250 \pm 5^{\circ}$ C ($482 \pm 9^{\circ}$ F) oven. The specimens shall be removed from the oven, cooled to $23 \pm 3^{\circ}$ C ($73 \pm 5^{\circ}$ F), wrapped 180 degrees around a mandrel selected in accordance with Table 2, and then visually examined for evidence of dripping, flowing, or cracking. Any side cracking caused by flattening of the specimen on the mandrel shall not constitute failure.

4.3.8. Dynamic Cut-Through at Temperature

Two 150-mm (6-inch) lengths of size 3/16-inch tubing shall each be recovered on a 175-mm (7-inch) length of 2.38-mm (3/32-inch) oil hardened drill rod, by placing in a 200 \pm 5°C (392 \pm 9°F) mechanical convection oven for 3 minutes. The cut-through tests shall be performed at 135 \pm 3°C (275 \pm 5°F) in accordance with ASTM D 3032 using the optional cutting edge. Four readings shall be taken on each of the assemblies.

4.3.9. Heat Resistance

Specimens in accordance with Section 4.3.5 shall be conditioned for 336 hours in a $225 \pm 3^{\circ}C$ (437 $\pm 5^{\circ}F$) oven. The specimens shall be removed from the oven, cooled to $23 \pm 3^{\circ}C$ (73 $\pm 5^{\circ}F$) and tested for elongation in accordance with Section 4.3.5.

4.3.10. Copper Stability

Three 150-mm (6-inch) specimens of tubing shall be slid over a snug-fitting, straight, clean, bare copper conductor. For tubing sizes 1/4 and smaller, a solid conductor shall be used; for tubing sizes 3/8 and larger, a solid or tubular conductor shall be used. The specimens on the conductors shall be conditioned for 24 hours in a desiccator or similar humidity chamber at 90 to 95 percent relative humidity and $23 \pm 3^{\circ}$ C ($73 \pm 5^{\circ}$ F). The specimens on the conductors then shall be conditioned for 168 hours in a 180 $\pm 3^{\circ}$ C ($356 \pm 5^{\circ}$ F) oven. After conditioning, the specimens shall be removed from the oven and cooled to $23 \pm 3^{\circ}$ C ($73 \pm 5^{\circ}$ F). The copper conductor then shall be removed from the tubing, and the tubing and conductor shall be examined. Darkening of the copper due to normal air oxidation shall not be cause for rejection. The tubing shall be tested for elongation in accordance with 4.3.5.



RT-220 Specification



4.3.11. Corrosive Effect

4.3.11.1. Copper Mirror Corrosion

The tubing shall be tested for copper mirror corrosion in accordance with ASTM D 2671, Procedure A, for 16 hours at $160 \pm 3^{\circ}C$ ($320 \pm 5^{\circ}F$). For tubing sizes 1/8 and larger, specimens shall consist of 6 x 25 mm ($1/4 \times 1$ -inch) strips cut longitudinally. Evidence of corrosion shall be the removal of copper from a mirror, leaving an area of transparency greater than 5 percent of its total area

4.3.11.2. Corrosion in Contact with Copper

The tubing shall be tested for corrosion in contact with copper for 16 hours at 175 \pm 3°C (347 \pm 5°F) in accordance with ASTM D 2671, Procedure B.

4.3.12. Fluid Resistance

Six 150-mm (6-inch) specimens of tubing, prepared and measured in accordance with ASTM D 2671 solvent resistance, shall be completely immersed in each listed fluid for 24 ± 2 hours at $50 \pm 3^{\circ}$ C ($122 \pm 5^{\circ}$ F). The volume of the fluid shall be not less than 20 times that of the specimens. After immersion, the specimens shall be lightly wiped and air-dried for 30 to 60 minutes at room temperature. Three specimens then shall be tested for dielectric strength and the other three for tensile strength.

4.4. REJECTION AND RETEST

Failure of any sample of tubing to conform to any one of the requirements of this specification shall be cause for rejection of the lot represented. Tubing which has been rejected may be replaced or reworked to correct the defects and resubmitted for acceptance. Before resubmitting, full particulars concerning previous rejection and action taken to correct the defects shall be furnished to Quality.

5. PREPARATION FOR DELIVERY

- 5.1. FORM
 - 5.1.1. The tubing shall be on spools unless otherwise specified.
- 5.2. PACKAGING
 - 5.2.1. Packaging shall be in accordance with good commercial practice. The shipping container shall not be less than 125-pound-test fibreboard.

5.3. MARKING

5.3.1. Each container of tubing shall be permanently and legibly marked with the size, quantity, manufacturer's identification, part number and lot number, and date of manufacturing.





APPENDIX

TABLE 1 MANDREL DIMENSIONS FOR HEAT SHOCK

Tubing			Mandrel Diameter		
				mm.	in.
3/64	to	3/16 i	nclusive	7.9	5/16
1/4	to	1 i	nclusive	19.1	3/4

TABLE 2 REQUIREMENTS

PROPERTY	UNIT	REQUIREMENT	TEST METHOD
PHYSICAL			
Dimensions	mm (Inches)	In accordance with RT220 SCD	Section 4.3.1
Longitudinal Change	Percent	+0, -10	ASTM D 2671
Concentricity as Supplied	Percent	70% minimum	Section 4.3.2
Weight Per Length as Supplied	kg/100 m (Ibs/100 ft) maximum	In accordance with RT-220 SCD	Section 4.3.3
Recovery Angle	Degrees	5 maximum	Section 4.3.4
Tensile Strength	MPa (psi)	27.6 minimum <i>(4,000)</i>	Section 4.3.5
Ultimate Elongation	Percent	300 minimum	ASTM D 2671
2% Secant Modulus	MPa (psi)	345 maximum (50,000)	ASTM D 2671
Low Temperature Flexibility 4 hours at -55°C (-67°F)		No cracking	Section 4.3.6
Heat Shock 4 hours at 250°C (482°F)		No dripping, flowing, or cracking	Section 4.3.7
Dynamic Cut-Through at 135°C (275°F)	N	5 minimum	Section 4.3.8 ASTM D 3032
Heat Resistance 336 hours at 225°C <i>(437°F)</i> Followed by test for:			Section 4.3.9
Ultimate Elongation	Percent	250 minimum	Section 4.3.5 ASTM D 2671
Copper Stability 168 hours at 180°C <i>(356°F)</i> Followed by test for		No brittleness, glazing or severe discoloration of tubing. No pitting or blackening of copper.	Section 4.3.10
Ultimate Elongation	Percent	250 minimum	Section 4.3.5 ASTM D 2671
Color		MIL-STD-104, Class I	MIL-STD-104
ELECTRICAL Dielectric Strength	Volts/ mm (Volts /mil)	19,680 minimum <i>(500)</i>	ASTM D 2671
Volume Resistivity	ohm-cm	1x10 ¹¹ minimum	ASTM D 2671

Requirements are continued on next page.





TABLE 2 REQUIREMENTS (continued)

CHEMICAL			
Corrosive Effect		Noncorrosive	Section 4.3.11 ASTM D 2671
Copper Mirror Corrosion 16 hours at 160°C <i>(320°F)</i>		Copper Removal 5%, maximum	Section 4.3.11.1 ASTM D 2671 Procedure A
Copper Contact Corrosion 16 hours at 175°C (347°F)		No blackening or pitting of copper	Section 4.3.11.2 ASTM D 2671 Procedure B
Flammability		 25% maximum flag burn no burning of cotton no flaming, or glowing longer than 60 seconds 	UL 224, VW-1 ASTM D 2671 Procedure C
Fungus Resistance			
E e a Destata e Alterrate Mathema		Rating of 1 or less	ASTM G 21
Fungus Resistance - Alternate Method			ISO 846 Method B
Followed by tests for:			
Tensile Strength	MPa <i>(psi)</i>	10.3 minimum <i>(1,500)</i>	Section 4.3.5 ASTM D 2671
Ultimate Elongation	Percent	200 minimum	ASTM D 2671
Dielectric Strength	Volts/mm (Volts/mil)	19,680 minimum <i>(500)</i>	
Water Absorption 24 hours at 23°C (73°F)	Percent	0.5 maximum	ASTM D 2671
Fluid Resistance 24 hours at 50°C (122°F) JP-8 Fuel (MIL-T-83133) Hydraulic Fluid (MIL-PRF-5606) Aviation Gasoline (100/130) (MIL-G-5572) Water Trichloroethane Lubricating Oil MIL-PRF-23699 Followed by tests for:			Section 4.3.12 ASTM D 2671
Dielectric Strength	Volts/mm (Volts/mil)	15,760 minimum <i>(400)</i>	ASTM D 2671
Tensile Strength	MPa (psi)	13.8 minimum <i>(2,000)</i>	Section 4.3.5 ASTM D 2671
Vacuum Outgassing TML (Total Mass Loss)	Percent	1.0 maximum	ASTM E 595
VCM (Volatile Condensable Materials)	Percent	0.1 maximum	ASTM E 595

*Trademark of the Monsanto Company