






LOC	DIST	REV	DATE	BY	CHK	APPV
GP	00	C	26MAR2015	JY	SH	




SCALE 5:1




- 1 SURFACE TRACES PERMITTED WITHIN THIS LENGTH EXCEPT WHERE CAGE STANDOFFS, SHOWN IN DETAIL J, CONTACT PC BOARD.
- 2 MINIMUM PITCH DIMENSION.
- 3 MATES WITH QSFP MSA COMPATIBLE TRANSCEIVER.
- 4 REFERENCE APPLICATION SPEC 114-13218 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.
- 6 DIMENSION C IS THE NOMINAL THICKNESS OF CUSTOMER SUPPLIED PC BOARD,
SINGLE SIDED PC BOARD MINIMUM THICKNESS: 1.45
DOUBLE SIDED PC BOARD MINIMUM THICKNESS: 2.7.
- 7 DATUM A IS TOP SURFACE OF THE HOST BOARD.
- 8 2D BARCODE AND DATE CODE (YYWW) MARKED APPROXIMATELY AS SHOWN.
- 9 CAGE MATERIAL: 0.25 THICK NICKEL SILVER
EMI SPRING MATERIAL: COPPER ALLOY
FRONT FLANGE MATERIAL: ZINC ALLOY.
- 10 EMI SPRING FINISH: 2µm MIN TIN
FRONT FLANGE FINISH: 3µm MIN THICK TIN OVER 1.27µm
MIN THICK NICKEL OVER 5.08µm
MIN THICK COPPER.



SEE DETAIL J





DETAIL J SCALE 20:1





1551891-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		OWN: E. ZIJLSTRA 08NOV2010 CHK: R. VERBEET 08NOV2010 APPV: T. D. ROER 08NOV2010	NAME: CAGE ASSEMBLY, BEHIND BEZEL, QSFP
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	APPLICATION SPEC
mm	0 PLC ±0.13 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.13 4 PLC ±0.13 ANGLES ±0.13		
MATERIAL	FINISH	WEIGHT	RESTRICTED TO
		A100779C=1551891	
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 4 REV C

LOC		DIST		REVISIONS			
GP	00	P	LTN	DESCRIPTION	DATE	DMN	APVD
-	-	-	-	SEE SHEET 1	-	-	-




ONE SIDED CONFIGURATION



BELLY TO BELLY CONFIGURATION
 SIMILAR TO ONE SIDED EXCEPT
 WHERE NOTED

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		DMN: E.ZIJLSTRA 08NOV2010 CHK: R.VERBEET 08NOV2010 APVD: T.D.ROER 08NOV2010	TE Connectivity NAME: CAGE ASSEMBLY, BEHIND BEZEL, ZQSF PRODUCT SPEC: - APPLICATION SPEC: - WEIGHT: - MATERIAL: - FINISH: -	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	SIZE: A1	CAGE CODE: 00779	DRAWING NO: 1551891
0 PLC ±0.13	1 PLC ±0.13	SCALE: 5:1	SHEET: 2	OF: 4
2 PLC ±0.13	3 PLC ±0.13	CUSTOMER DRAWING	REV: C	
4 PLC ±0.13	ANGLES ±0.13			

LOC	DIST	REV	DATE	BY	APPV
GP	00				
REVISIONS					



CROSSHATCHED AREA DENOTES COMPONENT AND TRACE KEEP-OUT (EXCEPT CHASSIS GROUND)


THIS AREA DENOTES COMPONENT KEEP-OUT (TRACES ALLOWED)

RECOMMENDED SINGLE-SIDE PC BOARD LAYOUT
 SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		OWN: E. ZIJLSTRA 08NOV2010	CHK: R. VERBEEF 08NOV2010	APVD: T. D. ROER 08NOV2010	NAME: CAGE ASSEMBLY, BEHIND BEZEL, ZQSF
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC: -	
		0 PLC ±0.13	1 PLC ±0.13	APPLICATION SPEC: -	
		2 PLC ±0.13	3 PLC ±0.13	SIZE: A100779	
		4 PLC ±0.13	ANGLES ±0.13	CAGE CODE: -	
MATERIAL: -		FINISH: -		DRAWING NO: 1551891	
		WEIGHT: -		RESTRICTED TO: -	
		CUSTOMER DRAWING		SCALE: 5:1 SHEET 3 OF 4 REV C	

LOC	DIST	REV	DATE	BY	APPD
GP	00				

REVISIONS					
REV	DATE	BY	APPD	DESCRIPTION	DATE
-	-	-	-	SEE SHEET 1	-



RECOMMENDED PCB LAYOUT
 BELLY TO BELLY CONFIGURATION
 SEE SHEET 3 FOR KEEP OUT AREAS
 SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN: E.ZIJLSTRA 08NOV2010 CHK: R.VERBEET 08NOV2010 APVD: T.D.ROER 08NOV2010	TE Connectivity
DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.13 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.13 4 PLC ±0.13 ANGLES ±0.13		NAME: CAGE ASSEMBLY, BEHIND BEZEL, ZQSFP PRODUCT SPEC: - APPLICATION SPEC: - WEIGHT: - MATERIAL: - FINISH: -	
MATERIAL: - FINISH: -		SIZE: A1 CAGE CODE: 00779 DRAWING NO: C=1551891	RESTRICTED TO: - SCALE: 5:1 SHEET: 4 OF 4 REV: C