





The Series FCA-212 relay is a polarized single-side stable design, where the flux from a permanent magnet provides the armature holding force in the deactivated state, and its flux path is switched and combined with the coil flux in the operated state. This

results in appreciably increased contact pressure in both states over that of a spring return nonpolar design. We also manufacture other versions of this relay:

FCA-412 — 12 Amp 4PDT Relay

General Specifications

Temperature Rating — -70°C TO + 125°C

Altitude — 300,000 Feet

Shock* -

Z. Y. & X Enclosures -200 g for 6 mS W & M Enclosures (Stud Mtg.) — 100 g for 6 mS

Vibration, Sinusoidal* —

Z, Y, & X Enclosures 30 g 33-3000Hz W Enclosure -20 g 33-3000Hz

Vibration, Random* —

Z, Y, & X Enclosures -0.4 g²/Hz 50-2000Hz W & M Enclosures (Stud Mtg.) — 0.2 g²/Hz 50-2000Hz

Dielectric Strength -

At Sea Level -

All circuits to ground and circuit to circuit — 1250 V rms Coil to ground — 1000 V rms At 80.000 Feet - 350 V rms

Insulation Resistance -

Initial (500 VDC) — 100 M Ω Min. After Life or Environmental Tests $50 \text{ M}\Omega \text{ Min.}$

Operate Time at Nominal Voltage

DC Relays — 10 ms or less AC Relays — 15 ms or less

Release Time at Nominal Voltage -

DC Relays — 10 ms or less AC Relays — 50 ms or less

For additional support numbers

Product Facts

- **■** Hermetically Sealed
- All Welded Construction
- **■** Balanced Force
- Permanent Magnet Drive
- Contacts Silver Cadmium **Oxide with Gold Plating**
- Coils for DC, 50 to 400Hz and 400Hz AC
- Weight 1.6 ounces max. (45.4 grams)

Contact Rating — Amperes Ratings Are Continuous Duty

Type of Load	Life (Min.) Cycles x 103	28 VDC	115VAC 400Hz	115/200VAC 3Ø	
Load				400Hz	60Hz*
Resistive	100	12	12	12	2.5
Inductive	20	8	8	8	2.5
Motor	100	4	4	4	2.0
Lamp	100	2	2	2	1

^{*60} Hz loads rated for 10,000 operations

Overload Current — 40 AMPS DC, 60 AMPS 400Hz Rupture Current — 50 AMPS DC, 80 AMPS 400Hz

Contact Make Bounce —1 MILLISECOND AT NOMINAL VOLTAGE

Max. Contact Drop at 12 Amps — INITIAL 0.150 VOLTS

End of Life — 0.175 VOLTS

Coil Data

Coil Code	Nominal Voltages	Freq. Hz	DC Res. AC Amps (B)	Over Temperature Range		
				Pickup or Below Volts	Dropout or Above Volts	Must Hold Voltage (C)
1	6	DC	20 Ω	4.5	0.3	2.5
2	12	DC	80 Ω	9.0	0.75	4.5
3	28	DC	320 Ω	18.0	1.5	7.0
4 (A)	28	DC	320 Ω	18.0	1.5	7.0
5	48	DC	920 Ω	32.0	2.5	14.0
6	28	400Hz	180 mA	22.0	1.25	10.0
7	28	50/400Hz	100 mA	22.0	1.25	10.0
8	115	400 Hz	40 mA	90.0	5.0	40.0
9	115	50/400 Hz	30 mA	95.0	5.0	40.0

- A. CODE 4 COILS HAVE BACK EMF SUPPRESSION TO 42 VOLTS MAX.
- B. DC COIL RESISTANCE ± 10% AT 25°C; AC COIL MAX. CURRENT AT NOMINAL VOLTAGE.
- C. RELAY WILL STAY IN PICKED-UP STATE DOWN TO MUST HOLD VOLTAGES SHOWN.
- D. MAX. OVERVOLTAGE: 6 & 12 VDC COILS 120% OF NOMINAL; ALL OTHERS 110% OF NOMINAL.
- E. COILS AVAILABLE FOR OTHER VOLTAGES AND FOR AC 50/60HZ.


www.te.com

^{*} Max. contact opening under vibration or shock 10 microseconds



FCA-212 Series, 12 Amperes, DPDT (Continued)

Below are shown the standard terminal types and the enclosures available. Specify the assembly as indicated under How To Order. Dimensions are shown in inches \pm .010 and (Millimeters \pm .25).




www.te.com



FCA-212 Series, 12 Amperes, DPDT (Continued)


Terminal Wiring



NOTE: Polarity must be observed with DC coil supply. Relay is polarized with a permanent magnet and will not operate or be damaged by reverse polarity.

Diodes used in transient suppression and in AC rectifier circuits have peak inverse voltage rating of 600 VDC minimum. Zener diodes have a minimum rating of 1 watt.

Terminal designations are for reference only and do not appear on the header.



HOW TO ORDER

RELAY TYPE TERMINALS (Socket Pins, DC Coil) ENCLOSURE (With Flanges) COIL (28 VDC With Transient Suppression).

www.te.com