


REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	MODIF TRAITEMENT	22MA107	FB	DM
	B	ADDITIONAL PART	04AUG2020	GL	-



REFERENCE	PN	Packing Qty	CAPACITES: Principal - Dérivé CAPACITY: Main - Tap	MASSE WEIGHT	COUPLE DE RUPTURE BREAKING SHEAR HEAD TORQUE
P3X4/0	1727742-1	50	4 AWG to 4/0 AWG Al-Cu * * Max Cu-Cu: 2/0 to 2/0 AWG	170g	18Nm
P3X4/0 (B25)	1727742-2	25	4 AWG Str to 4/0 AWG Al-Cu * * Max Cu-Cu: 2/0 to 2/0 AWG		

MARQUAGE: LOGO, REFERENCE, CAPACITES, LOT
MARKING: LOGO, REFERENCE, CAPACITIES, DATE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES:

FINISH
FINITION

DIMENSIONS:

mm

DWN / DESSINE
C. ANDRE

23SEP2003

MATERIAL
MATIERE

TE

TE Connectivity

CHK / VERIFIE
C. TISSE

APVD / APPROUVE
G. PORCHERAY

PRODUCT SPEC
SPEC. PRODUIT

APPLICATION SPEC
SPEC. APPLICATION

NAME
TITRE

P3X4/0

SIZE
FORMAT

A4

CAGE CODE

-

DRAWING NO
No PLAN

C-1727742

RESTRICTED TO
RESERVE A

WEIGHT
MASSE APPROX.

CUSTOMER DRAWING

/PLAN CLIENT

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 1:2

SHEET
FEUILLE

OF
DE 1

REV

B

